



ELECTRICAL CHARACTERISTICS

- 1. RATING:DC 30V 0.1A
- 2. CONTACT RESISTANCE: 100MΩ MAX
- 3. INSULATION RESISTANCE:100MΩ MIN
- 4. DIELECTRIC STRENGTH:AC 250V (50~60HZ) /60S

MECHANICAL CHARACTERISTICS

- 1. PRACTICAL TEMPERATURE RANG:-40℃~+85℃
- 2. OPERATING FORCE:250±50GF
- 3. MECHANICAL LIFE:20000 CYCLES

NO.	PART NAME	MATERIAL	QTY	FINISHING
7	TERMINAL	BRASS	6	AG PLATED
6	CASE	PPA	1	GRAY
5	LOCK PIN	SUS WIRE	1	NATURAL
4	SPRING	SUS WIRE	1	NATURAL
3	CANTACT	BRONZE	2	AG PLATED
2	KNOB	PPA	1	WHITE
1	cover	PPA	1	BLACK

X. ±0.50	X.° ± 5°	UNITS mm
.X ±0.30	.X° ± 2°	
.XX ±0.20	.XX° ± 1°	
.XXX ± 0.1	.XXX ±0.5°	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		FINISH
		Operation Force 250GF

<p>深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD</p>	PART NO. YTS58L250DWS	TITLE: 按键类5.8x5.8 脚距2.9x3.6mm						
	APPD: ROGER	DWG NO.: YTS58L250DWS						
CHKD: RDC	DR: BILLY WANG 2020/08/21	<table border="1"> <tr> <td>SCALE</td> <td>SHEET</td> <td>REV.</td> </tr> <tr> <td>1/1</td> <td>1/1</td> <td>A1</td> </tr> </table>	SCALE	SHEET	REV.	1/1	1/1	A1
SCALE	SHEET	REV.						
1/1	1/1	A1						