深圳市德普微电子有限公司

DP3080C

TRMOS N-MOSFET 30V, 3.6mΩ, 80A

Product Summary

Part #	V_{DS}	$R_{DS(on).typ}$	I_D
DP3080C	30V	3.6mΩ	80A



Features

- Advanced high cell desity Trench MOSFET technology
- Better $R_{DS(on)}$ enabled by a low $R_{DSon.sp}$, low conduction losses
- Excellent Q_gx$R_{DS(on)}$ product(FOM)
- Qualified according to JEDEC criteria



Applications

- Battery management
- Power Management Switches

100% Avalanche Tested

100% Rg Tested

Package Marking and Ordering Information

Part #	Marking	Package	Packing
DP3080C	DP3080C	TO-252	Tube/Reel

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Drain-source voltage	V_{DS}	30	V
Continuous drain current T_C = 25°C (Silicon limit) T_C = 25°C (Package limit) T_C = 100°C (Silicon limit)	I_D	101 80 64	A
Pulsed drain current (T_C = 25°C, t_p limited by T_{jmax})	$I_{D\ pulse}$	320	A
Avalanche energy, single pulse (l=0.3mH, Rg=25)[1]	E_{AS}	94	mJ
Gate-Source voltage	V_{GS}	±20	V
Power dissipation (T_C = 25°C)	P_{tot}	75	W
Operating junction and storage temperature	T_j , T_{stg}	-55...+150	°C

[1].EAS is tested at starting T_j = 25°C, V_{GS} = 10V.

Thermal Resistance

Parameter	Symbol	Max	Unit
Thermal resistance, junction – case.	R_{thJC}	1.67	°C/W
Thermal resistance, junction – ambient(min. footprint)	R_{thJA}	62	

Electrical Characteristic (at Tj = 25 °C, unless otherwise specified)

Parameter	Symbol	Value			Unit	Test Condition
		min.	typ.	max.		
Static Characteristic						
Drain-source breakdown voltage	BV_{DSS}	30	-	-	V	V_{GS}=0V, I_D=250uA
Gate threshold voltage	$V_{GS(th)}$	0.8	1.3	1.8	V	V_{DS}=V_{GS},I_D=250uA
Zero gate voltage drain current	I_{DSS}	- -	- -	1 100	μA	V_{DS}=30V,V_{GS}=0V T_j=25°C T_j=150°C
Gate-source leakage current	I_{GSS}	-	-	±100	nA	V_{GS}=±20V,V_{DS}=0V
Drain-source on-state resistance	$R_{DS(on)}$	- -	3.6 4.9	4.3 6.1	mΩ mΩ	V_{GS}=10V, I_D=40A V_{GS}=4.5V, I_D=25A
Gate resistance	R_g	-	2.5	3.7	Ω	V_{GS}=0V, V_{DS}=0V, f=1MHz
Transconductance[2]	g_{fs}	-	110	-	S	V_{DS}=5V,I_D=40A
Dynamic Characteristic[2]						
Input Capacitance	C_{iss}	-	2216	-	pF	V_{GS}=0V, V_{DS}=15V, f=1MHz
Output Capacitance	C_{oss}	-	289	-		
Reverse Transfer Capacitance	C_{rss}	-	225	-		
Gate Total Charge(V_{GS}=10V)	Q_g	-	48	-	nC	V_{GS}=10V, V_{DS}=15V, I_D=40A, f=1MHz
Gate Total Charge(V_{GS}=4.5V)	Q_g	-	23.5	-		
Gate-Source charge	Q_{gs}	-	8.7	-		
Gate-Drain charge	Q_{gd}	-	10.5	-		
Turn-on delay time	$t_{d(on)}$	-	13.8	-	ns	V_{GS}=10V, V_{DD}=15V, R_{G_ext}=2.7Ω
Rise time	t_r	-	88	-		
Turn-off delay time	$t_{d(off)}$	-	42	-		
Fall time	t_f	-	94	-		

Body Diode Characteristic

Parameter	Symbol	Value			Unit	Test Condition
		min.	typ.	max.		
Body Diode Forward Voltage	V_{SD}	-	0.7	1	V	V_{GS}=0V,I_{SD}=1A
Diode continuous forward current	I_s	-	80	-	A	TC = 25°C
Diode pluse current	$I_{s\ pluse}$	-	320	-	A	TC = 25°C
Body Diode Reverse Recovery Time[2]	t_{rr}	-	13	-	ns	I_F=20A, dI/dt=100A/μs
Body Diode Reverse Recovery Charge[2]	Q_{rr}	-	4	-	nC	

[2]. Defined by design. Not subject to production test

Typical Performance Characteristics

Fig 1: Output Characteristics



Fig 2: Transfer Characteristics



Fig 3: Rds(on) vs Drain Current and Gate Voltage



Fig 4: Rds(on) vs Gate Voltage



Fig 5: Rds(on) vs. Temperature



Fig 6: Capacitance Characteristics



Fig 7: Gate Charge Characteristics



Fig 8: Body-diode Forward Characteristics



Fig 9: Power Dissipation



Fig 10: Drain Current Derating



Fig 11: Safe Operating Area



Fig 12: Max. Transient Thermal Impedance



Test Circuit & Waveform

Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms





Unclamped Inductive Switching (UIS) Test Circuit & Waveforms





Diode Recovery Test Circuit & Waveforms





Package Outline: TO-252



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.15	2.45	0.085	0.096
A1	0.00	0.15	0.000	0.006
A2	0.76	1.36	0.030	0.054
b	0.60	0.91	0.024	0.036
b1	0.65	1.15	0.026	0.045
b2	5.00	5.64	0.197	0.222
c	0.45	0.61	0.018	0.024
c1	0.36	0.66	0.014	0.026
D	5.80	6.30	0.228	0.248
D1	5.00	6.00	0.197	0.236
e	2.29 BSC.		0.090 BSC.	
E	6.30	6.90	0.248	0.272
E1	4.55	5.30	0.179	0.209
H	9.40	10.48	0.370	0.413
L	1.18	1.70	0.046	0.067
L1	2.92 REF		0.115 REF	
L2	0.36	0.66	0.014	0.026
L3	0.72	1.35	0.028	0.053
L4	0.60	1.20	0.024	0.047

Revision History

Revison	Major changes
1.0	Release for formal version