

PARA LIGHT ELECTRONICS CO., LTD.

4F, No.1, Lane 93, Chien Yi Road, Chung Ho City, Taipei, Taiwan.

Tel: 886-2-2225-3733 Fax: 886-2-2225-4800 E-mail: para@para.com.tw http://www.para.com.tw

DATA SHEET

PART NO.: LQR5VELPG6W447G

REV: <u>A/0</u>


CUSTOMER'S APPROVAL : _____ DCC : ____



LQR5VELPG6W447G

REV:A/0


PACKAGE DIMENSIONS



ITEM	MATERIALS
RESIN	Epoxy Resin
LEAD FRAME	Sn Plating iron Alloy

Note:

- 1.All Dimensions are in millimeters.
- 2.Tolerance is ±0.25mm(0.010 ")
 Unless otherwise specified.
- 3.Protruded resin under flange is 1.5mm(0.059 ") max.





LQR5VELPG6W447G

REV:A/0

FEATURES

- * High-brightness
- * High reliability
- * Low-voltage characteristics
- * Wide view angle
- * Pb FREE Products
- * RoHS Compliant

CHIP MATERIALS

* Dice Material: GaAlInP/GaAs & GaInN/GaN

* Light Color: PURE GREEN & RED

* Lens Color : White Diffuse

ABSOLUTE MAXIMUM RATING : ($Ta = 25^{\circ}C$)

SYMBOL	DESCRIPTION	RED	PURE GREEN	UNIT
PD	Power Dissipation Per Chip	85	120	mW
VR	Reverse Voltage Per Chip	5	5	V
IF	Average Forward Current Per Chip	30	30	mA
IPF	Peak Forward Current (Duty=0.1,1KHZ) Per Chip	120	120	mA
-	Derating Linear From 25°C Per Chip	0.3	0.4	mA/°C
Topr	Operating Temperature Range	erature Range -40°C to 85°C		
Tstg	Storage Temperature Range	-40°C to 85°C		

ELECTRO-OPTICAL CHARACTERISTICS: (Ta = 25°C)


SYMBOL	PARAMETER	TEST CONDITION		MIN.	TYP.	MAX.	UNIT
\/⊏	Forward Voltage	15-20-a	Red		2.2	2.8	V
VF	Forward Voltage	IF=20mA	PURE GREEN		2.9	4.0	V
ID	Daylara a Currant	\/D-E\/	Red			100	μΑ
IR	Reverse Current	VR=5V	PURE GREEN			100	μA
λD	Dominant	IF=20mA	Red		622		nm
λD	Wavelength	IF-ZUITA	PURE GREEN		520		nm
Δλ	Spectral Line	IF=20mA	Red		35		nm
Δλ	Half-Width	IF-ZUITA	PURE GREEN		30		nm
201/2	Half Intensity Angle	IF=20mA	Red		100		deg
201/2	nali intensity Angle	IF-ZUITA	PURE GREEN		100		deg
	1	JE 00 A	Red		480		mcd
IV	Luminous Intensity	IF=20mA	PURE GREEN		800		mcd





LQR5VELPG6W447G


REV:A/0


VE



















LQR5VELPG6W447G


REV:A/0


LPG6
















LQR5VELPG6W447G

REV:A/0

Label Explanation

PAR/ igh	1 ハ		子股分有	
PARA	NO.	•		
LOT	NO.	* *		INSPECTED
BIN		* *		
Q'	TY	* *	PCS	
N. W		•	g	

PARA NO.: LQR5VELPG6W447G

Refer to p12

LOT NO.: E L L 4 7 0009

A B C D E F

A---E: For series number B---L: Local F: Foreign

C---L: LAMP D---Year E---Month

F---SPEC.




LQR5VELPG6W447G

REV:A/0


SOLDERING

METHOD	SOLDERING CONDITIONS	REMARK
DIP SOLDERING	Bath temperature: 260°C Immersion time: with 5 sec, 1 time	 Solder no closer than 3mm from the base of the package Using soldering flux," RESIN FLUX" is recommended.
SOLDERING IRON	Soldering iron: 30W or smaller Temperature at tip of iron: 300℃ or lower Soldering time: within 5 sec.	 During soldering, take care not to press the tip of iron against the lead. (To prevent heat from being transferred directly to the lead, hold the lead with a pair of tweezers while soldering

1) When soldering the lead of LED in a condition that the package is fixed with a panel (See Fig.1), be careful not to stress the leads with iron tip.



2) When soldering wire to the lead, work with a Fig (See Fig.2) to avoid stressing the package.




Regarding solution in the tinning oven for product-tinning, compound sub-solution made of tin & copper and sliver is proposed with the temperature of Celsius 260. The proportion of the alloyed solution is tin 95.5: copper 3.5: silver 0.5 by percentage. The time of tinning is constantly 3 seconds.



LQR5VELPG6W447G

REV:A/0

Similarly, when a jig is used to solder the LED to PC board, take care as much as possible to avoid steering the leads (See Fig.3).



- 4) Repositioning after soldering should be avoided as much as possible. If inevitable, be sure to preserve the soldering conditions with irons stated above: select a best-suited method that assures the least stress to the LED.
- Lead cutting after soldering should be performed only after the LED temperature has returned to normal temperature.

STORAGE

- 1) The LEDs should be stored at 30°C or less and 70% RH or less after being shipped from PARA and the storage life limits are 1 year .
- 2) PARA LED lead frames are comprised of a stannum plated iron alloy. The silver surface may be affected by environments which contain corrosive gases and so on. Please avoid conditions which may cause the LEDs to corrode, tarnish or discolor. This corrosion or discoloration may cause difficulty during soldering operations. It is recommended that the LEDs be used as soon as possible.

Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.




LQR5VELPG6W447G


REV:A/0

•LED MOUNTING METHOD

1) When mounting the LED by using a case, as shown Fig.4, ensure that the mounting holds on the PC board match the pitch of the leads correctly-tolerance of dimensions of the respective components including the LED should be taken into account especially when designing the case, PC board, etc. to prevent pitch misalignment between the leads and board holes, the diameter of the board holes should be slightly larger than the size of the lead. Alternatively, the shape of the holes should be made oval. (See Fig.4)



2) Use LEDs with stand-off (Fig.5) or the tube or spacer made of resin (Fig.6) to position the LEDs.






LQR5VELPG6W447G


REV:A/0

FORMED LEAD

1) The lead should be bent at a point located at least 2mm away from the package. Bending should be performed with base fixed means of a jig or pliers (Fig.7)




- 2) Forming lead should be carried our prior to soldering and never during or after soldering.
- 3) Form the lead to ensure alignment between the leads and the hole on board, so that stress against the LED is prevented. (Fig.8)



LEAD STRENGTH

1) Bend strength
Do not bend the lead more than twice. (Fig.9)





LQR5VELPG6W447G

REV:A/0

Tensile strength (@Room Temperature)
 If the force is 1kg or less, there will be no problem. (Fig.10)



HEAT GENERATION

Thermal design of the end product is of paramount importance. Please consider the heat generation of the LED when making the system design. The coefficient of temperature increase per input electric power is affected by the thermal resistance of the circuit board and density of LED placement on the board, as well as other components. It is necessary to avoid intense heat generation and operate within the maximum ratings given in this specification.

The operating current should be decided after considering the ambient maximum temperature of LEDs.

•CHEMICAL RESISTANCE

- 1) Avoid exposure to chemicals as it may attack the LED surface and cause discoloration.
- 2) When washing is required, refer to the following table for the proper chemical to be sued. (Immersion time: within 3 minutes at room temperature.)

SOLVENT	ADAPTABILITY
Freon TE	\odot
Chlorothene	X
Isopropyl Alcohol	\odot
Thinner	X
Acetone	×
Trichloroethylene	X

 \odot --Usable \times --Do not use.

NOTE: Influences of ultrasonic cleaning of the LED resin body differ depending on such factors as the oscillator output, size of the PC board and the way in which the LED is mounted. Therefore, ultrasonic cleaning should only be performed after confirming there is no problem by conducting a test under practical.



LQR5VELPG6W447G

REV:A/0

OTHERS


- 1) Care must be taken to ensure that the reverse voltage will not exceed the absolute maximum rating when using the LEDs with matrix drive.
- 2) Flashing lights have been known to cause discomfort in people; you can prevent this by taking precautions during use. Also, people should be cautious when using equipment that has had LEDs incorporated into it.
- 3) The LEDs described in this brocVEe are intended to be used for ordinary electronic equipment (such as office equipment, communications equipment, measurement instruments and household appliances). Consult PARA's sales staff in advance for information on the applications in which exceptional quality and reliability are required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as for airplanes, aerospace, submersible repeaters, nuclear reactor control systems, automobiles, traffic control equipment, life support systems and safety devices).
- 4) User shall not reverse engineer by disassembling or analysis of the LEDs without having prior written consent from PARA. When defective LEDs are found, the User shall inform PARA directly before disassembling or analysis.
- 5) The formal specifications must be exchanged and signed by both parties before large volume purchase begins.
- 6) The appearance and specifications of the product may be modified for improvement without notice.



LQR5VELPG6W447G

REV:A / 0

LED Lamps: Part Number Rules





LQR5VELPG6W447G

REV:A/0

BIN Code List

DominantWavelength(λ D),				
	Unit:nm@20mA			
VE				
Bin Code Min Max				
О7	618	621		
O8 621 624				
R1	624	629		
R2	629	634		

Tolerance of each bin are ± 1 nm

Unit:nm@20mA			
LPG6			
Bin Code Min Max			
D4B	517.5	520.0	
D5A	520.0	522.5	
D5B	522.5	525.0	
D6A	525.0	527.5	
-			

DominantWavelength(λD),

Tolerance of each bin are ± 1 nm

Luminous Intensity(IV),Unit:mcd@20mA				
	VE			
Bin Code	Bin Code Min Max			
Q	222.0	310.8		
R	310.8	435.1		
S	435.1	609.1		
Т	609.1	852.7		
U	852.7	1193.8		

Tolerance of each bin are±15%

Luminous Intensity(IV),Unit:mcd@20mA				
	LPG6			
Bin Code Min Max				
E	550			
F	550	770		
G	1080			
HA	1080	1295		
НВ	1295	1510		

Tolerance of each bin are±15%