


NCE P-Channel Enhancement Mode Power MOSFET



Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
NCE30P25Q	NCE30P25Q	DFN3.3X3.3-8L	Ø330mm	12mm	5000 units

Absolute Maximum Ratings (T_A=25℃ unless otherwise noted)

Parameter	Symbol	Limit	Unit	
Drain-Source Voltage	Vds	-30	V	
Gate-Source Voltage	Vgs	±20	V	
Drain Current-Continuous	Ι _D	-25	A	
Drain Current-Continuous(T _C =100℃)	I _D (100℃)	-17.7	A	
Drain Current-Pulsed (Note 1)	I _{DM}	-100	A	
Maximum Power Dissipation	PD	40	W	
Operating Junction and Storage Temperature Range	T _J ,T _{STG}	-55 To 150	°C	

Thermal Characteristic

Thermal Resistance, Junction-to-Case (Note 2)	R _{ejc}	3.13	°C/W
---	------------------	------	------



Electrical Characteristics (T_A=25 $^\circ\!\!\mathrm{C}$ unless otherwise noted)

Parameter Symbol		Condition	Min	Тур	Max	Unit
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =-250µA	-30	-33	-	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-30V,V _{GS} =0V	-	-	-1	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V		-	±100	nA
On Characteristics (Note 3)						
Gate Threshold Voltage	V _{GS(th)}	$V_{DS}=V_{GS}$, $I_{D}=-250\mu A$	-1	-1.7	-2.2	V
		V _{GS} =-10V, I _D =-15A	-	8.9	11	mΩ
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =-4.5V, I _D =-15A	-	15	20	mΩ
Gate resistance	R _G			5.2	-	Ω
Forward Transconductance	g fs	V _{DS} =-5V,I _D =-15A		-	-	S
Dynamic Characteristics (Note4)	·		•			
Input Capacitance	C _{lss}		-	1632	-	PF
Output Capacitance	C _{oss}	– V _{DS} =-15V,V _{GS} =0V, – – F=1.0MHz –		227	-	PF
Reverse Transfer Capacitance	C _{rss}			178	-	PF
Switching Characteristics (Note 4)					•	
Turn-on Delay Time	t _{d(on)}		-	12	-	nS
Turn-on Rise Time	tr	V _{DD} =-15V, I _D =-15A,	-	10	-	nS
Turn-Off Delay Time	t _{d(off)}	V_{GS} =-10V, R_{GEN} =1 Ω	-	25	-	nS
Turn-Off Fall Time	t _f		-	13	-	nS
Total Gate Charge	Qg		-	45.6	-	nC
Gate-Source Charge	Q _{gs}	V _{DS} =-15V,I _D =-20A,V _{GS} =-10V	-	4.6	-	nC
Gate-Drain Charge	Q _{gd}	1	-	11.1	-	nC
Drain-Source Diode Characteristics	•					
Diode Forward Voltage (Note 3)	V _{SD}	V _{GS} =0V,I _S =-15A	-	-	-1.2	V

Notes:

- 1. Repetitive Rating: Pulse width limited by maximum junction temperature.
- **2.** Surface Mounted on FR4 Board, $t \le 10$ sec.
- **3.** Pulse Test: Pulse Width \leq 300µs, Duty Cycle \leq 2%.
- 4. Guaranteed by design, not subject to production



Typical Electrical and Thermal Characteristics





Figure 1:Switching Test Circuit







Figure 2:Switching Waveforms



-I_D- Drain Current (A) Figure 6 Drain-Source On-Resistance

10

15

5


0


20



http://www.ncepower.com

NCE30P25Q





0.2

0.4

0.6

0.8

1.0

1.2






Figure 13 Safe Operation Area

Figure 14 BV_{DSS} vs Junction Temperature





Figure 15 Normalized Maximum Transient Thermal Impedance




DFN3.3X3.3-8L Package Information






DFN3.3X3.3-8L Part Marking



包装信息

一、载带图纸与产品搭载方向示意图:



二、标签(标签尺寸: 100*60mm或100*50mm)示意图:



说明: 以上标签内容仅作格式, 品种会根据实际印章品名打印。



三、包装信息表(满箱信息)

封装形式	包装方式	盘尺寸	只虛	盘内盒	只内盒	内盒/箱	只焴
PDFN3.3*3.3 -8L	编带	13寸	5000	1	5000	5	25000


四、包装流程图







回流焊曲线





Attention

- Any and all NCE power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your NCE power representative nearest you before using any NCE power products described or contained herein in such applications.
- NCE power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all NCE power products described or contained herein.
- Specifications of any and all NCE power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- NCE power Semiconductor CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all NCE power products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of NCE power Semiconductor CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. NCE power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the NCE power product that you intend to use.
- This catalog provides information as of Sep.2010. Specifications and information herein are subject to change without notice.