


表面安装肖特基二极管
反向电压 20 ~ 200 V
正向电流 1.0 A

Surface Mounted Schottky Barrier Rectifiers
Reverse Voltage 20 ~ 200 V
Forward Current 1.0 A



特征 Features

- 反向漏电流低 Low reverse leakage
- 正向浪涌承受能力强 High forward surge capability
- 高信赖性 High reliability
- 高温焊接保证 High temperature soldering guaranteed:
260°C/10 秒
260°C/10seconds
- 引线和管体皆符合RoHS标准
Lead and body according with RoHS standard
- 型号后缀“-F”标记无卤素产品
Green compound with suffix "-F" on Marking

机械数据 Mechanical Data

- 封装外形:SMAF塑封 Case:SMAFMolded plastic
- 环氧树脂 : UL易燃等级 : 94V-0
Epoxy: UL 94V-0 rate flame retardant
- 引脚 : 镀锡,无铅 Lead: Pure tin plated, lead free

最大值和特性 TA = 25°C 除非另有规定。

Maximum Ratings & Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

参数 Parameter	符号 Symbols	SS12F	SS13F	SS14F	SS15F	SS16F	SS18F	SS110F	SS115F	SS120F	单位 Unit
最大可重复峰值反向电压 Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	80	100	150	200	V
最大均方根电压 Maximum RMS voltage	V _{RMS}	14	21	28	35	42	56	70	105	140	V
最大直流阻断电压 Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	80	100	150	200	V
最大正向平均整流电流 Maximum average forward rectified current	I _{F(AV)}						1.0				A
正向不重复浪涌电流 8.3 ms单一正弦半波 Non-repetitive peak forward surge current 8.3 ms singlehalf sine-wave	I _{FSM}						30				A
最大正向电压 @IF=1.0A Maximum forward voltage	V _F		0.55		0.70		0.85		0.92	0.95	V
最大反向电流 @V _{DC} TA= 25°C Maximum reverse current TA= 100°C	I _R		0.5				0.1				mA
			20				10				
典型热阻 Typical thermal resistance (Note 1)	R _{θJA} R _{θJL}					85					°C/W
						25					
典型结电容 VR=4.0V,f=1MHz Type junction capacitance	C _J					90					pF
工作结温 Operating junction	T _J		-55 --- +125				-55 --- +150				°C
存储温度 Storage temperature rang	T _{STG}					55 --- +150					°C

备注 Note:

1) 安装在PCB板上 , 从PN结到周围环境的热阻。

1) Thermal resistance from junction to ambient , PCB mounted.

特性曲线 Characteristic Curves
