



# 1.FIGURE AND DIMENSIONS(视图及尺寸)



X9357HM-03-N2

XXXXXT-PXX-AXXXX-LXXX-TX  
① ② ③ ④ ⑤

- ① 系列 (Series No)
- ② 材质 (Material) :P-BSN(黄铜镀锡高脚)
- ③ 线规线色 (Wire gauge line color) A:(AWG24-AWG16)  
Circuit:R(red)/B (black) /Y (yellow) /G (green) /  
L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 剥皮镀锡 (Peeled tin plated) T(可定制剥皮长度镀锡)

## 2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	
Circuit2	黄色	
Circuit3	黑色	

## 3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X9357HM-03-N2	1PCS		
2	X9357TF-BSN-H	3PCS		
3	UL1007/20AWG. 红. 黑. 黄色	各1PCS	300MM	
总量				

					ANGLAR	±5°	<b>XKIB</b>	DSND		SCALE: N/A	DRAWING NO. X9357T-BSN-A20RYB-L300-T3		
					L ≤ 4	±0.2		DWN		VIEW:	PART NO.:		
					4 < L ≤ 16	±0.3		CHKD		UNIT: mm/in	DWG NO.:		
					16 < L ≤ 63	±0.4		APPD		SIZE: A4			
					L > 63	±0.5							
MARK					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
REVISIONS												1/1	A0
www.helloxb.com www.helloxb.cn www.xk-dg.cn													