



# TECH PUBLIC —台舟电子—

www.sot23.com.tw

#### **GENERAL FEATURES**


- $V_{DS} = -60V I_D = -3.8 A$
- $R_{DS(ON)} < -98m\Omega$  @  $V_{GS}=10 V$
- $R_{DS(ON)} < -145 \,\mathrm{m}\Omega$  @  $V_{GS} = 4.5 \,\mathrm{V}$

## **Application**


- Load/Power Switching
- Interfacing Switching
- Logic Level Shift

#### Package and Pin Configuration






## Circuit diagram



# Marking:



## Absolute Maximum Ratings (T<sub>A</sub>=25 ℃ unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-Source Voltage		V <sub>DSS</sub>	-60	V
Continuous Drain Current		I <sub>D</sub>	-3.8	А
Pulsed Drain Current	(note1)	I <sub>DM</sub>	-16	А
Gate-Source Voltage		$V_{GSS}$	±20	V
Single Pulse Avalanche Energy	(note2)	E <sub>AS</sub>	36	mJ
Avalanche Current		I <sub>As</sub>	12	А
Power Dissipation (T <sub>C</sub> = 25°C)	(note3)	P <sub>D</sub>	2.3	W
Operating Junction and Storage Temperat	ure Range	T <sub>J</sub> , T <sub>stg</sub>	-55 To 150	°C

## **Thermal Data**

Symbol	Parameter		Value	Unit
Rthj-a	Thermal Resistance Junction-ambient <sup>3</sup>	Max.	40	°C/W



## **Dual P-Channel Enhancement Mode MOSFET**

www.sot23.com.tw

## Electrical Characteristics (Tj=25<sup>°</sup>C unless otherwise noted)

Specifications T <sub>J</sub> = 25°C, ur	less othe	rwise noted					
Dto	0	- 1 - 1111	Value				
Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_{D} = -250\mu A$	-60		/-	V	
Zana Oata Vallana Busin Oamasi		$V_{DS} = -60V$ , $V_{GS} = 0V$ , $T_{J} = 25$ °C	/ <u> </u>		-1		
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{DS} = -60V, V_{GS} = 0V, T_{J} = 150^{\circ}C$	==	-	-100	μΑ	
Gate-Source Leakage	I <sub>GSS</sub>	$V_{GS}$ = $\pm 20V$	- /	\	±100	nA	
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$	-1.0	-1.7	-3.0	٧	
D O O D	_	$V_{GS} = -10V, I_{D} = -4A$	<u></u>	90	98	mΩ	
Drain-Source On-Resistance (Note3)	R <sub>DS(on)</sub>	$V_{GS} = -4.5V, I_D = -3A$		100	145	mΩ	
Dynamic							
Input Capacitance	C <sub>iss</sub>	V <sub>GS</sub> = 0V,	1	976		pF	
Output Capacitance	C <sub>oss</sub>	$V_{DS} = -30V$ ,	-)	70			
Reverse Transfer Capacitance	C <sub>rss</sub>	f = 1.0MHz	/	30			
Total Gate Charge	$Q_g$			24		5	
Gate-Source Charge	$Q_{gs}$	$V_{DD} = -30V, I_{D} = -4A,$ $V_{GS} = -10V$	-	2.2		nC	
Gate-Drain Charge	$Q_{gd}$			3.6			
Turn-on Delay Time	t <sub>d(on)</sub>			10			
Turn-on Rise Time	t <sub>r</sub>	$V_{DD} = -30V, I_{D} = -4A,$		5		ns	
Turn-off Delay Time	t <sub>d(off)</sub>	$R_G = 2.5\Omega$		35			
Turn-off Fall Time	t <sub>f</sub>		==	9			
Drain-Source Body Diode Characteri	stics						
Continuous Body Diode Current	Is	T = 25%C	<del>==</del> :		-3.8	۸	
Pulsed Diode Forward Current	I <sub>SM</sub>	T <sub>C</sub> = 25°C			-16	Α	
Body Diode Voltage	V <sub>SD</sub>	$T_J = 25^{\circ}C$ , $I_{SD} = -4A$ , $V_{GS} = 0V$			-1.2	٧	
Reverse Recovery Time	t <sub>rr</sub>	I <sub>F</sub> = -4A,		36		ns	
Reverse Recovery Charge	Q <sub>rr</sub>	$di_F/dt = 100A/\mu s$		38		nC	







www.sot23.com.tw

#### **Typical Electrical and Thermal Characteristics**

Figure 1. Output Characteristics

20

-10V
-6V
-4.5V
-3.5V

-3.5V

-3V

-V<sub>DS</sub>, Drain-to-Source Voltage (V)

Figure 3. On-Resistance vs. Drain Current




Figure 5. Threshold Voltage vs. Junction Temperature




Figure 2. Transfer Characteristics




Figure 4. On-Resistance vs. Junction Temperature





Figure 6. Body Diode Forward Voltage









www.sot23.com.tw

Figure 7. Capacitance




Figure 9. Transient Thermal Impedance




Figure 8. Gate Charge






Figure 10. Safe Operating Area





www.sot23.com.tw

## **SOP-8 Package Information**



Symbol	<b>Dimensions In Millimeters</b>		Dimensions In Inches		
	Min.	Max.	Min.	Max.	
Α	1.350	1.750	0.053	0.069	
A1	0.100	0.250	0.004	0.010	
A2	1.350	1.550	0.053	0.061	
b	0.330	0.510	0.013	0.020	
С	0.170	0.250	0.006	0.010	
D	4.700	5.100	0.185	0.200	
E	3.800	4.000	0.150	0.157	
E1	5.800	6.200	0.228	0.244	
е	1.270(BSC)		0.050	(BSC)	
L	0.400	1.270	0.016	0.050	
θ	0°	8°	0°	8°	