




1.FIGURE AND DIMENSIONS(视图及尺寸)



X1002H-XXE-NOHF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
 ① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
 Circuit:R(red)/B (black) /Y (yellow) /G (green) /
 L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

| A | 颜色 | B |
|---|----|---|
| 1 | 红色 | 5 |
| 2 | 黄色 | 4 |
| 3 | 黄色 | 3 |
| 4 | 黑色 | 2 |

3. MATERIAL(材料)

| 标志 | 料号 | 单用量 | 备注 | 总用量 |
|----|--------------------------|-------|-------|-----|
| 1 | X1002H-04E-N OHF | 2PCS | | |
| 2 | X1002T-PSN-E | 8PCS | | |
| 3 | UL3302/30AWG. 红.黑.绿.黄 | 各1PCS | 200MM | |
| 总量 | | | | |

| | | | | | | | | | | | | | | |
|-----------------------------------------------|--|--|--|--|--|------------------------|------|---------------------------------------|------|--|-------------|---------------------------------|----------|-----|
| | | | | | | ANGLAR | ±5° | XKIB | DSND | | SCALE: N/A | DRAWING NO. | | |
| | | | | | | L ≤ 4 | ±0.2 | | DWN | | VIEW: | X1002T-PSN-A28RYB-L200-X1002T-Z | | |
| | | | | | | 4 < L ≤ 16 | ±0.3 | | CHKD | | UNIT: mm/in | PART NO.: | | |
| | | | | | | 16 < L ≤ 63 | ±0.4 | | APPD | | SIZE: A4 | DWG NO.: | | |
| | | | | | | L > 63 | ±0.5 | | | | | | | |
| MARK | | | | | | UNSPECIFIED TOLERANCES | | XKB INDUSTRIAL PRECISION CO., LIMITED | | | WEIGHT | SHEET | REVISION | |
| REVISIONS | | | | | | | | | | | | | | 1/1 |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn | | | | | | | | | | | | | | |