


Dual Common Source SiC MOSFET Power Module

Product Overview

The MSCSM170DUM23T3AG device is a 1700V/124A dual common source silicon carbide (SiC) MOSFET power module.



Notes:

1. All ratings at $T_j = 25\text{ }^\circ\text{C}$, unless otherwise specified.
2. All multiple inputs and outputs must be shorted together 13/14/15/16; 18/19/20/22/23/25/26/27/28; 29/30/31/32



These devices are sensitive to electrostatic discharge. Proper handling procedures must be followed.

Features

The following are the key features of MSCSM170DUM23T3AG device:

- SiC Power MOSFET
 - Low $R_{DS(on)}$
 - High temperature performance
- Kelvin source for easy drive
- Low stray inductance
- High level of integration
- Aluminum Nitride (AlN) substrate for improved thermal performance
- Internal thermistor for temperature monitoring

Benefits

The following are the benefits of MSCSM170DUM23T3AG device:

- Outstanding performance at high frequency operation
- Direct mounting to heatsink (isolated package)
- Low junction-to-case thermal resistance
- Low profile
- RoHS compliant
- Solderable terminals both for power and signal for easy PCB mounting

Application

The following are the applications of MSCSM170DUM23T3AG device:

- AC switches

1. Electrical Specifications

This section provides the electrical specifications of the MSCSM170DUM23T3AG device.

1.1 SiC MOSFET Characteristics (Per SiC MOSFET)

The following table lists the absolute maximum ratings of MSCSM170DUM23T3AG device.

Table 1-1. Absolute Maximum Ratings

| Symbol | Parameter | Maximum Ratings | Unit |
|--------------|----------------------------|----------------------------------|-----------|
| V_{DSS} | Drain-Source voltage | 1700 | V |
| I_D | Continuous drain current | $T_C = 25\text{ }^\circ\text{C}$ | 124 |
| | | $T_C = 80\text{ }^\circ\text{C}$ | 98 |
| I_{DM} | Pulsed drain current | 240 | |
| V_{GSmax} | Gate-Source voltage | -10/23 | V |
| $R_{DS(on)}$ | Drain-Source ON resistance | 22.5 | $m\Omega$ |
| P_D | Power dissipation | $T_C = 25\text{ }^\circ\text{C}$ | 602 |

The following table lists the electrical characteristics of MSCSM170DUM23T3AG device.

Table 1-2. Electrical Characteristics

| Symbol | Characteristic | Test Conditions | Min. | Typ. | Max. | Unit | |
|--------------|---------------------------------|--|-----------------------------------|------|------|---------|-----------|
| I_{DSS} | Zero gate voltage drain current | $V_{GS} = 0V$ $V_{DS} = 1700V$ | — | 20 | 200 | μA | |
| $R_{DS(on)}$ | Drain-Source on resistance | $V_{GS} = 20V$ $I_D = 60A$ | $T_J = 25\text{ }^\circ\text{C}$ | — | 17.5 | 22.5 | $m\Omega$ |
| | | | $T_J = 175\text{ }^\circ\text{C}$ | — | 31 | — | |
| $V_{GS(th)}$ | Gate threshold voltage | $V_{GS} = V_{DS}$ $I_D = 5\text{ mA}$ | 1.8 | 3.2 | — | V | |
| I_{GSS} | Gate-Source leakage current | $V_{GS} = 20V$ $V_{DS} = 0V$ | — | — | 200 | nA | |

The following table lists the dynamic characteristics of MSCSM170DUM23T3AG device.

Table 1-3. Dynamic Characteristics

| Symbol | Characteristic | Test Conditions | Min. | Typ. | Max. | Unit |
|---------------------|-------------------------------------|---|------|------|------|------|
| C _{iss} | Input capacitance | V _{GS} = 0V | — | 6600 | — | pF |
| C _{oss} | Output capacitance | V _{DS} = 1000V | — | 300 | — | |
| C _{rss} | Reverse transfer capacitance | f = 1 MHz | — | 20 | — | |
| Q _g | Total gate charge | V _{GS} = -5V/20V | — | 356 | — | nC |
| Q _{gs} | Gate-Source charge | V _{Bus} = 850V | — | 98 | — | |
| Q _{gd} | Gate-Drain charge | I _D = 60A | — | 54 | — | |
| T _{d(on)} | Turn-on delay time | V _{GS} = -5V/20V | — | 24 | — | ns |
| T _r | Rise time | V _{Bus} = 900V | | 17 | | |
| T _{d(off)} | Turn-off delay time | I _D = 100A | | 35 | | |
| T _f | Fall time | R _{Gon} = 2.4Ω R _{Goff} = 1.4Ω | | 19 | | |
| E _{on} | Turn-on energy | V _{GS} = -5V/20V | — | 2.6 | — | mJ |
| E _{off} | Turn-off energy | V _{Bus} = 900V I _D = 100A R _{Gon} = 2.4Ω R _{Goff} = 1.4Ω | — | 0.33 | — | |
| R _{Gint} | Internal gate resistance | | — | 2.93 | — | Ω |
| R _{thJC} | Junction-to-case thermal resistance | | — | — | 0.25 | °C/W |

The following table lists the body diode ratings and characteristics of MSCSM170DUM23T3AG device.

Table 1-4. Body Diode Ratings and Characteristics

| Symbol | Characteristic | Test Conditions | Min. | Typ. | Max. | Unit |
|-----------------|--------------------------|---|------|------|------|------|
| V _{SD} | Diode forward voltage | V _{GS} = 0V I _{SD} = 60A | — | 3.7 | — | V |
| | | V _{GS} = -5V I _{SD} = 60A | — | 3.9 | — | |
| t _{rr} | Reverse recovery time | I _{SD} = 60A | — | 27 | — | ns |
| Q _{rr} | Reverse recovery charge | V _{GS} = -5V | — | 1300 | — | nC |
| I _{rr} | Reverse recovery current | V _R = 900V di _F /dt = 2000A/μs | — | 92 | — | A |

1.2 Thermal and Package Characteristics

The following table lists the thermal and package characteristics of the MSCSM170DUM23T3AG device.

Table 1-5. Thermal and Package Characteristics

| Symbol | Characteristic | Min. | Max. | Unit | | |
|-------------------|--|-------------|-----------------------|------|---|-----|
| V _{ISOL} | RMS isolation voltage, any terminal to case t = 1 min, 50 Hz/60 Hz | 4000 | — | V | | |
| T _J | Operating junction temperature range | –40 | 175 | °C | | |
| T _{JOP} | Recommended junction temperature under switching conditions | –40 | T _{Jmax} –25 | | | |
| T _{STG} | Storage case temperature | –40 | 125 | | | |
| T _C | Operating case temperature | –40 | 125 | | | |
| Torque | Mounting torque | To heatsink | M4 | 2 | 3 | N.m |
| Wt | Package weight | — | 110 | g | | |

The following table lists the temperature sensor NTC of the MSCSM170DUM23T3AG device.

Table 1-6. Temperature Sensor NTC

| Symbol | Characteristic | Min. | Typ. | Max. | Unit |
|-----------------------------------|----------------------------|-------------------------|------|------|------|
| R ₂₅ | Resistance at 25 °C | — | 50 | — | kΩ |
| ΔR ₂₅ /R ₂₅ | — | — | 5 | — | % |
| B _{25/85} | T ₂₅ = 298.15 K | — | 3952 | — | K |
| ΔB/B | — | T _C = 100 °C | 4 | — | % |

$$R_T = \frac{R_{25}}{\exp\left[B_{25/85}\left(\frac{1}{T} - \frac{1}{T_{25}}\right)\right]}$$

T: Thermistor temperature
R_T: Thermistor value at T

Note: See [APT0406—Using NTC Temperature Sensor Integrated into Power Module](#) for more information.

1.3 Typical SiC MOSFET Performance Curve (Per SiC MOSFET)

This section shows the typical SiC MOSFET performance curves of the MSCSM170DUM23T3AG device.

Figure 1-1. Junction-to-Heatsink Thermal Impedance




Figure 1-2. Output Characteristics, $T_J = 25^\circ\text{C}$




Figure 1-3. Output Characteristics, $T_J = 175^\circ\text{C}$




Figure 1-4. Normalized $R_{DS(on)}$ vs. Temperature




Figure 1-5. Transfer Characteristics




Figure 1-6. Switching Energy vs. R_g




Figure 1-7. Switching Energy vs. Current




Figure 1-8. Capacitance vs. Drain Source Voltage




Figure 1-9. Gate Charge vs. Gate Source Voltage




Figure 1-10. Body Diode Characteristics, $T_J = 25^\circ\text{C}$




Figure 1-11. 3rd Quadrant Characteristics, $T_J = 25^\circ\text{C}$




Figure 1-12. Body Diode Characteristics, $T_J = 175^\circ\text{C}$




Figure 1-13. 3rd Quadrant Characteristics, $T_J = 175^\circ\text{C}$





Figure 1-14. Operating Frequency vs. Drain Current




2. Package Specifications

The following section shows the package specification of the MSCSM170DUM23T3AG device.

2.1 Package Outline

The following figure shows the package outline drawing of the MSCSM170DUM23T3AG device. The dimensions in the following figure are in millimeters.

Figure 2-1. Package Outline Drawing



Note: See application note [AN3500A—Mounting Instructions for SP1F and SP3F Power Modules](#) for more information.

3. Revision History

| Revision | Date | Description |
|----------|---------|------------------|
| A | 12/2021 | Initial Revision |

The Microchip Website

Microchip provides online support via our website at www.microchip.com/. This website is used to make files and information easily available to customers. Some of the content available includes:

- **Product Support** – Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- **General Technical Support** – Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip design partner program member listing
- **Business of Microchip** – Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

Product Change Notification Service

Microchip's product change notification service helps keep customers current on Microchip products. Subscribers will receive email notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, go to www.microchip.com/pcn and follow the registration instructions.

Customer Support

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Embedded Solutions Engineer (ESE)
- Technical Support

Customers should contact their distributor, representative or ESE for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in this document.

Technical support is available through the website at: www.microchip.com/support

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.

Legal Notice

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at www.microchip.com/en-us/support/design-help/client-support-services.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Klear, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, IntellIMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet- Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, NVM Express, NVMe, Omniscient Code Generation, PICDEM, PICDEM.net, PICKit, PICTail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQL, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, Symmcom, and Trusted Time are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2021, Microchip Technology Incorporated and its subsidiaries. All Rights Reserved.

ISBN: 978-1-5224-9528-4

Quality Management System

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Worldwide Sales and Service

| AMERICAS | ASIA/PACIFIC | ASIA/PACIFIC | EUROPE |
|---|---|--|---|
| <p>Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Tel: 480-792-7277 Technical Support: www.microchip.com/support Web Address: www.microchip.com</p> <p>Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455</p> <p>Austin, TX Tel: 512-257-3370</p> <p>Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088</p> <p>Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075</p> <p>Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924</p> <p>Detroit Novi, MI Tel: 248-848-4000</p> <p>Houston, TX Tel: 281-894-5983</p> <p>Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380</p> <p>Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800</p> <p>Raleigh, NC Tel: 919-844-7510</p> <p>New York, NY Tel: 631-435-6000</p> <p>San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270</p> <p>Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078</p> | <p>Australia - Sydney Tel: 61-2-9868-6733</p> <p>China - Beijing Tel: 86-10-8569-7000</p> <p>China - Chengdu Tel: 86-28-8665-5511</p> <p>China - Chongqing Tel: 86-23-8980-9588</p> <p>China - Dongguan Tel: 86-769-8702-9880</p> <p>China - Guangzhou Tel: 86-20-8755-8029</p> <p>China - Hangzhou Tel: 86-571-8792-8115</p> <p>China - Hong Kong SAR Tel: 852-2943-5100</p> <p>China - Nanjing Tel: 86-25-8473-2460</p> <p>China - Qingdao Tel: 86-532-8502-7355</p> <p>China - Shanghai Tel: 86-21-3326-8000</p> <p>China - Shenyang Tel: 86-24-2334-2829</p> <p>China - Shenzhen Tel: 86-755-8864-2200</p> <p>China - Suzhou Tel: 86-186-6233-1526</p> <p>China - Wuhan Tel: 86-27-5980-5300</p> <p>China - Xian Tel: 86-29-8833-7252</p> <p>China - Xiamen Tel: 86-592-2388138</p> <p>China - Zhuhai Tel: 86-756-3210040</p> | <p>India - Bangalore Tel: 91-80-3090-4444</p> <p>India - New Delhi Tel: 91-11-4160-8631</p> <p>India - Pune Tel: 91-20-4121-0141</p> <p>Japan - Osaka Tel: 81-6-6152-7160</p> <p>Japan - Tokyo Tel: 81-3-6880-3770</p> <p>Korea - Daegu Tel: 82-53-744-4301</p> <p>Korea - Seoul Tel: 82-2-554-7200</p> <p>Malaysia - Kuala Lumpur Tel: 60-3-7651-7906</p> <p>Malaysia - Penang Tel: 60-4-227-8870</p> <p>Philippines - Manila Tel: 63-2-634-9065</p> <p>Singapore Tel: 65-6334-8870</p> <p>Taiwan - Hsin Chu Tel: 886-3-577-8366</p> <p>Taiwan - Kaohsiung Tel: 886-7-213-7830</p> <p>Taiwan - Taipei Tel: 886-2-2508-8600</p> <p>Thailand - Bangkok Tel: 66-2-694-1351</p> <p>Vietnam - Ho Chi Minh Tel: 84-28-5448-2100</p> | <p>Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393</p> <p>Denmark - Copenhagen Tel: 45-4485-5910 Fax: 45-4485-2829</p> <p>Finland - Espoo Tel: 358-9-4520-820</p> <p>France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79</p> <p>Germany - Garching Tel: 49-8931-9700</p> <p>Germany - Haan Tel: 49-2129-3766400</p> <p>Germany - Heilbronn Tel: 49-7131-72400</p> <p>Germany - Karlsruhe Tel: 49-721-625370</p> <p>Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44</p> <p>Germany - Rosenheim Tel: 49-8031-354-560</p> <p>Israel - Ra'anana Tel: 972-9-744-7705</p> <p>Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781</p> <p>Italy - Padova Tel: 39-049-7625286</p> <p>Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340</p> <p>Norway - Trondheim Tel: 47-72884388</p> <p>Poland - Warsaw Tel: 48-22-3325737</p> <p>Romania - Bucharest Tel: 40-21-407-87-50</p> <p>Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91</p> <p>Sweden - Gothenberg Tel: 46-31-704-60-40</p> <p>Sweden - Stockholm Tel: 46-8-5090-4654</p> <p>UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820</p> |