<u>ElecSuper</u>

SuperESD - CDSOD323-T05C

1. Description

The CDSOD323-T05C is Transient Voltage Suppressor that designed to protect components which are connected to data and transmission lines against electrostatic discharge (ESD), electrical fast transient (EFT), and lightning. All pins are rated to withstand 25kV ESD pulses using the IEC61000-4-2 air discharge method.

2. Features

- IEC 61000-4-2 Level 4 ESD Protection
 - ±25kV Contact Discharge
 - ±25kV Air Discharge
- 300W Peak pulse Power (8/20us)
- Low clamping voltage

- Working voltage: 5.0V
- Low leakage current
- RoHS compliant
- Protecting one bi-directional lines
- Junction capacitance: 0.8pF Typ.

3. Applications

- Control & monitoring systems
- Portable electronics
- Servers, notebooks, and desktop PCs
- Set-top box
- Communication systems

4. Ordering Information

Part Number	Package Marki	Marking	Material	Packing	Quantity	Flammability	Reel
i artivaribei	T dendge	Marking	Material	T doking	per reel	Rating	Size
CDSOD323-T05C	SOD 333	AC	Halogen	Tape &	3,000	UL 94V-0	7
CD30D323-105C	30D-323 AC	AC	free	Reel	PCS		inches

Table-1 Ordering information

5. Pin Configuration and Functions

Pin	Name	Description	Outline	Circuit Diagram	
1	IO1	Connect to IO			
2	IO2	Connect to IO			
Table-2 Pin configuration					

6. Specification

6.1. Absolute Maximum rating

Over operating free-air temperature range (unless otherwise noted)

Parameters	Symbol	Min.	Max.	Unit
Peak pulse power (tp=8/20us)@25°C	P _{pk}	-	300	W
Peak pulse current (tp=8/20us)@25°C	I _{PP}		15	А
ESD (IEC61000-4-2 air discharge) @25°C	V _{ESD}	-	±25	kV
ESD (IEC61000-4-2 contact discharge) @25°C	V_{ESD}	-	±25	kV
Junction temperature	TJ	-	150	°C
Operating temperature	T _{OP}	-40	125	°C
Storage temperature	T _{STG}	-55	150	°C
Lead temperature	TL	-	260	°C

Table-3 Absolute Maximum rating


6.2. Electrical Characteristics

At TA = 25°C ι	unless otherwise noted
----------------	------------------------

Parameter	Symbol	Conditions	Min.	Тур.	Max.	Units
Reverse Stand-off Voltage	V _{RWM}				5.0	V
Reverse Breakdown Voltage	V_{BR}	IT=1mA	6.5			V
Reverse Leakage Current	I _R	V _{RWM} =5.0V			1	uA
Clamping Voltage	Vc	I _{PP} =1A; tp=8/20us			8	V
Clamping Voltage	Vc	I _{PP} =15A; tp=8/20us			20	V
Junction Capacitance	CJ	I/O to GND; V _R =0V; f=1MHz		0.8		pF

Table-4 Electrical Characteristics


Symbol	Parameters
V _{RWM}	Peak Reverse Working Voltage
I _R	Reverse Leakage Current @ V _{RWM}
V _{BR}	Breakdown Voltage @ I⊤
Ι _Τ	Test Current
IPP	Maximum Reverse Peak Pulse Current
Vc	Clamping Voltage @ IPP






www.elecsuper.com

7. Typical Characteristic




8. Typical Application



Typical Interface Application




9. Dimension



Symbol	Dimensions i	n Millimeters	Dimensions in Inches			
	Min.	Max.	Min.	Max.		
A		1.000		0.039		
A1	0.000	0.100	0.000	0.004		
A2	0.800	0.900	0.031	0.035		
b	0.250	0.350	0.010	0.014		
С	0.080	0.150	0.003	0.006		
D	1.200	1.400	0.047	0.055		
E	1.600	1.800	0.063	0.071		
E1	2.550	2.750	0.100	0.108		
L	0.475	SREF	0.019REF			
L1	0.250	0.400	0.010	0.016		
θ	0°	8°	0°	8°		

Table-6 product dimensions

10. Recommended Land Pattern



Note:

- 1. Controlling dimension: in millimeters
- 2. General tolerance: ± 0.05 mm
- 3. The pad layout is for reference only
- 4. Unit: mm

ElecSuper

DISCLAIMER

ELECSUER PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with ElecSuper products. You are solely responsible for

(1) selecting the appropriate ElecSuper products for your application;

(2) designing, validating and testing your application;

(3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. ElecSuper grants you permission to use these resources only for development of an application that uses the ElecSuper products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other ElecSuper intellectual property right or to any third party intellectual property right. ElecSuper disclaims responsibility for, and you will fully indemnify ElecSuper and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. ElecSuper's products are provided subject to ElecSuper's Terms of Sale or other applicable terms available either on www.elecsuper.com or provided in conjunction with such ElecSuper products. ElecSuper's provision of these resources does not expand or otherwise alter ElecSuper's applicable warranties or warranty disclaimers for ElecSuper products.

