






WITH CAP




Specifications:

- 规格:  
 Voltage rating: 50V AC/DC  
 额定电压: 50V AC/DC  
 Current rating: 0.5A AC/DC  
 额定电流: 0.5A AC/DC  
 Withstanding voltage: 250V AC/minute  
 耐受电压: 250V AC/分钟  
 Temperature range: -40°C +105°C  
 温度范围: -40°C +105°C  
 Insulation resistance: 500MΩ  
 绝缘电阻: 500MΩ  
 Contact resistance: 100mΩ  
 接触电阻: 100mΩ




WITH CAP

SECT:K-K



Recommended PCB Layout  
 General Tolerance: ±0.05



X0815 W R S - XX A S - 9T V01

- ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Stright 90°
4. Welding Way: S-SMT
5. Row No. Pin No: XX-10-100Pin
6. Category: A-6.7mm Height
7. Special No: S-With positioning column
8. Material: 9T-PA9T UL94V-0  
CAP Material: PA6T UL94V-0
9. Plating: Gold Plated 4u" MIN

Poles	Dimensions(mm)						
	A	B	C	D	E	F	G
10	5.00	6.70	13.00	3.20	6.40	1.00	16.00
20	9.00	10.70	17.00	7.20	10.40	5.00	20.00
30	13.00	14.70	21.00	11.20	14.40	9.00	24.00
40	17.00	18.70	25.00	15.20	18.40	13.00	28.00
50	21.00	22.70	29.00	19.20	22.40	17.00	32.00
60	25.00	26.70	33.00	23.20	26.40	21.00	36.00
70	29.00	30.70	37.00	27.20	30.40	25.00	40.00
80	33.00	34.70	41.00	31.20	34.40	29.00	44.00
90	37.00	38.70	45.00	35.20	38.40	33.00	48.00
100	41.00	42.70	49.00	39.20	42.40	37.00	52.00

X0815WRS-XXAS-9TV01	PA9T	Phosphor Bronze	X0815FVS-A
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND		SCALE: N/A	MODEL TYPE: 0.8mm BTB Connector
DWN		VIEW:	PART NO.: X0815WRS-XXAS-9TV01
CHKD		UNIT: mm/in	DWG NO.: X-X0815WRS-XXAS-9TV01
APPD		SIZE: A4	WEIGHT
KXB INDUSTRIAL PRECISION CO., LIMITED			SHEET
			REVISION
			1/1
			A0



ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn