Reference Specification

Type EA Safety Standard Certified Resin Molding SMD Type Ceramic Capacitors for General Purpose

Product specifications in this catalog are as of Apr. 2022, and are subject to change or obsolescence without notice.


Please consult the approval sheet before ordering.Please read rating and Cautions first.

1. OPERATING VOLTAGE

 Do not apply a voltage to a safety standard certified product that exceeds the rated voltage as called out in the specifications. Applied voltage between the terminals of a safety standard certified product shall be less than or equal to the rated voltage (+ 10%). When a safety standard certified product is used as a DC voltage product, the AC rated voltage value becomes the DC rated voltage value. (Example:AC250V (r.m.s.) rated product can be used as DC250V (+ 10%) rated product.) If both AC rated voltage and DC rated voltage are specified, apply the voltage lower than the respective rated voltage.

1-1) When a safety standard certified product is used in a circuit connected to a commercial power supply, ensure that the applied commercial power supply voltage including fluctuation should be less than 10% above its rated voltage.

- 1-2) When using a safety standard certified product as a DC rated product in circuits other than those connected to a commercial power supply.
- When AC voltage is superimposed on DC voltage, the zero-to-peak voltage shall not exceed the rated DC voltage. When AC voltage or pulse voltage is applied, the peak-to-peak voltage shall not exceed the rated DC voltage



(E:Maximum possible applied voltage.)

2) Abnormal voltages (surge voltage, static electricity, pulse voltage, etc.) shall not exceed the rated DC voltage.

2. OPERATING TEMPERATURE AND SELF-GENERATED HEAT

Keep the surface temperature of a capacitor below the upper limit of its rated operating temperature range. Be sure to take into account the heat generated by the capacitor itself.

When the capacitor is used in a high-frequency current, pulse current or the like, it may have the selfgenerated heat due to dielectric-loss. Applied voltage should be the load such as self-generated heat is within 20 °C on the condition of atmosphere temperature 25 °C. When measuring, use a thermocouple of small thermal capacity-K of ϕ 0.1mm and be in the condition where capacitor is not affected by radiant heat of other components and wind of surroundings. Excessive heat may lead to deterioration of the capacitor's characteristics and reliability.(Never attempt to perform measurement with the cooling fan running. Otherwise, accurate measurement cannot be ensured.)

3. TEST CONDITION FOR WITHSTANDING VOLTAGE

1) TEST EQUIPMENT

Test equipment for AC withstanding voltage should be used with the performance of the wave similar to 50/60 Hz sine wave.

If the distorted sine wave or over load exceeding the specified voltage value is applied, the defective may be caused.


2) VOLTAGE APPLIED METHOD

When the withstanding voltage is applied, capacitor's lead or terminal should be firmly connected to the out-put of the withstanding voltage test equipment, and then the voltage should be raised from near zero to the test voltage.

If the test voltage without the raise from near zero voltage would be applied directly to capacitor, test voltage should be applied with the *zero cross. At the end of the test time, the test voltage should be reduced to near zero, and then capacitor's lead or terminal should be taken off the out-put of the withstanding voltage test equipment.

If the test voltage without the raise from near zero voltage would be applied directly to capacitor, the surge voltage may arise, and therefore, the defective may be caused.

*ZERO CROSS is the point where voltage sine wave pass 0V. - See the right figure -



Soldering

10 - 30 s

ПШ

Preheating

60 - 120 s

Gradual

Cooling

Time

4. FAIL-SAFE When capacitor would be broken, failure may result in a short circuit. Be sure to provide an appropriate fail-safe function like a fuse on your product if failure would follow an electric shock, fire or fume. 5. VIBRATION AND IMPACT Do not expose a capacitor or its leads to excessive shock or vibration during use. 6. SOLDERING 6-1 Reflow Soldering [Standard Conditions for Reflow Soldering] When soldering capacitor, it should be performed in following conditions. Temperature (°C) Soldering temperature $: 230 \sim 260 \ ^\circ C$: 10 \sim 30s 260°C Soldering time 230°C Preheating temperature : 170 °C max. 170℃ 150℃ 6-2 Flow Soldering 130°C When soldering capacitor, it should be performed in following conditions. Soldering temperature : 260 °C max. Soldering time : 5s max. Preheating temperature : 120 °C max. Preheating time : 60s max. 6-3 Soldering Iron When soldering this product to a PCB/PWB, do not exceed the solder heat resistance specification of the capacitor. Subjecting this product to excessive heating could melt the internal junction solder and may result in thermal shocks that can crack the ceramic element. When soldering capacitor with a soldering iron, it should be performed in following conditions. Temperature of iron-tip : 400 °C max. Soldering iron wattage : 50W max. Soldering time : 3.5s max. 7. BONDING, RESIN MOLDING AND COATING Before bonding, molding or coating this product, verify that these processes do not affect the quality of capacitor by testing the performance of the bonded, molded or coated product in the intended equipment. In case of the amount of applications, dryness / hardening conditions of adhesives and molding resins containing organic solvents (ethyl acetate, methyl ethyl ketone, toluene, etc.) are unsuitable, the outer coating resin of a capacitor is damaged by the organic solvents and it may result, worst case, in a short circuit. The variation in thickness of adhesive, molding resin or coating may cause an outer coating resin cracking and/or ceramic element cracking of a capacitor in a temperature cycling.

8. OPERATING AND STORAGE ENVIRONMENT

The insulation coating of capacitors does not form a perfect seal; therefore, do not use or store capacitors in a corrosive atmosphere, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. And avoid exposure to moisture. Before cleaning, bonding, or molding this product, verify that these processes do not affect product quality by testing the performance of a cleaned, bonded or molded product in the intended equipment.

This one is MSL 3 product. So, in order to avoid the absorption of moisture, capacitors are packed in moisture-proof envelope.

Store the capacitors in the following conditions at all times, and use within 6 months after delivered.

Temperature : 10 to 30°C

Humidity : 60% max.

Solder the enclosed capacitors within 168 hours after opening the moisture-proof package.

After opening, store the capacitors in moisture-proof package with a desiccant and HIC card and keep the above condition.

In case the storage period has been exceeded 6 months or the indicator color of a enclosed HIC card has changed when the package has been opened, perform baking ($60^{\circ}C \times 168 \text{ hr}$) before soldering.

9. LIMITATION OF APPLICATIONS

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

- 1. Aircraft equipment
- 2. Aerospace equipment
- 3. Undersea equipment
- 4. Power plant control equipment
- 5. Medical equipment
- 6. Transportation equipment (automotives, trains, ships, etc.)
- 7. Traffic signal equipment
- 8. Disaster prevention / crime prevention equipment
- 9. Data-processing equipment exerting influence on public
- 10. Application of similar complexity and/or reliability requirements to the applications listed in the above.

NOTICE

1. CLEANING (ULTRASONIC CLEANING)

To perform ultrasonic cleaning, observe the following conditions.

Rinse bath capacity : Output of 20 watts per liter or less.

Rinsing time : 5 min maximum.

Do not vibrate the PCB/PWB directly.

Excessive ultrasonic cleaning may lead to fatigue destruction of the terminals.

2. CAPACITANCE CHANGE OF CAPACITORS

· Class 1 capacitors

Capacitance might change a little depending on a surrounding temperature or an applied voltage. Please contact us if you use for the strict time constant circuit.

· Class 2 capacitors

Class 2 capacitors like temperature characteristic B, E and F have an aging characteristic, whereby the capacitor continually decreases its capacitance slightly if the capacitor leaves for a long time. Moreover, capacitance might change greatly depending on a surrounding temperature or an applied voltage. So, it is not likely to be able to use for the time constant circuit. Please contact us if you need a detail information.

3. PERFORMANCE CHECK BY EQUIPMENT

Before using a capacitor, check that there is no problem in the equipment's performance and the specifications.


Generally speaking, Class 2 ceramic capacitors have voltage dependence characteristics and temperature dependence characteristics in capacitance. So, the capacitance value may change depending on the operating condition in an equipment. Therefore, be sure to confirm the apparatus performance of receiving influence in a capacitance value change of a capacitor, such as leakage current and noise suppression characteristic.

Moreover, check the surge-proof ability of a capacitor in the equipment, if needed, because the surge voltage may exceed specific value by the inductance of the circuit.

4. Land Dimensions

The recommendable land dimensions for reflow soldering are follows.

Regarding the "a" dimension, to ensure the creepage distance required by the safety standard applys to your equipment.



Dimension	а	b	С
8.0 x 6.0	8.0	2.2	3.6

- 1.Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- 2. You are requested not to use our product deviating from this specification.

1. Application

This specification is applied to Safety Standard Certified Resin Molding SMD Type Ceramic Capacitors Type EA used for General Electric equipment.

Type EA is Safety Standard Certified capacitors of Class X1, Y1.

Do not use these products in any automotive power train or safety equipment including battery charger for electric vehicles and plug-in hybrids.

Approval standard and recognized number

	8		
	Standard number	*Certified number	AC Rated volt.
UL/cUL	UL60384-14/CSA E60384-14	E37921	
ENEC (SEMKO)	EN60384-14	SE/16008-1A	X1:AC440V(r.m.s.) Y1:AC250V(r.m.s.)
CQC	IEC60384-14	CQC16001142384	11.40200 (1.11.3.)
KTC	KC60384-14	HU03008-16007	

*Above Certified number may be changed on account of the revision of standards and the renewal of certification.

2. Rating

2-1. Operating temperature range −40 ~ +125°C

2-2. Rated voltage

X1 : AC440V(r.m.s.) Y1 : AC250V(r.m.s.) DC1kV

2-3. Part number configuration

ex.)	DK1	<u>E3</u>	EA	102	M	86	<u>R</u>	AH01
	Series	Tempratature	Certified	Capacitance	Capacitance	Body	Package	Individual
		Characteristics	Туре		Tolerance	Dimension		Specification

Series

DK1 denotes resin molding SMD type safety standard recognized ceramic capacitor of class Y1.

Temperature Characteristics

Code	Temperature Characteristics
1X	SL
B3	В
E3	E

Please confirm detailed specification on [Specification and test method].

Certified Type

This denotes safety recognized type name Type EA.

Capacitance

The first two digits denote significant figures : the last digit denotes the multiplier of in $\ensuremath{\mathsf{pF}}$.

ex.) In case of 102 10 X $10^2 = 1000 \text{pF}$

•Capacitance Tolerance Please refer to [Part number list]

Body Dimension

Code	Body Dimension	
86	8.0 X 6.0 mm	

Package

Code	Package	
R	Ф330mm Reel type	

 Individual Specification Murata's control code
 Please refer to Part number list.

ETEA01C

3. Marking	
Certified type	: EA
Capacitance	: Actual value (under 100pF)
Rated Voltage	3 digit system (100pF and over) ∶ X1 440~
Nated Voltage	Y1 250~
Company name code	: 🕑15 (Made in Thailand)
Manufacturing year	: Letter code (The last digit of A.D. year.)
Manufacturing month	: Code
	ex.) YEAR MONTH
	202 <u>2</u> 11(<u>N</u> ovember)
	l2N*l
	*From January to September : "1" to "9",
	October : "O", November : "N", December : "D"
KTC Approval mark	
(Examp	ble)
	EA 102 XI 440~ YI 250~ MI5 2N K

Reference only

4. Pa	4. Part number list								
			0.75+/-0.3 ⊨						
				[1			Unit : mm	Dook
T.C.	Cap.	Cap.	Customer Part Number	Murata Part Number	Dim	ension (m	im)	Body	Pack qty.
	(pF)	Tol.			L	W	T max.	Dimension	(pcs)
SL		±10%		DK11XEA100K86RAH01	11.4±0.5		2.5	86	2500
SL	22			DK11XEA220K86RAH01	11.4±0.5		2.5	86	2500
SL	47			DK11XEA470K86RAH01	11.4±0.5		2.5	86	2500
B		±10%		DK1B3EA101K86RAH01	11.4±0.5		2.5	86	2500
B		±10% ±10%		DK1B3EA221K86RAH01 DK1B3EA331K86RAH01	11.4±0.5 11.4±0.5	6.0±0.5 6.0±0.5	2.5 2.5	86 86	2500 2500
B		±10%		DK1B3EA471K86RAH01	11.4±0.5		2.5	86	2500
B		±10%		DK1B3EA681K86RAH01	11.4±0.5		2.5	86	2500
E		±20%		DK1E3EA102M86RAH01	11.4±0.5		2.5	86	2500
E		±20%		DK1E3EA152M86RAH01	11.4±0.5	6.0±0.5	2.5	86	2500

Specification and test methods

	s and test meth	nods	
No. I	ltem	Specification	Test method
1 Operating	Temperature	-40~+125°C	
2 Appearance	е	No defects or abnormalities	Visual inspection.
3 Dimensions	S	Within the specified dimension.	Using calipers and micrometers.
4 Dielectric s	trength	No defects or abnormalities.	The capacitor shall not be damage when AC4000V(r.m.s.) is applied between the terminations for 60 s.
5 Insulation Resistance	e(I.R.)	6000 MΩ or more	The insulation resistance shall be measured with DC500 \pm 50V within 60 \pm 5 s of charging. The voltage should be applied to the capacitor through a resistor of 1M Ω .
6 Capacitanc		Within the specified tolerance.	Capacitance/D.F. shall be measured at 20°C with the
7 Dissipation		0.025 max.	frequency of 1±0.2kHz and a voltage of AC1±0.2V(r.m.s.).
8 Capacitanc Temperatu Characteris	re	Temp. Coefficient SL: +350 to -1000 ppm/°C (Temp. Range:+20 to +85°C) Cap. Change B:within ±10% E:within ±20/-55% (Temp. Range:-25 to +85°C)	The capacitance measurement shall be made at each stepin table.•Pretreatment for B,E char.Perform the heat treatment at 150+0/-10 °C for 60±5 minand then let sit for 24±2 h at *room condition.Step12345Temp. (°C)20±2-25±220±285±220±2
9 Vibration	Appographes	No marked defect	Solder the capacitor to the Test Jig A (glass epoxy board)
9 Vibration resistance		No marked defect. Within the specified tolerance. Pass the item No.7.	 Solder the capacitor to the Test Jig A (glass epoxy board) shown in "Complement of test method". The capacitor shall be subjected to a simple harmonic motion having a total amplitude of 1.5mm, the frequency being varied uniformly between the approximate limits of 10 and 55Hz. The frequency range, from 10 to 55Hz and return to 10Hz, shall be traversed in approximately 1 min. This motion shall be applied for a period of 2 h in each of 3 mutually perpendicular directions (total of 6h).
10 Solderabilit termination	•	75% of the terminations are to be soldered .	Immerse the capacitor in the solution of ethanol (JIS K 8101) and rosin (JIS K 5902) (25% rosin in weight proportion). Immerse in solder solution for 2±0.5s. Temp. of solder : 245±5°C
11 Soldering	Appearance	No marked defects.	Preheat the capacitor at 150 to 180°C for 90±30s.
effect		Within ±10%	Reflow temp. : 230°C min. (Max. temp. : 260°C)
(Reflow)	I.R.	1000 M Ω or more	Reflow time : 30 ± 10 s.
	Dielectric strength	Pass the item No.4.	 Reflow number of times : 4 times Let sit at *room condition for 24±2 h, then measure. The next reflow porcess should be done after the temperature of the sample has dropped to room temperature. Pretreatment for B,E char. Capacitor should be stored at 150+0/-10°C for 1 h, and apply the AC4000V(r.m.s.) 60s then placed at *room condition for 24±2 h before initial measurements.
12 Adhesive s termination		No removal of the terminations or other defects should occur.	Solder the capacitor to the Test Jig A (glass epoxy board) shown in "Complement of Test method". Then apply 10N force in the direction of the arrow.

ESEA01A

Specification and test methods

No.	Item		Specification	Test method		
13	Temperature cycle	Appearance	No marked defect.	Fix the capacitor to the supporting Test Jig A (glass epoxy board) shown in "Complement of test method".		
	eyele	Capacitance	Within ±15%	Perform the 5 cycles according to the 4 heat treatments		
		change		listed the following table.		
		D.F.	SL :0.025 max.	Step Templ(°C) Time(min.)		
			B,E:0.05 max.	1 -40±3 30±3		
		I.R. Dialactria	3000 MΩ or more	2 Room Temp. 2 to 3 3 125±3 30±3		
		Dielectric strength	Pass the item No.4.	4 Room Temp. 2 to 3		
				Let sit for 24 ± 2 h at *room condition, then measure. •Pretreatment for B,E char. Capacitor should be stored at $150+0/-10^{\circ}$ C for 1 h, and apply the AC4000V(r.m.s.) 60s then placed at *room condition for 2 ± 2 h before initial measurements.		
14	Humidity	Appearance	No marked defect.	Sit the capacitor at 40±2°C and relative humidity 90 to 95% fo		
• •	(Steady	Capacitance	Within ±20%	500+24/-0 h. Remove and let sit for 24±2 h at *room condition		
	state)	change		then measure. • Pretreatment for B,E char. Capacitor should be stored at 150+0/-10°C for 1 h, and apply the AC4000V(r.m.s.) 60s then placed at *room condition for 2		
		D.F.	SL :0.025 max. B,E:0.05 max.	±2 h before initial measurements.		
		I.R.	3000 MΩ or more			
		Dielectric	Pass the item No.4.			
45	L Li una i aliti i	strength	No we award all for at	Apply the rated voltage at $40\pm2^{\circ}$ C and relative humidity		
15	Humidity Loading	Appearance Capacitance	No marked defect. Within ±20%	$_$ Apply the rated voltage at 40±2 C and relative number $_{90}$ to 95% for 500+24/-0 h. Remove and let sit for 24±2 h at		
	Loading	change		*room condition, then measure.		
		D.F.	SL :0.025 max.	Pretreatment for B,E char.		
			B,E:0.05 max.	Capacitor should be stored at 150+0/-10°C for 1 h, and apply		
		I.R.	3000 MΩ or more	the AC4000V(r.m.s.) 60s then placed at *room condition for 2		
		Dielectric strength	Pass the item No.4.	±2 h before initial measurements.		
16	Life	Appearance	No marked defect.	Impulse Voltage test is performed. Each individual capacitor shall be subjected to a 8kV Impulse (the voltage value means zero to peak) for 3 times. Then the capacitors are applied to life test.		
				Front time (T1) = 1.7μs=1.67T Time to half-value (T2) = 50μs		
			Within ±20%			
		<u>change</u> I.R.	3000 MΩ or more			
		Dielectric	Pass the item No.4.	Apply voltage as Table for 1000 h at 125+2/-0°C, relative humidity 50% max.		
		strength				
		0		Applied voltage AC550V(r.m.s.), except that once each hour the voltage is		
				increased to AC1000V(r.m.s.) for 0.1s.		
				Remove and let sit for 24±2 h at *room condition, then measure.		
				 Pretreatment for B,E char. Capacitor should be stored at 150+0/-10°C for 1 h, and apply the AC4000V(r.m.s.) 60s then placed at *room condition for 2 ±2 h before initial measurements. 		
	* "room cond	l lition" Tempe	I rature:15 to 35°C, Relative humidity:45 t	to 75%, Atmosphere pressure:86 to 106kPa		
				· ·		

ESEA01A

Specification and test methods

	14		-
No.	Item	Specification	Test method
17	Passive flammability	The burning time should not be exceeded the time 30s. The tissue paper should not ignite.	The capacitor under test shall be held in the flame in the position which best promotes burning. Each specimen shall only be exposed once to the flame. Time of exposure to flame : 30 s. Length of flame : 12±1mm Gas burner : Length 35mm min. Inside dia : 0.5±0.1mm Outside dia : 0.5±0.1mm Outside dia : 0.9mm max. Gas : Butane gas purity 95% min.
18	Active flammability	The cheese-cloth should not be on fire.	The capacitor shall be individually wrapped in at least one but more than two complete layers of cheesecloth. The capacitor shall be subjected to 20 discharges. The interval between successive discharges shall be 5 s. The UAC shall be maintained for 2 min after the last discharge. $s_1 + t_1 + t_2 + t_2 + t$
	* "room condition" Tem	perature:15 to 35°C, Relative humidity:45 to 75%, /	Atmosphere pressure:86 to 106kPa

ESEA01A



Specification and test methods

