MSCSM70AM19CT1AG

Datasheet

Phase Leg SiC MOSFET Power Module

April 2020





Contents

1 Revision History	1
1.1 Revision 1.0	
2 Product Overview	2
2.1 Features	3
2.1 Features 2.2 Benefits	3
2.3 Applications	3
3 Electrical Specifications	4
3.1 SiC MOSFET Characteristics (Per MOSFET)	
3.2 SiC Schottky Diode Ratings and Characteristics (Per SiC Diode)	
3.3 Thermal and Package Characteristics	6
3.4 Typical SiC MOSFET Performance Curves	7
3.5 Typical SiC Diode Performance Curves	
4 Package Specifications	11
4.1 Package Outline Drawing	



1 Revision History

The revision history describes the changes that were implemented in the document. The changes are listed by revision, starting with the most current publication.

1.1 Revision 1.0

Revision 1.0 was published in April 2020. It is the first publication of this document.



2 Product Overview

The MSCSM70AM19CT1AG device is a phase leg 700 V,124 A full silicon carbide (SiC) power module. Figure 1 • MSCSM70AM19CT1AG Electrical Schematic





Figure 2 • MSCSM70AM19CT1AG Pinout Location



Pins 1/2; 4/5; 7/8 must be shorted together

All ratings at $T_J = 25$ °C, unless otherwise specified.

Caution: These devices are sensitive to electrostatic discharge. Proper handling procedures should be followed.



2.1 Features

The following are key features of the MSCSM70AM19CT1AG device:

- SiC Power MOSFET
 - High speed switching
 - Low R_{DS(on)}
 - Ultra-low loss
- SiC Schottky Diode
 - Zero reverse recovery
 - Zero forward recovery
 - Temperature independent switching behavior
 - Positive temperature coefficient on VF
- Very low stray inductance
- Kelvin source for easy drive
- Internal thermistor for temperature monitoring
- Aluminum nitride (AIN) substrate for improved thermal performance

2.2 Benefits

The following are benefits of the MSCSM70AM19CT1AG device:

- High efficiency converter
- Outstanding performance at high frequency operation
- Direct mounting to heatsink (isolated package)
- Low junction-to-case thermal resistance
- Solderable terminals for power and signal, for easy PCB mounting
- Low profile
- RoHS compliant

2.3 Applications

The MSCSM70AM19CT1AG device is designed for the following applications:

- Welding converters
- Switched mode power supplies
- Uninterruptible power supplies (UPS)
- EV motor and traction drive



3 Electrical Specifications

This section shows the electrical specifications of the MSCSM70AM19CT1AG device.

3.1 SiC MOSFET Characteristics (Per MOSFET)

The following table shows the absolute maximum ratings per MOSFET of the MSCSM70AM19CT1AG device. Table 1 • Absolute Maximum Ratings

Symbol	Parameter	Max Ratings	Unit	
V _{DSS}	Drain-source voltage	urce voltage		
I _D	Continuous drain current	124 ¹	А	
		98 ¹		
I _{DM}	Pulsed drain current	250		
V _{GS}	Gate-source voltage		-10/25	v
R _{DSon}	Drain source ON resistance	19	mΩ	
P _D	Power dissipation	T _C = 25 °C	365	w

Note:

1. Specification of SiC MOSFET device but output current must be limited due to size of power connectors.

The following table shows the electrical characteristics per MOSFET of the MSCSM70AM19CT1AG device.

Symbol	Characteristic	Test Conditions		Min	Тур	Max	Unit
I _{DSS}	Zero gate voltage drain current	V _{GS} = 0 V; V _{DS} = 700 V				100	μΑ
R _{DS(on)}	Drain-source on resistance	65	T _J = 25 °C		15	19	mΩ
	I _D = 40 A	T _J = 175 °C		18.8			
V _{GS(th)}	Gate threshold voltage	$V_{GS} = V_{DS}$, $I_D = 4$ mA		1.9	2.4		v
I _{GSS}	Gate-source leakage current	V_{GS} = 20 V, V_{DS} = 0 V				150	nA

Table 2 • Electrical Characteristics



The following table shows the dynamic characteristics per MOSFET of the MSCSM70AM19CT1AG device. **Table 3 • Dynamic Characteristics**

Symbol	Characteristic	Test Conditions		Min	Тур	Max	Unit
C _{iss}	Input capacitance	V _{GS} = 0 V	V _{GS} = 0 V				pF
C _{oss}	Output capacitance	V _{DS} = 700 V f = 1 MHz			510		
C _{rss}	Reverse transfer capacitance	_			29		
Qg	Total gate charge	V _{GS} = -5 V/20 V	V _{GS} = -5 V/20 V				nC
Q _{gs}	Gate-source charge	V _{Bus} = 470 V I _D = 40 A			58		
Q _{gd}	Gate-drain charge	_			35		
T _{d(on)}	Turn-on delay time	V _{GS} = -5 V/20 V					ns
T _r	Rise time	V _{Bus} = 400 V I _D = 80 A; T _J = 150 °C			35		
T _{d(off)}	Turn-off delay time	$R_{Gon} = 27 \Omega; R_{Goff} = 4.7 \Omega$	2		50		
Τ _f	Fall time				20		
E _{on}	Turn on energy	Inductive switching	T _J = 150 °C		545		μ
E _{off}	Turn off energy	$V_{GS} = -5 V/20 V$ $V_{Bus} = 400 V$ $I_{D} = 80 A$ $R_{Gon} = 27 \Omega$ $R_{Goff} = 4.7 \Omega$			186		μ
R _{Gint}	Internal gate resistance				0.69		Ω
R _{thJC}	Junction-to-case thermal resistance					0.41	°C/W

The following table shows the body diode ratings and characteristics per MOSFET of the MSCSM70AM19CT1AG device.

Table 4 • Body	Diode Ratings and Characteristics
----------------	-----------------------------------

Symbol	Characteristic	Test Conditions	Min	Тур	Max	Unit
V_{SD}	Diode Forward Voltage	V_{GS} = 0 V ; I _{SD} = 40 A		3.4		v
		V_{GS} = -5 V ; I _{SD} = 40 A		3.8		
t _{rr}	Reverse recovery time	I _{SD} = 40 A; V _{GS} = -5 V V _R = 400 V; d _{iF} /dt = 1000 A/μs		38		ns
Q _{rr}	Reverse recovery charge			318		nC
I _{rr}	Reverse recovery current			14.8		А



3.2 SiC Schottky Diode Ratings and Characteristics (Per SiC Diode)

The following table shows the reverse SiC diode ratings and characteristics per SiC diode of the MSCSM70AM19CT1AG device.

Symbol	Characteristic	Test Conditions		Min	Тур	Max	Unit
V _{RRM}	Peak repetitive reverse voltage					700	v
I _{RM}	Reverse leakage current		T _J = 25 °C		15	200	μΑ
			T _J = 175 °C		250		
I _F	DC forward current	T _C = 80 °C			50		А
V _F	Diode forward voltage	I _F = 50 A	T _J = 25 °C		1.5	1.8	v
			T _J = 175 °C		1.9		
Qc	Total capacitive charge	V _R = 400 V			133		nC
С	Total capacitance	f = 1 MHz, V _R = 200 V f = 1 MHz, V _R = 400 V			248		pF
					216		
R _{thJC}	Junction-to-case thermal resistance	e				0.86	°C/W

Table 5 • SiC Schottky Diode Ratings and Characteristics (Per SiC Diode)

3.3 Thermal and Package Characteristics

The following table shows the package characteristics of the MSCSM70AM19CT1AG device.

Table 6 • Package Characteristics


Symbol	Characteristic				Max	Unit
V _{ISOL}	RMS isolation voltage, any terminal to case t = 1 min,	4000		v		
Тј	Operating junction temperature range				175	°C
T _{JOP}	Recommended junction temperature under switching conditions				T _{Jmax} –25	
T _{STG}	Storage temperature range				125	
т _с	Operating case temperature			-40	125	
Torque	Mounting torque	2	3	N.m		
Wt	Package weight				80	g



The following table shows the temperature sensor NTC (see application note *APT0406* on www.microsemi.com) of the MSCSM70AM19CT1AG device.


Table 7 • Temperature Sensor NTC

Symbol	Characteristic		Min	Тур	Max	Unit
R ₂₅	Resistance at 25 °C			50		kΩ
$\Delta R_{25}/R_{25}$				5		%
B _{25/85}	T ₂₅ = 298.15 K			3952		К
ΔВ/В		T _C = 100 °C		4		%




3.4 Typical SiC MOSFET Performance Curves

This sections shows the typical SiC MOSFET performance curves of the MSCSM70AM19CT1AG device.








Microsemi Proprietary and Confidential MSCSM70AM19CT1AG Datasheet Revision 1.0








3.5 Typical SiC Diode Performance Curves

This sections shows the typical SiC diode performance curves of the MSCSM70AM19CT1AG device.






4 Package Specifications

This section shows the package specification of the MSCSM70AM19CT1AG device.

4.1 Package Outline Drawing

The following figure illustrates the package outline of the MSCSM70AM19CT1AG device. The dimensions are in millimeters.

Figure 21 • Package Outline Drawing







Microsemi 2355 W. Chandler Blvd. Chandler, AZ 85224 USA

Within the USA: +1 (480) 792-7200 Fax: +1 (480) 792-7277

www.microsemi.com $^{\textcircled{C}}$ 2020 Microsemi and its corporate affiliates. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation and its corporate affiliates. All other trademarks and service marks are the property of their respective owners. Microsemi's product warranty is set forth in Microsemi's Sales Order Terms and Conditions. Information contained in this publication is provided for the sole purpose of designing with and using Microsemi products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is your responsibility to ensure that your application meets with your specifications. THIS INFORMATION IS PROVIDED "AS IS." MICROSEMI MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. IN NO EVENT WILL MICROSEMI BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE WHATSOEVER RELATED TO THIS INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROSEMI HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROSEMI'S TOTAL LIABILITY ON ALL CLAIMS IN RELATED TO THIS INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, YOU PAID DIRECTLY TO MICROSEMI FOR THIS INFORMATION. Use of Microsemi devices in life support, mission-critical equipment or applications, and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend and indemnify Microsemi from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microsemi intellectual property rights unless otherwise stated.

Microsemi Corporation, a subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), and its corporate affiliates are leading providers of smart, connected and secure embedded control solutions. Their easy-to-use development tools and comprehensive product portfolio enable customers to create optimal designs which reduce risk while lowering total system cost and time to market. These solutions serve more than 120,000 customers across the industrial, automotive, consumer, aerospace and defense, communications and computing markets. Headquartered in Chandler, Arizona, the company offers outstanding technical support along with dependable delivery and quality. Learn more at **www.microsemi.com**.

MSCC-0344-DS-01084