

VOLTAGE -CONTROLLED CRYSTAL OSCILLATOR (VCXO) **OUTPUT : CMOS**



Product Number Q3614CE00xxxx00

SEIKO EPSON CORPORATION

VG-4231CE

 Frequency range 	: 3 MHz to 50 MHz * * 50MHz is not included in Output frequency range.
 Supply voltage 	: 3.3 V (PSCM / CSCM)
	2.8 V (PSBM / CSBM) 1.8 V (PQEM / CQEM)
•Frequency control range	: ±140 × 10 ⁻⁶ (*SCM / *SBM) ±120 × 10 ⁻⁶ (*QEM)
 Low current consumption External dimensions 	: 1.0 mA Typ. (27 MHz , 3.3 V) : 3.2 × 2.5 × 1.05 mm

Specifications (characteristics)

opcontations (characteristics)								
Item	Symbol	Specifications			Conditions / Remarks			
nem	Symbol	PSCM / CSCM	PSBM / CSBM	PQEM / CQEM				
Output frequency range	Fo			24 MHz to 30 MHz	Please contact us about available frequencies.			
Output hequency range	10			24 10112 10 30 101112	50MHz is not included in Output frequency range.			
Supply voltage	Vcc	3.3 V ± 0.3 V	2.8 V ± 0.2 V	1.8 V ± 0.2 V				
Storage temperature	T_stg	-40 °C to +125 °C			Storage as single product.			
Operating temperature	T_use	As per below table						
Frequency tolerance	f_tol	As per below table			C : Vc=1.65 V / B : Vc=1.40 V / E : Vc=0.90 V			
Current consumption	lcc	7 mA Max.	6.8 mA Max.	1.2 mA Max.	No load condition			
Frequency control range	f_cont	S:± 140 × 10 ⁻⁶ Min. Q:± 120 × 10 ⁻⁶ Min.			$Vc = 1/2 Vcc \pm 1/2 Vcc$			
Modulation characteristics	BW	15 kHz Min.			± 3 dB (at 1 kHz)			
Input resistance	Rin	M : 5 MΩ Min.			DC level			
Frequency change polarity		Positive polarity			Vc=0 V to Vcc			
Symmetry	SYM	40 % to 60 %			CMOS load:50 % Vcc level			
Онтальна Кала		Vcc-0.4 V Min.			Іон=-3.0 mA			
Output voltage	Vol	0.4 V Max.			IoL= 3.0 mA			
Output load condition (CMOS)	L_CMOS	15 pF Max.			CMOS load			
Rise time and Fall time	tr / tf	4 ns Max. 6 ns Max. CMC		CMOS load: 20 % Vcc to 80 % Vcc level				
Start-up time	t_str	5 ms Max.		Time at 90 % Vcc to be 0 s				
Frequency aging	f_age	± 5 × 10 ⁻⁶ Max.			+25 °C, 5 years			

Please keep Vc pin open or ground while powering up Vcc.

(1)

50MHz is not included in Output frequency range.

Product Name (Standard form) VG-4231 CE 27.000000MHz C S C - M 456 7 (2) 3

(56:SE,QC,QB are not available)

①Model 2 Package type 3 Frequency 4 Frequency tolerance / Operating temperature ⑤Frequency control range ⑥Supply voltage ⑦Input resistance (M: 5 MΩ Min.)

(Unit:mm)


45	GFrequency tolerance / Operating temperature GFrequency control range (Absolute pull range)		requency control range (Absolute pull range*)	6St	upply voltage	
CS	С	±30 × 10 ⁻⁶ / -20 to +70 °C	S	±140 × 10 ⁻⁶ Min. (±100 × 10 ⁻⁶ Min.)	Е	1.8 V Typ.
PS	Р	±37 × 10 ⁻⁶ / -40 to +85 °C	S	±140 × 10 ⁻⁶ Min. (±95 × 10 ⁻⁶ Min.)	В	2.8 V Typ.
CQ	С	±30 × 10 ⁻⁶ / -20 to +70 °C	Q	±120 × 10 ⁻⁶ Min. (±80 × 10 ⁻⁶ Min.)	С	3.3 V Typ.
PQ	Р	±37 × 10 ⁻⁶ / -40 to +85 °C	Q	±120 × 10 ⁻⁶ Min. (±75 × 10 ⁻⁶ Min.)		


* Absolute pull range = Frequency control range- (Frequency tolerance + 5 years Aging + Free fall + Vibration)

External dimensions

Footprint (Recommended)

(Unit:mm)





GND


OUT

Vcc

2

3

4



0.1uF by-pass capacitor at a location as near as possible to the power source terminal of the crystal product (between Vcc - GND).





PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs, Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired IATF 16949 certification that is requested strongly by major automotive manufacturers as standard.

Explanation of the mark that are using it for the catalog

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

IATF 16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

Pb Free	► Pb free.
RoHS	 Complies with EU RoHS directive. *About the products without the Pb-free mark. Contains Pb in products exempted by EU RoHS directive. (Contains Pb in sealing glass, high melting temperature type solder or other.)
For Automotive	► Designed for automotive applications such as Car Multimedia, Body Electronics, Remote Keyless Entry etc.
Automotive Safety	► Designed for automotive applications related to driving safety (Engine Control Unit, Air Bag, ESC etc).

NOTICE : PLEASE READ CAREFULLY BELOW BEFORE THE USE OF THIS DOCUMENT ©Seiko Epson Corporation 2020

- 1. The content of this document is subject to change without notice. Before purchasing or using Epson products, please contact with sales representative of Seiko Epson Corporation ("Epson") for the latest information and be always sure to check the latest information published on Epson's official web sites and resources.
- 2. This document may not be copied, reproduced, or used for any other purposes, in whole or in part, without Epson's prior consent.
- 3. Information provided in this document including, but not limited to application circuits, programs and usage, is for reference purpose only. Epson makes no guarantees against any infringements or damages to any third parties' intellectual property rights or any other rights resulting from the information. This document does not grant you any licenses, any intellectual property rights or any other rights with respect to Epson products owned by Epson or any third parties.
- 4. Using Epson products, you shall be responsible for safe design in your products; that is, your hardware, software, and/or systems shall be designed enough to prevent any critical harm or damages to life, health or property, even if any malfunction or failure might be caused by Epson products. In designing your products with Epson products, please be sure to check and comply with the latest information regarding Epson products (including, but not limited to this document, specifications, data sheets, manuals, and Epson's web site). Using technical contents such as product data, graphic and chart, and technical information, including programs, algorithms and application circuit examples under this document, you shall evaluate your products thoroughly both in stand-alone basis and within your overall systems. You shall be solely responsible for deciding whether to adopt/use Epson products with your products.
- 5. Epson has prepared this document carefully to be accurate and dependable, but Epson does not guarantee that the information is always accurate and complete. Epson assumes no responsibility for any damages you incurred due to any misinformation in this document.
- No dismantling, analysis, reverse engineering, modification, alteration, adaptation, reproduction, etc., of Epson products is allowed.
 Epson products have been designed, developed and manufactured to be used in general electronic applications and specifically designated applications ("Anticipated Purpose"). Epson products are NOT intended for any use beyond the Anticipated Purpose that requires particular quality or extremely high reliability in order to refrain from causing any malfunction or failure leading to critical harm to life and health, serious property damage, or severe impact on society, including, but not limited to listed below ("Specific Purpose"). Therefore, you are strongly advised to use Epson products only for the Anticipated Purpose. Should you desire to purchase and use Epson products for Specific Purpose, Epson makes no warranty and disclaims with respect to Epson products, whether express or implied, including without limitation any implied warranty of merchantability or fitness for any Specific Purpose. Please be sure to contact our sales representative in advance, if you desire Epson products for Specific Purpose:

Space equipment (artificial satellites, rockets, etc.)/ Transportation vehicles and their control equipment (automobiles, aircraft, trains, ships, etc.) / Medical equipment/ Relay equipment to be placed on sea floor/ Power station control equipment / Disaster or crime prevention equipment/Traffic control equipment/ Financial equipment Other equipment and the state of a list is a state of the state of the

Other applications requiring similar levels of reliability as the above

- 8. Epson products listed in this document and our associated technologies shall not be used in any equipment or systems that laws and regulations in Japan or any other countries prohibit to manufacture, use or sell. Furthermore, Epson products and our associated technologies shall not be used for the purposes of military weapons development (e.g. mass destruction weapons), military use, or any other military applications. If exporting Epson products or our associated technologies, please be sure to comply with the Foreign Exchange and Foreign Trade Control Act in Japan, Export Administration Regulations in the U.S.A (EAR) and other export-related laws and regulations in Japan and any other countries and to follow their required procedures.
- 9. Epson assumes no responsibility for any damages (whether direct or indirect) caused by or in relation with your non-compliance with the terms and conditions in this document or for any damages (whether direct or indirect) incurred by any third party that you give, transfer or assign Epson products.
- 10. For more details or other concerns about this document, please contact our sales representative.
- 11. Company names and product names listed in this document are trademarks or registered trademarks of their respective companies.