TN0106

N-Channel Enhancement-Mode Vertical DMOS FET

Features

- · 2V Maximum Low Threshold
- · High Input Impedance
- · 50 pF Typical Low Input Capacitance
- · Fast Switching Speeds
- · Low On-Resistance
- · Free from Secondary Breakdown
- · Low Input and Output Leakage

Applications


- Logic-Level Interfaces (Ideal for TTL and CMOS)
- · Solid-State Relays
- · Battery-Operated Systems
- · Photovoltaic Drives
- · Analog Switches
- · General Purpose Line Drivers
- · Telecommunication Switches

General Description

TN0106 low-threshold Enhancement-mode (normally-off) transistor uses a vertical DMOS structure and a well-proven silicon-gate manufacturing process. This combination produces a device with the power handling capabilities of bipolar transistors and the high input impedance and positive temperature coefficient inherent in MOS devices. Characteristic of all MOS structures, this device is free from thermal runaway and thermally induced secondary breakdown.

Microchip's vertical DMOS FETs are ideally suited to a wide range of switching and amplifying applications where very low threshold voltage, high breakdown voltage, high input impedance, low input capacitance, and fast switching speeds are desired.

Package Type



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings†

Drain-to-Source Voltage	BV _{DSS}
Drain-to-Gate Voltage	BV _{DGS}
Gate-to-Source Voltage	200
Operating Ambient Temperature, T _A	
Storage Temperature, T _S	

† Notice: Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

Electrical Specifications: $T_A = 25^{\circ}$ C unless otherwise specified. All DC parameters are 100% tested at 25°C unless otherwise stated. (Pulse test: 300 µs pulse, 2% duty cycle)

Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions
Drain-to-Source Breakdown Voltage	BV _{DSS}	60	_	_	V	$V_{GS} = 0V$, $I_D = 1$ mA
Gate Threshold Voltage	V _{GS(th)}	0.6	_	2	٧	$V_{GS} = V_{DS}, I_{D} = 0.5 \text{ mA}$
Change in V _{GS(th)} with Temperature	$\Delta V_{GS(th)}$	_	-3.2	-5	mV/°C	$V_{GS} = V_{DS}$, $I_D = 1$ mA (Note 1)
Gate Body Leakage Current	I _{GSS}	_	_	100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$
		_		10	μΑ	V _{GS} = 0V, V _{DS} = Maximum rating
Zero-Gate Voltage Drain Current	I _{DSS}	_		500	μΑ	V_{DS} = 0.8 Maximum rating, V_{GS} = 0V, T_A = 125°C (Note 1)
On-State Drain Current	1	0.75	1.4	_	Α	$V_{GS} = 5V, V_{DS} = 25V$
On-State Drain Current	I _{D(ON)}	2	3.4	_	Α	$V_{GS} = 10V, V_{DS} = 25V$
Static Drain-to-Source On-State Resistance	D	_	2	4.5	Ω	V_{GS} = 4.5V, I_{D} = 250 mA
Static Diani-to-Source Oil-State Resistance	R _{DS(ON)}	_	1.6	3	Ω	V_{GS} = 10V, I_{D} = 500 mA
Change in R _{DS(ON)} with Temperature	ΔR _{DS(ON)}	_	0.6	1.1	%/°C	V _{GS} = 10V, I _D = 500 mA (Note 1)

Note 1: Specification is obtained by characterization and is not 100% tested.

AC ELECTRICAL CHARACTERISTICS

Electrical Specifications: T_A = 25°C unless otherwise specified. Specification is obtained by characterization and is not 100% tested.

Parameter		Min.	Тур.	Max.	Unit	Conditions	
Forward Transconductance	G _{FS}	225	400	_	mmho	V _{DS} = 25V, I _D = 500 mA	
Input Capacitance	C _{ISS}	_	50	60	pF	$V_{GS} = 0V$,	
Common-Source Output Capacitance	Coss	_	25	35	pF	V _{DS} = 25V,	
Reverse Transfer Capacitance	C _{RSS}	_	4	8	pF	f = 1 MHz	
Turn-On Delay Time	t _{d(ON)}	_	2	5	ns		
Rise Time	t _r	_	3	5	ns	V _{DD} = 25V, I _D = 1A,	
Turn-Off Delay Time	t _{d(OFF)}	_	6	7	ns	$R_{GEN} = 25\Omega$	
Fall Time	t _f	_	3	6	ns	GEN	
DIODE PARAMETER							
Diode Forward Voltage Drop	V_{SD}		1	1.5	V	V _{GS} = 0V, I _{SD} = 500 mA (Note 1)	
Reverse Recovery Time	t _{rr}	_	400	_	ns	V _{GS} = 0V, I _{SD} = 500 mA	

Note 1: All DC parameters are 100% tested at 25°C unless otherwise stated. (Pulse test: 300 µs pulse, 2% duty cycle)

TEMPERATURE SPECIFICATIONS

Parameter		Min.	Тур.	Max.	Unit	Conditions		
TEMPERATURE RANGE								
Operating Ambient Temperature	T _A	-55	_	+150	°C			
Storage Temperature		-55	_	+150	°C			
PACKAGE THERMAL RESISTANCE								
3-lead TO-92	θ_{JA}	_	132	_	°C/W			

THERMAL CHARACTERISTICS

Package	I _D (Note 1) (Continuous) (mA)	I _D (Pulsed) (A)	Power Dissipation at T _A = 25°C (W)	I _{DR} (Note 1) (mA)	I _{DRM} (A)
3-lead TO-92	350	2	1	350	2

Note 1: I_D (continuous) is limited by maximum rated T_J .

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g. outside specified power supply range) and therefore outside the warranted range.




FIGURE 2-1: Output Characteristics.




FIGURE 2-2: Transconductance vs. Drain Current.




FIGURE 2-3: Maximum Rated Safe Operating Area.




FIGURE 2-4: Saturation Characteristics.




FIGURE 2-5: Power Dissipation vs. Case Temperature.




FIGURE 2-6: Thermal Response Characteristics.





FIGURE 2-7: BV Temperature.






FIGURE 2-8: Transfer Characteristics.




FIGURE 2-9: Capacitance vs. Drain-to-Source Voltage.




FIGURE 2-10: On Current.

On-Resistance vs. Drain




FIGURE 2-11: with Temperature.

 $V_{GS(th)}$ and R_{DS} Variation




FIGURE 2-12: Characteristics.

Gate Drive Dynamic

TN0106

3.0 PIN DESCRIPTION

Table 3-1 shows the description of pins in TN0106. Refer to **Package Type** for the location of pins.

TABLE 3-1: PIN FUNCTION TABLE

Pin Number	Pin Name	Description					
1	Source	Source					
2	Gate	Gate					
3	Drain	Drain					

4.0 FUNCTIONAL DESCRIPTION

Figure 4-1 illustrates the switching waveforms and test circuit for TN0106.





FIGURE 4-1: Switching Waveforms and Test Circuit.

TABLE 4-1: PRODUCT SUMMARY

BV _{DSS} /BV _{DGS} (V)	R _{DS(ON)}	I _{D(ON)}	V _{GS(th)}
	(Maximum)	(Minimum)	(Maximum)
	(Ω)	(A)	(V)
60	3	2	2

5.0 PACKAGING INFORMATION


5.1 Package Marking Information




Legend: XX...X Product Code or Customer-specific information
Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')
NNN Alphanumeric traceability code
Pb-free JEDEC® designator for Matte Tin (Sn)
* This package is Pb-free. The Pb-free JEDEC designator (@3)
can be found on the outer packaging for this package.

Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for product code or customer-specific information. Package may or not include the corporate logo.

3-Lead TO-92 Package Outline (L/LL/N3)





Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Symb	ool	А	b	С	D	E	E1	е	e1	L
	MIN	.170	.014 [†]	.014 [†]	.175	.125	.080	.095	.045	.500
Dimensions (inches)	NOM	-	-	-	-	-	-	-	-	-
()	MAX	.210	.022 [†]	.022 [†]	.205	.165	.105	.105	.055	.610*

JEDEC Registration TO-92.
* This dimension is not specified in the JEDEC drawing.
† This dimension differs from the JEDEC drawing.

Drawings not to scale.

TN0106

NOTES:

APPENDIX A: REVISION HISTORY

Revision A (September 2020)

- Converted Supertex Docs# DSFP-TN0106 to Microchip DS20005932A
- · Changed the package marking format
- Updated the packing medium of the TN0106 N3 P013 media type from 2000/Reel to 2000/Reel (Ammo Pack) to align it with the actual BQM
- Made minor text changes throughout the document

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO	<u>). XX</u>	- <u>X</u> - <u>X</u>	Examples:	
Device	Package Options	Environmental Media Type	a) TN0106N3-G:	N-Channel Enhance- ment-Mode, Vertical DMOS FET, 3-lead TO-92,1000/Bag
Device:	TN0106 =	DMOS FET	b) TN0106N3-G-P003:	N-Channel Enhance- ment-Mode, Vertical DMOS FET, 3-lead TO-92,
Package:	N3 =	= 3-lead TO-92		2000/Reel
Environmental:	G =	Lead (Pb)-free/RoHS-compliant Package	c) TN0106N3-G-P013:	N-Channel Enhance- ment-Mode, Vertical
Media Types:	(blank) =	1000/Bag for an N3 Package		DMOS FET, 3-lead TO-92, 2000/Reel (Ammo Pack)
	P003 =	2000/Reel for an N3 Package		,
	P013 =	= 2000/Reel (Ammo Pack) for an N3 Package		

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not
 mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are
 committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection
 feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or
 other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDI-RECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUEN-TIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN:978-1-5224-6789-2



Worldwide Sales and Service

AMERICAS

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address: www.microchip.com

Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Austin, TX Tel: 512-257-3370

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Dallas Addison, TX Tel: 972-818-7423

Tel: 972-818-7423 Fax: 972-818-2924

Detroit Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323

Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

Raleigh, NC Tel: 919-844-7510

New York, NY Tel: 631-435-6000

San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270

Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

China - Beijing Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

China - Dongguan Tel: 86-769-8702-9880

China - Guangzhou Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

China - Shenzhen

Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan Tel: 86-27-5980-5300

China - Xian

Tel: 86-29-8833-7252 China - Xiamen

Tel: 86-592-2388138 **China - Zhuhai** Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

Japan - Osaka Tel: 81-6-6152-7160

Japan - Tokyo Tel: 81-3-6880- 3770

Korea - Daegu

Tel: 82-53-744-4301 **Korea - Seoul** Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

Singapore Tel: 65-6334-8870

Taiwan - Hsin Chu Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

Taiwan - Taipei Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

EUROPE

Austria - Wels Tel: 43-7242-2244-39

Fax: 43-7242-2244-393 **Denmark - Copenhagen**Tel: 45-4485-5910

Fax: 45-4485-2829 Finland - Espoo

Tel: 358-9-4520-820

France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

Germany - Haan Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

Germany - Karlsruhe Tel: 49-721-625370

Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

Poland - Warsaw Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 **Sweden - Gothenberg**

Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820