www.elecsuper.com

SuperESD - USBLC6-2P6

1.Description

The USBLC6-2P6 is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability. Low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium.

2.Features

- IEC 61000-4-2 Level 4 ESD Protection
 - ±12kV Contact Discharge
 - ±17kV Air Discharge
- IEC 61000-4-4 EFT Protection
 - 40A (5/50ns)
- IEC 61000-4-5 Surge
 - 4.5A (8/20us)

- RoHS compliance
- Protecting two I/O line
- Ultra-low Capacitance:0.6pF (Typical)
- Low clamping voltage
- Low leakage current
- Solid-state silicon technology

3.Applications

- HDMI/USB2.0
- Monitors and flat panel display
- 10/100/1000 ethernet

- Notebook computers
- SIM ports
- ATM interface

4. Ordering Information

Part Number	Package	Marking	Material	Packing	Quantity per reel	Flammability Rating	Reel Size
USBLC6-2P6	SOT-563	A	Halogen	Tape &	3K PCS	UL 94V-0	7 inches
			free	Reel	JK FC3		

Table-1 Ordering information

5.Pin Configuration and Functions

Pin	Name	Description	Outline	Circuit Diagram		
1	Ю	Connect to IO				
2	GND	Connect to GND	6 5 4	5		
3	Ю	Connect to IO		384		
4	Ю	Connect to IO		364		
5	Vcc	Connect to Vcc	1 2 3	2		
6	Ю	Connect to IO				

Table-2 Pin configuration

6.Specification

6.1. Absolute Maximum rating

Over operating free-air temperature range (unless otherwise noted)

Parameters	Symbol	Min.	Max.	Unit
Peak pulse power (tp=8/20us)@25°C	P_{pk}	-	60	W
Peak pulse current (tp=8/20us)@25°C	I _{PP}		4.5	А
ESD (IEC61000-4-2 air discharge) @25°C	V _{ESD}	-	±17	kV
ESD (IEC61000-4-2 contact discharge) @25°C	V _{ESD}	-	±12	kV
Junction temperature	TJ	-	150	℃
Operating temperature	T _{OP}	-40	125	℃
Storage temperature	T _{STG}	-55	150	℃
Lead temperature	TL	-	260	°C

Table-3 Absolute Maximum rating

6.2. Electrical Characteristics


At TA = 25°C unless otherwise noted

Parameters	Symbol	conditions	Min.	Тур.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				5	V
Reverse Breakdown Voltage	V_{BR}	I _T = 1mA	6			V
Reverse Leakage Current	I _R	V _{RWM} =5V			1	uA
Peak Pulse Current	I _{PP}	TP=8/20us@25°C		4.5		А
Clamping Voltage	V _{CL}	I _{PP} =1A; TP=8/20us		8.5		
Clamping Voltage	V _{CL}	I _{PP} =4.5A; TP=8/20us		12		V
	e C _J	I/O pins to ground;				
lunction canacitance		$V_R=0V$; $f=1MHz$		0.6		nE
Junction capacitance		Between I/O pins;			√ pF	
		$V_R=0V$; f = 1MHz		0.3		


Table-4 Electrical Characteristics

<u>ElecSuper</u>

7. Typical Characteristic



8. Typical Application





Typical Interface Application





<u>ElecSuper</u>

9. Dimensions and Land Pattern (SOT-563)










Units in millimeters

symbol	Α	В	С	D	Е	F	G	Н	I	J
Min.	1.50	0.50	1.55	1.10	0.15	0.50	0.00	0.10	0.10	0.15
Max.	1.70	0.60	1.70	1.25	0.30	0.60	0.05	0.18	0.30	0.20

Table-5 Product dimensions



Note:

- 1. Controlling dimension: in millimeters
- 2. General tolerance: ± 0.05 mm
- 3. The pad layout is for reference only

DISCLAIMER

USBLC6-2P6 Rev-1.1 <u>www.elecsuper.com</u>

ELECSUPER PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with ElecSuper products. You are solely responsible for

- (1) selecting the appropriate ElecSuper products for your application;
- (2) designing, validating and testing your application;
- (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. ElecSuper grants you permission to use these resources only for development of an application that uses the ElecSuper products described in the resource. Other reproduction and display of these resources are prohibited. No license is granted to any other ElecSuper intellectual property right or to any third party intellectual property right. ElecSuper disclaims responsibility for, and you will fully indemnify ElecSuper and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources. ElecSuper's products are provided subject to ElecSuper's Terms of Sale or other applicable terms available either on www.elecsuper.com or provided in conjunction with such ElecSuper products. ElecSuper's provision of these resources does not expand or otherwise alter ElecSuper's applicable warranties or warranty disclaimers for ElecSuper products.