

P-Channel Enhancement Mode Field Effect Transistor

General Description

The CMSA150P03 uses advanced trench

technology to provide excellent RDS(ON).

This device is ideal for load switch and

battery protection applications.

Features

- Fast switching speed
- Lower On-resistance
- 100% EAS Guaranteed
- Simple Drive Requirement

Product Summary

BVDSS	RDSON	ID
-30V	5.8mΩ	-150A

Applications

- Load Switch
- Power Management in Notebook Computer, Portable
 Equipment and Battery Powered Systems.

DFN-8 5x6 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units	
V_{DS}	Drain-Source Voltage	-30	V	
V_{GS}	Gate-Source Voltage	±20	V	
I _D @T _C =25°C	Continuous Drain Current -150		Α	
I _{DM}	Pulsed Drain Current	-600	Α	
EAS	Single Pulse Avalanche Energy ¹	666	mJ	
P _D @T _C =25°C	Total Power Dissipation	110	W	
T _{STG}	Storage Temperature Range	-55 to 150	°C	
TJ	Operating Junction Temperature Range	-55 to 150	°C	

Thermal Data

Symbol	Parameter	Тур.	Max.	Unit
$R_{\theta JA}$	Junction-to-Ambient(Steady-State)		55	°C/W
R _{eJC}	Junction-to-Case		1.5	°C/W



P-Channel Enhancement Mode Field Effect Transistor

Electrical Characteristics ($T_J=25^{\circ}$ C), unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =-250uA	-30			٧
В	Static Drain-Source On-Resistance	V _{GS} =-10V, I _D =-20A		4.6	5.8	C
R _{DS(ON)}	Static Dialii-Source Off-Resistance	V _{GS} =-4.5V, I _D =-20A		5.6	8	mΩ
V _{GS(th)}	Gate Threshold Voltage	V_{GS} = V_{DS} , I_D =-250uA	-1		-3	V
I _{DSS}	Drain-Source Leakage Current	V_{DS} =-24V , V_{GS} =0V , T_{J} =25 $^{\circ}$ C			-1	uA
I _{GSS}	Gate-Source Leakage Current	V_{GS} =±20V , V_{DS} =0V			±100	nA
gfs	Forward Transconductance	V _{DS} =-10V , I _D =-10A		28		S
R_g	Gate Resistance	V_{DS} =0V , V_{GS} =0V , f=1MHz		20		Ω
Qg	Total Gate Charge	V - 40V I - 20A		100		
Q_gs	Gate-Source Charge	V _{DS} =-10V , I _D =-20A V _{GS} =-4.5V		20		nC
Q_{gd}	Gate-Drain Charge			30		
T _{d(on)}	Turn-On Delay Time			20		
Tr	Rise Time	V _{DD} =-10V, V _{GEN} =-4.5V		50		200
T _{d(off)}	Turn-Off Delay Time	I_D =-1A , R_G =3 Ω , R_L =0.5 Ω		100		ns
T _f	Fall Time			40		
C _{iss}	Input Capacitance			9400		
Coss	Output Capacitance	V _{DS} =-10V, V _{GS} =0V , f=1MHz		800		pF
C _{rss}	Reverse Transfer Capacitance			520		

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Is	Continuous Source Current	V _G =V _D =0V , Force Current			-150	Α
I _{SM}	Pulsed Source Current				-600	A
V _{SD}	Diode Forward Voltage	V _{GS} =0V , I _F =-1A			-1.2	V

Note:

1.The EAS data shows Max. rating . The test condition is V_{DD} =-20V, V_{GS} =-10V,L=1 mH,ID=-36.5A

This product has been designed and qualified for the counsumer market. Cmos assumes no liability for customers' product design or applications. Cmos reserver the right to improve product design ,functions and reliability without notice.