





WITH CAP



WITH CAP



Recommended PCB Layout

Specifications:

规格:  
 Voltage rating:50V AC/DC  
 额定电压: 50V AC/DC  
 Current rating:0.5A AC/DC  
 额定电流: 0.5A AC/DC  
 Withstanding voltage:250V AC/minute  
 耐受电压: 250V AC/分钟  
 Temperature range:-40℃~+105℃  
 温度范围: -40℃~+105℃  
 Insulation resistance:500MΩ  
 绝缘电阻: 500MΩ  
 Contact resistance:100mΩ  
 接触电阻: 100mΩ

X0815 W V S - XX E S - 9T V01  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-30-80Pin
- 6.Category:E-7.8mm Height
- 7.Special No:S-With positioning column
- 8.Material:9T-PA9T UL94V-0  
CAP:PA6T UL94V-0
- 9.Plating:Gold Plated 4u" MIN

Poles	Dimensions(mm)				
	A	B	C	D	E
30	11.20	13.00	14.40	16.30	16.10
40	15.20	17.00	18.40	20.30	20.10
50	19.20	21.00	22.40	24.30	24.10
60	23.20	25.00	26.40	28.30	28.10
70	27.20	29.00	30.40	32.30	32.10
80	31.20	33.00	34.40	36.30	36.10

X0815WVS-XXES-9TV01	PA9T	Phosphor Bronze	X0815FVS-A	12.75mm±0.5
			X0815FVS-B	9.0mm±0.5
PART NO	Material	Material(Pin)	Suitable XKB Wafer	Mating Height

广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△X					ANGULAR ±5°
△X					L ≤ 4 ±0.2
△X					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND		SCALE: N/A	MODEL TYPE: 0.8mm BTB Connector
DWN		VIEW:	PART NO.: X0815WVS-XXES-9TV01
CHKD		UNIT: mm/in	DWG NO.: X-X0815WVS-XXES-9TV01
APPD		SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED