






REV.	DESCRIPTION OF REVISIONS	APPR.	DRAW.	RELEASE	DATE
X1					
X2					



ELECTRIC FUNCTION	DETECT SWITCH
WITHOUT CARD	OPEN
CARD INSERTED	CLOSED



Coplanarity of metal solder pins $\leq 0.10\text{mm}$

TECHNICAL CHARACTERISTICS

- General Characteristics
Dimensions: 28.77LX18.97WX2.00 mm
Weight: Approx 0.70±0.1g
Durability: 100,000 cycles min.
- Electrical Characteristics
Contact resistance: 50mΩ typical, 100mΩ max
Insulation resistance: >1000MΩ/500V DC
- Solderability
IR reflow: 260°C, 10sec. Max
Manual soldering: 370°C, 3sec. Max
- Environmental Characteristics
Operating temperature: -40°C~+85°C
Operating humidity: 10%~+95%RH

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	BASE	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	8	Copper Alloy	Contact area: Gold plated
3	SWITCH CONTACT 2	1	Copper Alloy	Contact area: Gold plated
4	SWITCH CONTACT 1	1	Copper Alloy	Contact area: Gold plated

Unless otherwise specified, other tolerance are:

MUP MUP INDUSTRIAL CO.,LTD.

NAME: **Smart Card Connector**

MODEL NO: **MUP-C738-4 (H2.00 mm)**

TYPE: **with post(with logo)**

PROJ.	UNIT	SCALE	DRAWN	Zoey	Oct.07.2009	DWG NO.:	DWG-MUP-C738-4
①	mm	1:1	CHECKED	Keey	Oct.07.2009	SHEET	1/1
CUSTOMER DRAWING			APPROVAL	Simon	Oct.07.2009	REVISION	X1

