






REV.	DESCRIPTION OF REVISIONS	APPR.	DRAW.	RELEASE	DATE
X1	NEW REVISION				Henry Sep.22.2017
X2					



ELECTRIC FUNCTION	DETECT SWITCH
WITHOUT CARD	OPEN
CARD INSERTED	CLOSED



- PAD AREA
 - CONNECTOR OUTLINE
 - NO PATTERN AND VIA HOLE IN THIS AREA
- RECOMMENDED P.C.B LAYOUT COMPONENT SIDE(TOLERANCE ±0.05)

TECHNICAL CHARACTERISTICS

1.General Characteristics
 Dimensions:10.40LX8.90WX0.48H mm
 Weight:Approx 0.40±0.2g
 Durability:2,500 cycles min.
 2.Electrical Characteristics
 Contact resistance:50mΩ typical, 100mΩMax
 Insulation resistance:>1000MΩ/500V DC
 3.Solderability
 Vaporphase:215°C, 30sec.Max
 IR reflow:260°C,5sec.Max
 Manual soldering:370°C.3sec.Max
 4.Environmental Characteristics
 Operating temperature:-40°C~+85°C
 Operating humidity:10%~+95%RH

NANO SIM CARD	
Pin No.	ASSIGNMENT
C1	VCC(SUPPLY VOLTAGE)
C2	RST(RESET SIGNAL)
C3	CLK(COLCK SIGNAL)
C7	I/O(DATA INPUT/OUTPUT)
C5	GND
C6	VPP(VARIABLE SUPPLY VOLTAGE)
SW	DETECTION SWITCH

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	6	Copper Alloy	Contact area:Gold plated
3	SW	1	Copper Alloy	Contact area:Gold plated

Unless otherwise specified, other tolerance are:

MUP MUP INDUSTRIAL CO.,LTD.

NAME: **NANO-SIM Card Connector**
 MODEL NO: **MUP-C786-1**
 TYPE: **H0.50mm 6PIN WITH SWITCH PIN**

PROJ.	UNIT	SCALE	DRAWN	Henry Sep.22.2017	DWG NO.:	DWG-MUP-C786-1	
	mm	1:1	CHECKED	Henry Sep.22.2017	SHEET	1/1	REVISION
CUSTOMER DRAWING			APPROVAL	Simon Sep.22.2017	X1		

