








REV.	DESCRIPTION OF REVISIONS	APPR.	DRAW.	RELEASE	DATE
X1					



NOTES:

- ELECTRICAL CHARACTERISTICS
  - CONTACT RESISTANCE: 60 Milliohms Max
  - INSULATION RESISTANCE: 1,000 Megohms Min.
  - VOLTAGE RATING: 50V.
  - CURRENT RATING: 1.0A.
- MECHANICAL CHARACTERISTICS
  - OPERATION TEMPERATURE RANGE: -20°C~+85°C
  - DURABILITY: 3000 CYCLES
- MATERIAL:
  - HOUSING: THERMOPLASTIC,UL 94-V0
  - TERMINAL: PHOSPHOR BRONZE,T=0.12
  - SHELL: STAINLESS STEEL,T=0.15
- FINISHED:
  - TERMINAL: Ni PLATED UNDER, 1U" Au MIN PLATED ON CONTACT AREA,G/F PLATED ON SOLDER TAIL
  - SHELL: Ni PLATED UNDER,G/F PLATED ON SOLDER TAIL



PIN No.	DESCRIPTION
C1	VCC (SUPPLY VOLTAGE)
C2	RST (RESET SIGNAL)
C3	CLK (CLOCK SIGNAL)
C4	RESERVED
C5	GND
C6	VPP (VARIABLE SUPPLY VOLTAGE)
C7	I/O (DATA INPUT/OUTPUT)
C8	RESERVED

RECOMMENDED PCB LAYOUT (Top View)  
GENERAL TOLERANCE ±0.05

Unless otherwise specified, other tolerance are:		
X ±0.35	X' ±5'	
X.X ±0.25	X.X' ±4'	
X.XX ±0.15	X.XX' ±3'	
X.XXX ±0.10	X.XXX' ±2'	
PROJ.	UNIT	SCALE
①	mm	1:1
CUSTOMER DRAWING		

**MUP**® MUP INDUSTRIAL CO.,LTD.

NAME: MICRO SIM CARD CONNECTOR		DRAWN: HUABO 10/8-16'		DWG NO.: DWG-MUP-C7903-001	
MODEL NO: MUP-C7903-51A		CHECKED: HUABO 10/8-16'		SHEET: 1/1	
TYPE: H1.5 SMT TYPE		APPROVAL: Wang 10/8-16'		REVISION: X1	

