ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

Intelligent Power Module (IPM), 650 V, 50 A

Advance Information NFAM5065L4BL

General Description

The NFAM5065L4BL is a fully-integrated inverter power module consisting of an independent High side gate driver, LVIC, six IGBT's and a temperature sensor (VTS), suitable for driving permanent magnet synchronous (PMSM) motors, brushless DC (BLDC) motors and AC asynchronous motors. The IGBT's are configured in a three-phase bridge with separate emitter connections for the lower legs for maximum flexibility in the choice of control algorithm.

The power stage has under voltage lockout protection (UVP). Internal boost diodes are provided for high side gate boost drive.

Features

- Three-phase 650 V, 50 A IGBT Module with Independent Drivers
- Active Logic Interface
- Built-in Undervoltage Protection (UVP)
- Integrated Bootstrap Diodes and Resistors
- Separate Low-side IGBT Emitter Connections for Individual Current Sensing of Each Phase
- Temperature Sensor (VTS)
- UL1557 Certified (File No.339285)
- This Device is Pb-Free and RoHS Compliant

Typical Applications

- Industrial Drives
- Industrial Pumps
- Industrial Fans
- Industrial Automation





Figure 1. Application Schematic

This document contains information on a new product. Specifications and information herein are subject to change without notice.



ON Semiconductor®

www.onsemi.com



DIP39, 54.5x31.0 EP-2 CASE MODGX

MARKING DIAGRAM



Device marking is on package top side

NFAM5065L4BL	= Specific Device Code
ZZZ	= Assembly Lot Code
А	= Assembly Location
Т	= Test Location
Y	= Year
WW	= Work Week

ORDERING INFORMATION

Device	Package	Shipping
NFAM5065L4BL	DIP39 54.5 x 31.0 (Pb-Free)	90 / Box

APPLICATION SCHEMATIC





Figure 2. Application Schematic – Adjustable Option

BLOCK DIAGRAM





PIN FUNCTION DESCRIPTION

Pin	Name	Description
1	VS(U)	High–Side Bias Voltage GND for U phase IGBT Driving
(2)	-	Dummy
3	VB(U)	High–Side Bias Voltage for U phase IGBT Driving
4	VDD(UH)	High–Side Bias Voltage for U phase IC
(5)	-	Dummy
6	HIN(U)	Signal Input for High–Side U Phase
7	VS(V)	High–Side Bias Voltage GND for V phase IGBT Driving
(8)	-	Dummy
9	VB(V)	High–Side Bias Voltage for V phase IGBT Driving
10	VDD(VH)	High–Side Bias Voltage for V phase IC
(11)	-	Dummy
12	HIN(V)	Signal Input for High-Side V Phase
13	VS(W)	High–Side Bias Voltage GND for W phase IGBT Driving
(14)	-	Dummy
15	VB(W)	High–Side Bias Voltage for W phase IGBT Driving
16	VDD(WH)	High–Side Bias Voltage for W phase IC
(17)	-	Dummy
18	HIN(W)	Signal Input for High-Side W Phase
(19)	-	Dummy
20	VTS	Voltage Output for LVIC Temperature Sensing Unit
21	LIN(U)	Signal Input for Low-Side U Phase
22	LIN(V)	Signal Input for Low–Side V Phase
23	LIN(W)	Signal Input for Low–Side W Phase
24	VFO	Fault Output
25	CFOD	Capacitor for Fault Output Duration Selection
26	CIN	Input for Current Protection
27	VSS	Low–Side Common Supply Ground
28	VDD(L)	Low–Side Bias Voltage for IC and IGBTs Driving
(29)	-	Dummy
(30)	-	Dummy
31	NW	Negative DC-Link Input for U Phase
32	NV	Negative DC-Link Input for V Phase
33	NU	Negative DC-Link Input for W Phase
34	W	Output for U Phase
35	V	Output for V Phase
36	U	Output for W Phase
37	Р	Positive DC-Link Input
38	N.C	No Connection
(39)	-	Dummy
	1	

1. Pins of () are the dummy for internal connection. These pins should be no connection.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^{\circ}C$) (Note 2)

Symbol	Rating	Conditions	Value	Unit	
VPN	Supply Voltage	P–NU, NV, NW	450	V	
VPN(surge)	Supply Voltage (Surge)	P-NU, NV, NW (Note 3)	550	V	
VPN(PROT)	Self Protection Supply Voltage Limit (Short–Circuit Protection Capability)			V	
Vces	Collector-emitter voltage		650	V	
VRRM	Maximum Repetitive Revers Voltage				
±lc	Each IGBT Collector Current		±30	А	
Іор	op Output current (peak) PWM control		±50	А	
±lcp	Each IGBT Collector Current (Peak)	Under 1 ms Pulse Width	±100	A	
VDD	Control Supply Voltage	VDD(UH,VH,WH), VDD(L)-VSS	-0.3 to 20	V	
VBS	High–Side Control Bias voltage	VB(U)–VS(U), VB(V)–VS(V), VB(W)–VS(W)	-0.3 to 20	V	
VIN	Input Signal Voltage	HIN(U), HIN(V), HIN(W), LIN(U), LIN(V), LIN(W)–VSS		V	
VFO	Fault Output Supply Voltage	VFO-VSS	-0.3 to VDD	V	
IFO	Fault Output Current	Sink Current at VFO pin	2	mA	
VCIN	Current Sensing Input Voltage	CIN-VSS	–0.3 to VDD	V	
Pc	Corrector Dissipation	Per One Chip	125	W	
TJ	Operating Junction Temperature		-40 to +150	°C	
Tstg	Storage temperature		-40 to +125	°C	
Тс	Module Case Operation Temperature		-40 to +125	°C	
V _{ISO}	Isolation voltage	60 Hz, Sinusoidal, AC 1 minute, Connection Pins to Heat Sink Plate	2500	Vrms	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

2. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters. 3. This surge voltage developed by the switching operation due to the wiring inductance between P and NU, NV, NW terminal.

THERMAL CHARACTERISTICS

Symbol	Rating	Conditions	Min	Тур	Мах	Unit
R _{th(j-c)Q}	Junction-to-Case Thermal	Inverter IGBT Part (per 1/6 module)	-	-	1.0	°C/W
R _{th(j-c)F}	Resistance	Inverter FWD Part (per 1/6 module)	-	-	1.7	°C/W

4. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.

RECOMMENDED OPERATING CONDITIONS (Note 5)

Symbol	Rating	Cond	Min	Тур	Max	Unit	
VPN	Supply Voltage	P–NU, NV, NW		-	300	400	V
VDD	Gate Driver Supply	VDD(UH,VH,WH)	, VDD(L)-VSS	13.5	15	16.5	V
VBS	Voltages	VB(U)–VS(U), VB(V)–VS(V), VB(W)–VS(W)		13.0	15	18.5	V
dVDD / dt, dVBS / dt	Supply Voltage Variation			-1	-	1	V/μs
fPWM	PWM Frequency			1	-	20	kHz
DT	Dead Time	Turn-off to Turn-on (external)		2.0	-	-	μs
lo	Allowable r.m.s. Current	VPN = 300 V, VDD = 15 V, P.F. = 0.8	f _{PWM} = 5 kHz	-	-	29.2	Arms
		Tc ≤ 125°C, Tj ≤ 150°C (Note 5)	f _{PWM} = 15 kHz	-	-	20.2	
PWIN (on)	Allowable Input Pulse Width		200 V ≤ VPN ≤ 400 V 13.5 V ≤ VDD ≤ 16.5 V		-	-	μs
PWIN (off)		$13.0 V \le VBS \le 18$ $-20^{\circ}C \le Tc \le 100^{\circ}$		1.5	-	-]
	Package Mounting Torque	M3 type screw		0.6	0.7	0.9	Nm

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.5. Allowable r.m.s current depends on the actual conditions.

6. Flatness tolerance of the heatsink should be within $-50 \,\mu\text{m}$ to $+100 \,\mu\text{m}$.

ELECTRICAL CHARACTERISTICS (T_C = 25°C, VDD = 15 V, VBS = 15 V, unless otherwise specified.) (Note 7)

Symbol	Parameter		Test Conditions	Min	Тур	Max	Unit
INVERTERSE	CTION						
lces	Collector-Emitter Leakage	Vce = Vces, $T_J = 25^{\circ}C$	-	-	1	mA	
	Current		Vce = Vces, T _J = 150°C	-	-	10	mA
VCE(sat)	Collector-Emitter Saturation Voltage		VDD = VBS = 15 V, IN = 5 V Ic = 50 A, T _J = 25°C	_	1.65	2.30	V
		VDD = VBS = 15 V, IN = 5 V Ic = 50 A, T _J = 150°C	-	1.85	-	V	
VF	FWDi Forward Voltage	tage	$IN = 0 V$, $Ic = 50 A$, $T_J = 25^{\circ}C$	-	2.00	2.40	V
			$IN = 0 V$, $Ic = 50 A$, $T_J = 150^{\circ}C$	-	2.00	-	V
ton	Switching Times High	High Side	VPN = 300 V, VDD(H) = VDD(L) = 15 V Ic = 50 A, T _J = 25°C, IN = 0 \Leftrightarrow 5 V Inductive Load	1.05	1.65	2.25	μs
tc(on)	1			-	0.40	0.90	μs
toff	1			-	1.80	2.40	μs
tc(off)	1			-	0.25	0.75	μs
trr	1			-	0.25	-	μS
ton	1	Low Side	VPN = 300 V, VDD(H) = VDD(L) = 15 V	1.25	1.85	2.45	μs
tc(on)	1		$Ic = 50 A, T_J = 25^{\circ}C, IN = 0 \Leftrightarrow 5 V$ Inductive Load	-	0.50	1.00	μs
toff	7			-	1.70	2.30	μs
tc(off)	1			-	0.25	0.75	μs
trr	7			-	0.25	_	μs

ELECTRICAL CHARACTERISTICS (T _C = 25°C, VDD = 15 V, VBS = 15 V, unless otherwise specified.) (Note 7)	(continued)
--	-------------

Symbol	Parameter	Test Conditions		Min	Тур	Max	Unit
RIVER SECT	ION						
IQDDH	Quiescent VDD Supply Current	VDD(UH,VH,WH) = 15 V, HIN(U,V,W) = 0 V	VDD(UH)-VSS VDD(VH)-VSS VDD(WH)-VSS	-	-	0.30	mA
IQDDL		VDD(L) = 15 V, LIN(U,V,W) = 0 V	VDD(L)-VSS	-	-	3.50	mA
IPDDH	Operating VCC Supply Current	$\label{eq:VDD} \begin{array}{l} \text{VDD}(\text{UH},\text{VH},\text{WH}) = 15 \text{ V}, \\ \text{f}_{\text{PWM}} = 20 \text{ kHz}, \text{Duty} = 50\%, \\ \text{Applied to one PWM Signal} \\ \text{Input for High-Side} \end{array}$	VDD(UH)-VSS VDD(VH)-VSS VDD(WH)-VSS	-	_	0.40	mA
IPDDL		$\begin{array}{l} VDD(L) = 15 \text{ V}, \\ f_{PWM} = 20 \text{ kHz}, \text{ Duty} = 50\%, \\ \text{Applied to one PWM Signal} \\ \text{Input for Low-Side} \end{array}$	VDD(L)-VSS	-	-	6.00	mA
IQBS	Quiescent VBS Supply Current	VBS = 15 V, HIN(U,V,W) = 0 V	VB(U)-VS(U) VB(V)-VS(V) VB(W)-VS(W)	-	-	0.30	mA
IPBS	Operating VBS Supply Current	$\label{eq:VDD} \begin{array}{l} VDD = VBS = 15 \ V, \\ f_{PWM} = 20 \ kHz, \ Duty = 50\%, \\ Applied \ to \ one \ PWM \ Signal \\ Input \ for \ High\text{-}Side \end{array}$	VB(U)-VS(U) VB(V)-VS(V) VB(W)-VS(W)	-	_	5.00	mA
VIN(ON)	ON Threshold Voltage	HIN(U,V,W)–VSS, LIN(U,V,W)–VSS	-	-	2.6	V
VIN(OFF)	OFF Threshold Voltage			0.8	-	_	V
VCIN(ref)	Short Circuit Trip Level	VDD = 15 V, CIN-VSS		0.46	0.48	0.50	V
UVDDD	Supply Circuit	Detection Level		10.3	-	12.5	V
UVDDR	Under-Voltage Protection	Reset Level		10.8	-	13.0	V
UVBSD	1	Detection Level		10.0	-	12.0	V
UVBSR	1	Reset Level		10.5	-	12.5	V
VTS	Voltage Output for LVIC Temperature Sensing Unit	VTS-VSS = 10 nF, Temp. = 2	5°C	0.905	1.030	1.155	V
VFOH	Fault Output Voltage	$\label{eq:VDD} \begin{array}{l} VDD = 0 \ V, \ CIN = 0 \ V, \\ VFO \ Circuit: \ 10 \ k\Omega \ to \ 5 \ V \ Pull-up \\ \\ \hline VDD = 0 \ V, \ CIN = 1 \ V, \\ VFO \ Circuit: \ 10 \ k\Omega \ to \ 5 \ V \ Pull-up \end{array}$		4.9	-	-	V
VFOL				-	-	0.95	V
t _{FOD}	Fault-Output Pulse Width	CFOD = 22 nF		1.6	2.4	-	ms

BOOTSTRAP SECTION

VF	Bootstrap Diode Forward Voltage	If = 0.1 A	3.4	4.6	5.8	V
RBOOT	Built-in Limiting Resistance		30	38	46	Ω

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

7. Performance guaranteed over the indicated operating temperature range by design and/or characterization tested at $T_J = T_A = 25^{\circ}C$. Low duty cycle pulse techniques are used during testing to maintain the junction temperature as close to ambient as possible.

8. The fault–out pulse width t_{FOD} depends on the capacitance value of CFOD according to the following approximate equation: $t_{FOD} = 0.1 \times 10^6 \times CFOD$ (s). 9. Values based on design and/or characterization.

Temperature of LVIC versus VTS Characteristics





Figure 4. Temperature of LVIC versus VTS Characteristics

PACKAGE DIMENSIONS

DIP39, 54.5x31.0 EP-2 CASE MODGX ISSUE O



NOTES:

- 1. DIMENSIONING AND TOLERANCING PER. ASME Y14.5M, 2009.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. DIMENSION b and c APPLY TO THE PLATED LEADS AND ARE MEASURED BETWEEN 1.00 AND 2.00 FROM THE LEAD TIP.
- 4. POSITION OF THE LEAD IS DETERMINED AT THE BASE OF THE LEAD WHERE IT EXITS THE PACKAGE BODY.
- 5. AREA FOR 2D BAR CODE.
- 6. SHORTENED/CUT PINS ARE 2,5,8,11,14,17,19,29, 30 AND 39.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdi/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor products are not application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves have any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal inju

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative