

## General Description

The 12N65 uses advanced planar stripe DMOS technology to provide excellent  $R_{DS(ON)}$  and superior switching performance, and withstand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency switched mode power supplies, active power factor correction based on half bridge topology.

## Features

- Fast switching
- 100% avalanche tested
- Improved dv/dt capability
- RoHS Compliant


## Product Summary

BVDSS	RDSON	ID
650V	0.75Ω	12A

## Applications

- Charger
- Adaptor
- Power Supply

## TO-220/220F Pin Configuration



## Absolute Maximum Ratings (Tc=25°C unless otherwise noted)

Symbol	Parameter	220	220F	Units
$V_{DSS}$	Drain-Source Voltage	650		V
$I_D$	Drain Current - Continuous (T <sub>C</sub> = 25°C) - Continuous (T <sub>C</sub> = 100°C)	12	12*	A
		7.4	7.4*	A
$I_{DM}$	Drain Current - Pulsed <sup>1</sup>	48	48*	A
$V_{GSS}$	Gate-Source Voltage	±30		V
$E_{AS}$	Single Pulsed Avalanche Energy <sup>2</sup>	865		mJ
$E_{AR}$	Repetitive Avalanche Energy <sup>1</sup>	23		mJ
dv/dt	Peak Diode Recovery dv/dt <sup>3</sup>	4.5		V/ns
$P_D$	Power Dissipation (T <sub>C</sub> = 25°C)	230	54	W
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Temperature Range	-55 to +150		°C
T <sub>L</sub>	Maximum lead temperature for soldering purposes, 1/8 from case for 5 seconds	300		°C

\* Drain current limited by maximum junction temperature

## Thermal Characteristics

Symbol	Parameter	220	220F	Units
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	0.54	2.33	°C/W
$R_{\theta CS}$	Thermal Resistance, Case-to-Sink Typ.	0.5	---	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	62.5	62.5	°C/W

**Electrical Characteristic (T<sub>c</sub>=25°C unless otherwise noted)**

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
<b>Off Characteristics</b>						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> = 0 V, I <sub>D</sub> = 250 μA	650	--	--	V
BV <sub>DSS</sub> / T <sub>J</sub>	Breakdown Voltage Temperature Coefficient	I <sub>D</sub> = 250 μA, Referenced to 25°C	--	0.7	--	V/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 650 V, V <sub>GS</sub> = 0 V	--	--	1	μA
		V <sub>DS</sub> = 520 V, T <sub>C</sub> = 125°C	--	--	10	
I <sub>GSSF</sub>	Gate-Body Leakage Current, Forward	V <sub>GS</sub> = 30 V, V <sub>DS</sub> = 0 V	--	--	100	nA
I <sub>GSSR</sub>	Gate-Body Leakage Current, Reverse	V <sub>GS</sub> = -30 V, V <sub>DS</sub> = 0 V	--	--	-100	nA
<b>On Characteristics</b>						
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	3	--	5	V
R <sub>DS(on)</sub>	Static Drain-Source On-Resistance	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 6A	--	0.63	0.75	Ω
<b>Dynamic Characteristics</b>						
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = 25 V, V <sub>GS</sub> = 0 V, f = 1.0 MHz	--	2500	--	pF
C <sub>oss</sub>	Output Capacitance		--	180	--	pF
C <sub>rss</sub>	Reverse Transfer Capacitance		--	20	--	pF
<b>Switching Characteristics <sup>4 5</sup></b>						
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> = 325 V, I <sub>D</sub> = 12A R <sub>G</sub> = 25Ω	--	30	--	ns
t <sub>r</sub>	Turn-On Rise Time		--	90	--	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		--	140	--	ns
t <sub>f</sub>	Turn-Off Fall Time		--	90	--	ns
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> = 520 V, I <sub>D</sub> = 12A V <sub>GS</sub> = 10 V	--	50	--	nC
Q <sub>gs</sub>	Gate-Source Charge		--	8	--	nC
Q <sub>gd</sub>	Gate-Drain Charge		--	20	--	nC
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
I <sub>S</sub>	Maximum Continuous Drain-Source Diode Forward Current		--	--	12	A
I <sub>SM</sub>	Maximum Pulsed Drain-Source Diode Forward Current		--	--	48	A
V <sub>SD</sub>	Drain-Source Diode Forward Voltage	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 10A	--	--	1.4	V
t <sub>rr</sub>	Reverse Recovery Time <sup>4</sup>	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 12A dI <sub>F</sub> / dt = 100 A/μs	--	430	--	ns
Q <sub>rr</sub>	Reverse Recovery Charge <sup>4</sup>		--	5	--	μC

note:

1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. L=11mH, I<sub>AS</sub>=12A, V<sub>DD</sub>=50V, R<sub>G</sub>=25 Ω, Starting T<sub>J</sub>=25 °C.
3. I<sub>SD</sub>≤12A, di/dt ≤ 200A/us, V<sub>DD</sub> ≤ BV<sub>DSS</sub>, Starting T<sub>J</sub> = 25°C.
4. Pulse Test: Pulse width ≤ 300us, Duty Cycle ≤ 2%.
5. Essentially Independent of Operating Temperature Typical Characteristics.

This product has been designed and qualified for the consumer market.  
Cmos assumes no liability for customers' product design or applications.  
Cmos reserves the right to improve product design, functions and reliability without notice.