# **MOSFET** – Power, N-Channel, SUPERFET<sup>®</sup> III, Automotive, Easy-drive 650 V, 24 A, 125 mΩ

# NVB125N65S3

#### Description

SUPERFET III MOSFET is ON Semiconductor's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provides superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET Easy drive series helps manage EMI issues and allows for easier design implementation.

#### Features

- AEC-Q101 Qualified
- 700 V @ T<sub>J</sub> = 150°C
- Typ.  $R_{DS(on)} = 105 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ.  $Q_g = 46 \text{ nC}$ )
- Low Effective Output Capacitance (Typ. Coss(eff.) = 439 pF)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant

#### Applications


- Automotive On Board Charger
- Automotive DC/DC Converter for HEV



## **ON Semiconductor®**


#### www.onsemi.com

V <sub>DSS</sub>	R <sub>DS(ON)</sub> MAX	I <sub>D</sub> MAX		
650 V	125 m $\Omega$ @ 10 V	24 A		





#### MARKING DIAGRAM



#### ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

Symbol	Parameter	Value	Unit	
V <sub>DSS</sub>	Drain to Source Voltage		650	V
V <sub>GSS</sub>	Gate to Source Voltage	– DC	±30	V
		– AC (f > 1 Hz)	±30	
ID	Drain Current	– Continuous (T <sub>C</sub> = 25°C)	24	А
		– Continuous (T <sub>C</sub> = 100°C)	15	
I <sub>DM</sub>	Drain Current	– Pulsed (Note 1)	60	А
E <sub>AS</sub>	Single Pulsed Avalanche Energy (Note 2)	Single Pulsed Avalanche Energy (Note 2)		
I <sub>AS</sub>	Avalanche Current (Note 2)	3.7	А	
E <sub>AR</sub>	Repetitive Avalanche Energy (Note 1)		1.81	mJ
dv/dt	MOSFET dv/dt		100	V/ns
	Peak Diode Recovery dv/dt (Note 3)		20	
PD	Power Dissipation	(T <sub>C</sub> = 25°C)	181	W
		– Derate Above 25°C	1.45	W/°C
TJ, T <sub>STG</sub>	Operating and Storage Temperature Range		–55 to +150	°C
ΤL	Maximum Lead Temperature for Soldering, 1/8"	300	°C	

#### ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25°C, Unless otherwise noted)

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Repetitive rating: pulse-width limited by maximum junction temperature. 2.  $I_{AS} = 3.7 \text{ A}$ ,  $R_G = 25 \Omega$ , starting  $T_J = 25^{\circ}C$ . 3.  $I_{SD} \le 12 \text{ A}$ , di/dt  $\le 200 \text{ A}/\mu\text{s}$ ,  $V_{DD} \le 400 \text{ V}$ , starting  $T_J = 25^{\circ}C$ .

#### **THERMAL CHARACTERISTICS**

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max.	0.69	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max.	40	

#### PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Reel Size	Tape Width	Shipping <sup>†</sup>
NVB125N65S3	NVB125N65S3	D <sup>2</sup> -PAK	330 mm	24 mm	800 / Tape & Reel


+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### ELECTRICAL CHARACTERISTICS (T<sub>C</sub> = 25°C unless otherwise noted)


Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
OFF CHARACT	ERISTICS	•				
BV <sub>DSS</sub>	Drain to Source Breakdown Voltage	$V_{GS}$ = 0 V, $I_D$ = 1 mA, $T_J$ = 25°C	650			V
		$V_{GS}$ = 0 V, $I_{D}$ = 1 mA, $T_{J}$ = 150°C	700			V
$\Delta \text{BV}_{\text{DSS}}  /  \Delta \text{T}_{\text{J}}$	Breakdown Voltage Temperature Coefficient	$I_D = 1 \text{ mA}$ , Referenced to $25^{\circ}\text{C}$		0.68		V/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	$V_{DS} = 650 \text{ V}, V_{GS} = 0 \text{ V}$			1	μA
		$V_{DS}$ = 520 V, $T_{C}$ = 125°C		1.35		
I <sub>GSS</sub>	Gate to Body Leakage Current	$V_{GS}$ = $\pm 30$ V, $V_{DS}$ = 0 V			±100	nA
ON CHARACTE	RISTICS	-				
V <sub>GS(th)</sub>	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_D = 0.59 \text{ mA}$	2.5		4.5	V
R <sub>DS(on)</sub>	Static Drain to Source On Resistance	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 12 A		105	125	mΩ
9 <sub>FS</sub>	Forward Transconductance	V <sub>DS</sub> = 20 V, I <sub>D</sub> = 12 A		16		S
DYNAMIC CHAI	RACTERISTICS	•	•		•	
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = 400 V, V <sub>GS</sub> = 0 V, f = 1 MHz		1940		pF
C <sub>oss</sub>	Output Capacitance			40		pF
C <sub>oss(eff.)</sub>	Effective Output Capacitance	$V_{DS}$ = 0 V to 400 V, $V_{GS}$ = 0 V		439		pF
C <sub>oss(er.)</sub>	Energy Related Output Capacitance	$V_{DS}$ = 0 V to 400 V, $V_{GS}$ = 0 V		62		pF
Q <sub>g(tot)</sub>	Total Gate Charge at 10 V	V <sub>DS</sub> = 400 V, I <sub>D</sub> = 12 A, V <sub>GS</sub> = 10 V (Note 4)		46		nC
Q <sub>gs</sub>	Gate to Source Gate Charge			12		nC
Q <sub>gd</sub>	Gate to Drain "Miller" Charge			19		nC
ESR	Equivalent Series Resistance	f = 1 MHz		0.5		Ω
WITCHING CH	IARACTERISTICS	-				
t <sub>d(on)</sub>	Turn-On Delay Time	$V_{DD} = 400 \text{ V}, \text{ I}_{D} = 12 \text{ A}, \text{ V}_{GS} = 10 \text{ V},$		21		ns
t <sub>r</sub>	Turn-On Rise Time	R <sub>g</sub> = 4.7 Ω (Note 4)		19		ns
t <sub>d(off)</sub>	Turn-Off Delay Time			48		ns
t <sub>f</sub>	Turn-Off Fall Time			4.6		ns
SOURCE-DRAII	N DIODE CHARACTERISTICS		-	-	-	-
ا <sub>S</sub>	Maximum Continuous Source to Drain Diode Forward Current				24	Α
I <sub>SM</sub>	Maximum Pulsed Source to Drain Diode Forward Current		1	1	60	А
V <sub>SD</sub>	Source to Drain Diode Forward Voltage	$V_{GS} = 0 V, I_{SD} = 12 A$			1.2	V
t <sub>rr</sub>	Reverse Recovery Time	V <sub>DD</sub> = 400 V, I <sub>SD</sub> = 12 A,		339		ns
Q <sub>rr</sub>	Reverse Recovery Charge	dI <sub>F</sub> /dt = 100 A/µs		5.7	1	μC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 4. Essentially independent of operating temperature typical characteristics.

#### **TYPICAL CHARACTERISTICS**







#### **TYPICAL CHARACTERISTICS**





Figure 17. Transient Thermal Response









Figure 19. Resistive Switching Test Circuit & Waveforms









Figure 21. Peak Diode Recovery dv/dt Test Circuit & Waveforms


SUPERFET is a registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

#### **MECHANICAL CASE OUTLINE** PACKAGE DIMENSIONS









© Semiconductor Components Industries, LLC, 2018

rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative