ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET - N-Channel, SUPERFET® II, FRFET®

650 V, 10.2 A, 380 mΩ

FCPF380N65FL1-F154

Description

SUPERFET II MOSFET is ON Semiconductor's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate. Consequently, SUPERFET II MOSFET is very suitable for the various power system for miniaturization and higher efficiency. SUPERFET II FRFET MOSFET's optimized reverse recovery performance of body diode can remove additional component and improve system reliability.

Features

- 700 V @ T_J = 150°C
- $R_{DS(on)} = 320 \text{ m}\Omega \text{ (Typ.)}$
- Ultra Low Gate Charge (Typ. Q_g = 33 nC)
- Low Effective Output Capacitance (Typ. Coss(eff.) = 165 pF)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant

Applications


- Computing / Display Power Supplies
- Telecom / Server Power Supplies
- Industrial Power Supplies
- Lighting / Charger / Adapter



ON Semiconductor®

www.onsemi.com

V _{DSS}	R _{DS(ON)} MAX	I _D MAX	
650 V	380 mΩ @ 10 V	10.2 A	





TO-220F Ultra Narrow Lead CASE 221BN

MARKING DIAGRAM



\$Y = ON Semiconductor Logo &Z = Assembly Plant Code &3 = Data Code (Year & Week)

 $\mathsf{K} = \mathsf{Lot}$

FCPF380N65F = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^{\circ}C$, Unless otherwise noted)

Symbol	Parameter	Value	Unit	
V _{DSS}	Drain to Source Voltage		650	V
V_{GSS}	Gate to Source Voltage	- DC	±20	V
		- AC (f > 1 Hz)	±30	
I _D	Drain Current	– Continuous (T _C = 25°C)	10.2	Α
		- Continuous (T _C = 100°C)	6.4	
I _{DM}	Drain Current	- Pulsed (Note 1)	30.6	Α
E _{AS}	Single Pulsed Avalanche Energy (Note 2)		212	mJ
I _{AS}	Avalanche Current (Note 2)		2.3	Α
E _{AR}	Repetitive Avalanche Energy (Note 1)		0.33	mJ
dv/dt	MOSFET dv/dt		100	V/ns
	Peak Diode Recovery dv/dt (Note 3)		50	
P_{D}	Power Dissipation	(T _C = 25°C)	33	W
		- Derate Above 25°C	0.26	W/°C
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to +150	°C
TL	Maximum Lead Temperature for Soldering, 1/8" from Case for 5 Seconds		300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected. 1. Repetitive rating: pulse width limited by maximum junction temperature. 2. $I_{AS} = 2.3 \text{ A}$, $R_{G} = 25 \Omega$, starting $T_{J} = 25^{\circ}\text{C}$. 3. $I_{SD} \le 5.1 \text{ A}$, di/dt $\le 200 \text{ A}/\mu\text{s}$, $V_{DD} \le 380 \text{ V}$, starting $T_{J} = 25^{\circ}\text{C}$.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{ heta JC}$	Thermal Resistance, Junction to Case, Max.	3.8	°C/W
$R_{ heta JA}$	R ₀ JA Thermal Resistance, Junction to Ambient, Max.		°C/W

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Shipping
FCPF380N65FL1-F154	FCPF380N65F	TO-220F (Pb-Free)	50 Units / Tube

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
OFF CHARACT	ERISTICS			•		
BV _{DSS}	Drain to Source Breakdown Voltage	V_{GS} = 0 V, I_D = 10 mA, T_J = 25°C	650	-	_	V
		V _{GS} = 0 V, I _D = 10 mA, T _J = 150°C	700	-	-	V
$\Delta BV_{DSS}/\Delta T_{J}$	Breakdown Voltage Temperature Coefficient	I _D = 10 mA, Referenced to 25°C	-	0.72	=	V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 650 V, V _{GS} = 0 V	-	-	10	μΑ
		V _{DS} = 520 V, V _{GS} = 0 V, T _C = 125°C	-	40	-	
I _{GSS}	Gate to Source Leakage Current	V _{GS} = ±20 V, V _{DS} = 0 V	ı	-	±100	μΑ
ON CHARACTE	ERISTICS					
V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 1 \text{ mA}$	3	-	5	V
R _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 5.1 A	-	320	380	mΩ
9 _{FS}	Forward Transconductance	V _{DS} = 20 V, I _D = 5.1 A	-	9.9	-	S
OYNAMIC CHA	RACTERISTICS					-
C _{iss}	Input Capacitance	V _{DS} = 100 V, V _{GS} = 0 V, f = 1 MHz	-	1265	1680	pF
C _{oss}	Output Capacitance		-	42	55	pF
C _{rss}	Reverse Transfer Capacitance		-	1.0	-	pF
C _{oss}	Output Capacitance	V _{DS} = 380 V, V _{GS} = 0 V, f = 1 MHz	-	25	-	pF
C _{oss(eff.)}	Effective Output Capacitance	V _{DS} = 0 V to 400 V, V _{GS} = 0 V	-	165	-	pF
Q _{g(tot)}	Total Gate Charge at 10 V	$V_{DS} = 380 \text{ V}, I_D = 5.1 \text{ A}, V_{GS} = 10 \text{ V}$	-	33	43	nC
Q_{gs}	Gate to Source Gate Charge	(Note 4)	-	6.6	-	nC
Q_{gd}	Gate to Drain "Miller" Charge		-	14	-	nC
ESR	Equivalent Series Resistance	f = 1 MHz	ı	0.46	-	Ω
WITCHING CH	HARACTERISTICS					
t _{d(on)}	Turn-On Delay Time	$V_{DD} = 380 \text{ V}, I_D = 5.1 \text{ A}, V_{GS} = 10 \text{ V},$	-	18	46	ns
t _r	Turn-On Rise Time	$R_g = 4.7 \Omega$ (Note 4)	-	7.8	25.6	ns
t _{d(off)}	Turn-Off Delay Time		-	45	100	ns
t _f	Turn-Off Fall Time		-	8	26	ns
SOURCE-DRA	IN DIODE CHARACTERISTICS					-
I _S	Maximum Continuous Source to Drain Diode Forward Current		_	-	10.2	Α
I _{SM}	Maximum Pulsed Source to Drain Diode Forward Current		_	-	30.6	Α
V _{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _{SD} = 5.1 A	_	-	1.2	V
t _{rr}	Reverse Recovery Time	$V_{DD} = 400 \text{ V}, I_{SD} = 5.1 \text{ A},$	_	84	-	ns
Q _{rr}	Reverse Recovery Charge	dI _F /dt = 100 A/μs	_	224	_	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature.

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 6. Gate Charge Characteristics

TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 11. E_{OSS} vs. Drain to Source Voltage




Figure 8. On-Resistance Variation vs. Temperature




Figure 10. Maximum Drain Current vs. Case Temperature

TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 12. Transient Thermal Response Curve




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms




Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms




Figure 16. Peak Recovery dv/dt Test Circuit & Waveforms

SUPERFET and FRFET are a registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

PACKAGE DIMENSIONS


TO-220 FULLPACK, 3-LEAD


CASE 221BN ISSUE O



NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. CONTOUR UNCONTROLLED IN THIS AREA.
- DIMENSIONS EXCLUDE BURRS, MOLD FLASH, AND TIE BAR PROTRUSIONS.





MILLIMETERS			
MIN.	N□M.	MAX.	
4.60	4.70	4.80	
2.50	2.60	2.70	
2.47	2.57	2.67	
0.56	0.63	0.69	
		0.90	
0.46	0.53	0.59	
15.80	16.00	16.20	
9.58	9.68	9.78	
10.00	10.20	10.40	
2.54 BSC			
6.32 REF			
13.45	13.60	13.75	
1.70	1.80	1.90	
3.00	3.10	3.20	
3,25	3.35	3.45	
	MIN. 4.60 2.50 2.47 0.56 0.46 15.80 9.58 10.00 13.45 1.70 3.00	MIN. NDM. 4.60 4.70 2.50 2.60 2.47 2.57 0.56 0.63 0.46 0.53 15.80 16.00 9.58 9.68 10.00 10.20 2.54 BSC 6.32 REF 13.45 13.60 1.70 1.80 3.00 3.10	

ON Semiconductor and the are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor newsers on warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemn

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative