

F1-2PACK SIC MOSFET Module

Advance Information

NXH010P120MNF1PTNG, NXH010P120MNF1PNG, NXH010P120MNF1PTG, NXH010P120MNF1PG

General Description

The NXH010P120MNF1 is a power module containing an $10~\text{m}\Omega/1200~\text{V}$ SiC MOSFET half bridge and a thermistor in an F1 package.

Features

- 10 mΩ/1200V SiC MOSFET Half Bridge
- Thermistor
- Options With Pre-Applied Thermal Interface Material (TIM) and Without Pre-Applied TIM
- Press-Fit Pins

Typical Applications

- Solar Inverter
- Uninterruptible Power Supplies
- Electric Vehicle Charging Stations
- Industrial Power





Figure 1. NXH010P120MNF1 Schematic Diagram

This document contains information on a new product. Specifications and information herein are subject to change without notice.



PIM18 33.8x42.5 (PRESS FIT) CASE 180BW

MARKING DIAGRAM

NXH010P120MNF1z = Specific Device Code
z = PTNG/PNG/PTG/PG
AT = Assembly & Test Site Code
YYWW = Year and Work Week Code

ORDERING INFORMATION

See detailed ordering and shipping information on page of this data sheet.

$\begin{array}{c} NXH010P120MNF1PTNG,\ NXH010P120MNF1PNG,\ NXH010P120MNF1PTG,\\ NXH010P120MNF1PG \end{array}$

PIN CONNECTIONS




Figure 2. Pin Connections

PIN FUNCTION DESCRIPTION

Pin	Name	Description		
8	TH1	Thermistor Connection 1		
7	TH2	Thermistor Connection 2		
1	DC+	DC Positive Bus connection		
2	DC+	DC Positive Bus connection		
13	PHASE	Center point of half bridge		
14	PHASE	Center point of half bridge		
9	DC-	DC Negative Bus connection		
3	S1	Q1 Kelvin Emitter (High side switch)		
4	G1	Q1 Gate (High side switch)		
10	DC-	DC Negative Bus connection		
15	G2	Q2 Gate (Low side switch)		
16	S2	Q2 Kelvin Emitter (High side switch)		
11	DC-	DC Negative Bus connection		
12	DC-	DC Negative Bus connection		
5	DC+	DC Positive Bus connection		
6	DC+	DC Positive Bus connection		
17	PHASE	Center point of half bridge		
18	PHASE	Center point of half bridge		

Table 1. ABSOLUTE MAXIMUM RATINGS (Note 1)

Rating	Symbol	Value	Unit
SIC MOSFET			
Drain-Source Voltage	V _{DSS}	1200	V
Gate-Source Voltage	V _{GS}	+25/–15	V
Continuous Drain Current @ T _C = 80°C (T _J = 175°C)	I _D	114	А
Pulsed Drain Current (T _J = 175°C)	I _{Dpulse}	342	А
Maximum Power Dissipation (T _J = 175°C)	P _{tot}	250	W
Short Circuit Withstand Time @ $V_{GE} = -5V/20 V$, $V_{CE} = 600 V$, $T_{J} \le 150^{\circ}C$	T _{sc}	2	μs
Minimum Operating Junction Temperature	T _{JMIN}	-40	°C
Maximum Operating Junction Temperature	T_{JMAX}	175	°C
THERMAL PROPERTIES			
Storage Temperature range	T _{stg}	-40 to 150	°C
INSULATION PROPERTIES			
Isolation test voltage, t = 1 sec, 60 Hz	V _{is}	4800	V _{RMS}
Creepage distance		12.7	mm

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe

RECOMMENDED OPERATING RANGES

Rating	Symbol	Min	Max	Unit
Module Operating Junction Temperature	T_J	-40	150	°C

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS

 $T_J = 25^{\circ}C$ unless otherwise noted

Parameter	Test Conditions	Test Conditions Symbol		Тур	Max	Unit	
SIC MOSFET CHARACTERISTICS							
Drain-Source Breakdown Voltage	$V_{GS} = 0 \text{ V}, I_D = 400 \mu\text{A}$	V _{(BR)DSS}	1200	-	-	V	
Zero Gate Voltage Drain Current	V _{GS} = 0 V, V _{DS} = 1200 V	I _{DSS}	_	_	200	μΑ	
Drain-Source On Resistance	$V_{GS} = 20 \text{ V}, I_D = 100 \text{ A},$ $T_J = 25^{\circ}\text{C}$	R _{DS(ON)}	_	10.5	14	mΩ	
	V _{GS} = 20 V, I _D = 100 A, T _J = 125°C		_	14.1	_		
	V _{GS} = 20 V, I _D = 100 A, T _J = 150°C		_	14.5	-		
Gate-Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 40 \text{ mA}$	V _{GS(TH)}	1.8	2.90	4.3	V	
Gate Leakage Current	$V_{GS} = -10/20 \text{ V}, V_{DS} = 0 \text{ V}$	I _{GSS}	-500	-	500	nA	
Internal Gate Resistance		R_{G}		0.8		Ω	
Input Capacitance	$V_{DS} = 800 \text{ V}, V_{GS} = 0 \text{ V}.$	C _{ISS}	=	4707	-	pF	
Reverse Transfer Capacitance	f = 1 MHz	C _{RSS}	_	39	_		
Output Capacitance		C _{OSS}	_	548	_		
C _{OSS} Stored Energy	V _{DS} = 0 V to 800 V, V _{GS} = 0 V	E _{OSS}	_	221	_	μJ	
Total Gate Charge	V _{DS} = 800 V. V _{GS} = 20 V.	Q _{G(TOTAL)}	_	454	_	nC	
Gate-Source Charge	I _D = 100 A	Q _{GS}	_	129	_	nC	
Gate-Drain Charge	in Charge		-	131	-	nC	

Operating parameters.

$\begin{array}{c} NXH010P120MNF1PTNG,\ NXH010P120MNF1PNG,\ NXH010P120MNF1PTG,\\ NXH010P120MNF1PG \end{array}$

ELECTRICAL CHARACTERISTICS (continued)

 $T_J = 25^{\circ}C$ unless otherwise noted


Parameter	Test Conditions	Symbol	Min	Тур	Max	Unit
SIC MOSFET CHARACTERISTICS						
Turn-on Delay Time	T _J = 25°C	t _{d(on)}	_	44.2	_	ns
Rise Time	$V_{DS} = 600 \text{ V}, I_D = 100 \text{ A}$ $V_{GS} = -5\text{V}/18\text{V}, R_G = 2 \Omega$	t _r	_	16.2	_	
Turn-off Delay Time		t _{d(off)}	_	136.6	_	
Fall Time	1	t _f	_	9.8	_	
Turn-on Switching Loss per Pulse		E _{ON}	_	0.95	_	mJ
Turn off Switching Loss per Pulse]	E _{OFF}	_	0.72	_	1
Turn-on Delay Time	T _J = 150°C	t _{d(on)}	_	40.2	_	ns
Rise Time	$V_{DS} = 600 \text{ V}, I_D = 100 \text{ A}$ $V_{GS} = -5\text{V}/18\text{V}, R_G = 2 \Omega$	t _r	_	14.9	_	1
Turn-off Delay Time		t _{d(off)}	_	150.3	_	1
Fall Time	1	t _f	_	12.7	_	
Turn-on Switching Loss per Pulse	1	E _{ON}	_	1.1	_	mJ
Turn off Switching Loss per Pulse]	E _{OFF}	_	0.81	_	1
Diode Forward Voltage	I _D = 100 A, T _J = 25°C	V _{SD}	_	3.94	6	V
	I _D = 100 A, T _J = 150°C		_	3.42	_	1
Reverse Recovery Time	T _J = 25°C	t _{rr}	<u> </u>	24.2	_	ns
Reverse Recovery Charge	$V_{DS} = 600 \text{ V}, I_{D} = 100 \text{ A}$	Q _{rr}	_	1207	_	nC
Peak Reverse Recovery Current	$V_{GS} = -5V/18V, R_G = 2 \Omega$	I _{RRM}	_	79.8	_	Α
Peak Rate of Fall of Recovery Current	1	di/dt	_	7570	_	A/μs
Reverse Recovery Energy]	E _{rr}	_	516	_	μJ
Reverse Recovery Time	T _J = 150°C	t _{rr}	_	31.2	_	ns
Reverse Recovery Charge	$V_{DS} = 600 \text{ V}, I_{D} = 100 \text{ A}$	Q _{rr}	<u> </u>	2591	_	μС
Peak Reverse Recovery Current	$V_{GS} = -5V/18V, R_G = 2 \Omega$	I _{RRM}	_	134.2	_	Α
Peak Rate of Fall of Recovery Current	1	di/dt	_	11849	_	A/μs
Reverse Recovery Energy]	E _{rr}	_	1198	_	μJ
Thermal Resistance - chip-to-case	M1,M2	R _{thJC}	_	0.23	_	°C/W
Thermal Resistance – chip-to-heatsink	Thermal Resistance - chip-to- heatsink, Thermal grease, Thickness = 2 Mil _2%, A = 2.8 W/mK	R _{thJH}	-	0.38	-	°C/W
THERMISTOR CHARACTERISTICS						
Nominal resistance	T = 25°C	R ₂₅	=	5	=	kΩ
Nominal resistance	T = 100°C	R ₁₀₀	T -	457	_	Ω
Deviation of R25		ΔR/R	-3	_	3	%
Power dissipation		P_{D}	_	50	_	mW
Power dissipation constant			_	5	_	mW/K
B-value	B(25/50), tolerance ±3%		_	3375	=	K
B-value	B(25/100), tolerance ±3%		_	3455	_	K

$\begin{array}{c} NXH010P120MNF1PTNG,\ NXH010P120MNF1PNG,\ NXH010P120MNF1PTG,\\ NXH010P120MNF1PG \end{array}$

ORDERING INFORMATION

Orderable Part Number	Specific Device Marking	Package Type	Shipping [†]
NXH010P120MNF1PNG	NXH010P120MNF1PNG	F1-2PACK: Case 180BW Press-fit Pins, Ni-Plated DBC (Pb-Free and Halide-Free)	28 Units / Blister Tray
NXH010P120MNF1PTNG	NXH010P120MNF1PTNG	F1-2PACK: Case 180BW Press-fit Pins, Ni-Plated DBC with pre-applied thermal interface material (TIM) (Pb-Free and Halide-Free)	28 Units / Blister Tray
NXH010P120MNF1PG	NXH010P120MNF1PG	F1-2PACK: Case 180BW Press-fit Pins, Copper DBC (Pb-Free and Halide-Free)	28 Units / Blister Tray
NXH010P120MNF1PTG	NXH010P120MNF1PTG	F1-2PACK: Case 180BW Press-fit Pins, Copper DBC with pre-applied thermal interface material (TIM) (Pb-Free and Halide-Free)	28 Units / Blister Tray


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.



140 —20V 19V 120 18V ID, DRAIN CURRENT (A) 17V 100 -16V 15V 80 _14\/ 13V 60 -12V —10V 40 VGS, T_.= 125°C 20 0.0 2.0 8.0 10.0 V_{DS}, DRAIN-SOURCE VOLTAGE (V)

Figure 3. MOSFET Typical Output Characteristics

Figure 4. MOSFET Typical Output Characteristics







Figure 5. MOSFET Typical Output Characteristics

Figure 6. MOSFET Typical Transfer Characteristics






Figure 7. Body Diode Forward Characteristic

Figure 8. Gate-to-Source Voltage vs. Total Charge

TYPICAL CHARACTERISTICS

SiC MOSFET (M1, M2)




Figure 9. Capacitance vs. Drain-to-Source Voltage




Figure 10. SiC Mosfet Junction- to-Case Transient Thermal Impedance

Element #	M1		M2		
	Rth (K/W)	Cth (Ws/K)	Rth (K/W)	Cth (Ws/K)	
1	0.00569	0.00195	0.01290	0.00461	
2	0.01079	0.00951	0.02387	0.02538	
3	0.03005	0.01813	0.04253	0.02953	
4	0.08398	0.08121	0.07199	0.08994	
5	0.09325	0.11117	0.07823	0.06854	

Figure 11. Table of Cauer Networks-M1, M2

TYPICAL CHARACTERISTICS

M1/M2 MOSFET SWITCHING CHARACTERISTICS





Figure 14. Typical Switching Loss E_{Off} vs. IC

I_C(A)

Figure 15. Typical Switching Loss $E_{\mbox{Off}}$ vs. $R_{\mbox{G}}$

 $R_G(\Omega)$



1.0

Figure 16. Typical Turn-On Switching T_{don} vs. IC

Figure 17. Typical Turn-On Switching T_{don} vs. R_G

TYPICAL CHARACTERISTICS

M1/M2 MOSFET SWITCHING CHARACTERISTICS





Figure 22. Typical Turn-Off Switching Tf vs. IC

Figure 23. Typical Turn-Off Switching Tf vs. RG

TYPICAL CHARACTERISTICS

M1/M2 MOSFET SWITCHING CHARACTERISTICS






Figure 26. Typical Reverse Recovery Time vs. IC

Figure 27. Typical Reverse Recovery Time vs. R_G




Figure 28. Typical Reverse Recovery Charge vs. IC

Figure 29. Typical Reverse Recovery Charge vs. R_G

TYPICAL CHARACTERISTICS

M1/M2 MOSFET SWITCHING CHARACTERISTICS




Figure 30. Typical Reverse Recovery Current vs. IC

Figure 31. Typical Reverse Recovery Current vs. R_G




Figure 32. Typical di/dt vs. IC


Figure 33. Typical di/dt vs. R_G

$\begin{array}{c} {\sf NXH010P120MNF1PTNG,\ NXH010P120MNF1PNG,\ NXH010P120MNF1PTG,}\\ {\sf NXH010P120MNF1PG} \end{array}$

PACKAGE DIMENSIONS

PIM18 33.8x42.5 (PRESS FIT)


CASE 180BW ISSUE B




NOTES

- 1. CONTROLLING DIMENSION: MILLIMETERS
- 2. PIN POSITION TOLERANCE IS ± 0.4mm

	MILLIMETERS			
DIM	MIN.	NOM.	MAX.	
Α	11.65	12.00	12.35	
A 1	16.00	16.50	17.00	
A2	0.00	0.35	0.60	
А3	12.85	13.35	13.85	
b	1.15	1.20	1.25	
b1	0.59	0.64	0.69	
D	33.50	33.80	34.10	
D1	4.40	4.50	4.60	
D2	27.95	28.10	28.25	
E	47.70	48.00	48.30	
E1	42.35	42.50	42.65	
E2	52.90	53.00	53.10	
E3	62.30	62.80	63.30	
E4	4.90	5.00	5.10	
Р	2.20	2.30	2.40	





RECOMMENDED MOUNTING PATTERN

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Sho

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative