

TinyLogic HST 2-Input NAND Gate

NC7ST00

Description

The NC7ST00 is a single 2–Input high performance CMOS NAND Gate, with TTL–compatible inputs. Advanced Silicon Gate CMOS fabrication assures high speed and low power circuit operation. ESD protection diodes inherently guard both inputs and output with respect to the V_{CC} and GND rails. High gain circuitry offers high noise immunity and reduced sensitivity to input edge rate. The TTL–compatible inputs facilitate TTL to NMOS / CMOS interfacing. Device performance is similar to MM74HCT but with 1/2 the output current drive of HC / HCT.

Features

- Space Saving SOT23-5, SC-74A and SC-88A 5-Lead Package
- Ultra Small MicroPak™ Leadless Package
- High Speed: $t_{PD} < 7$ ns Typ, $V_{CC} = 5$ V, $C_L = 15$ pF
- Low Quiescent Power: $I_{CC} < 1 \mu A$ Typ, $V_{CC} = 5.5 \text{ V}$
- Balanced Output Drive: 2 mA I_{OL}, -2 mA I_{OH}
- TTL-compatible Inputs
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant





Figure 1. Logic Symbol

MARKING DIAGRAMS



SIP6 CASE 127EB





SC-74A CASE 318BQ





SOT23-5 CASE 527AH





SC-88A CASE 419A-02



E3, 8S00, T00 = Specific Device Code

KK = 2-Digit Lot Run Traceability Code

XY = 2-Digit Date Code FormatZ = Assembly Plant Code

M = Date Code

■ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 4 of this data sheet.

NC7ST00

Pin Configurations




Figure 2. SOT23-5, SC-88A and SC-74A (Top View)




Figure 3. MicroPak (Top Through View)

PIN DESCRIPTIONS

| Pin Names | Description |
|-----------|-------------|
| A, B | Inputs |
| Y | Output |
| NC | No Connect |

FUNCTION TABLE $(Y = \overline{AB})$

| Inp | Output | |
|-----|--------|---|
| Α | В | Υ |
| L | L | Н |
| L | Н | Н |
| Н | L | Н |
| Н | Н | L |

H = HIGH Logic Level L = LOW Logic Level

ABSOLUTE MAXIMUM RATINGS

| Symbol | Paramete | r | Min | Max | Unit |
|-------------------------------------|---|------------------------------------|------|-----------------------|------|
| V _{CC} | Supply Voltage | | -0.5 | 6.5 | V |
| I _{IK} | DC Input Diode Current | V _{IN} < 0 V | - | -20 | mA |
| | | V _{IN} > V _{CC} | - | +20 | |
| V _{IN} | DC Input Voltage | | -0.5 | V _{CC} + 0.5 | V |
| l _{ok} | DC Output Diode Current V _{OUT} < 0 V | | - | -20 | mA |
| | | V _{OUT} > V _{CC} | - | +20 | |
| V _{OUT} | Output Voltage | | -0.5 | V _{CC} + 0.5 | V |
| l _{out} | DC Output Source or Sink Current | | - | ±12.5 | mA |
| I _{CC} or I _{GND} | DC V _{CC} or Ground Current per Supply Pin | | - | ±25 | mA |
| T _{STG} | Storage Temperature | | -65 | +150 | °C |
| TJ | Junction Temperature | | - | +150 | °C |
| TL | Lead Temperature (Soldering, 10 Seconds) | | - | +260 | °C |
| P_{D} | Power Dissipation in Still Air | SC-74A / SOT23-5 | - | 390 | mW |
| | | SC-88A | - | 332 | |
| | | MicroPak-6 | - | 812 | |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

NC7ST00

RECOMMENDED OPERATING CONDITIONS

| Symbol | Parameter | Conditions | Min | Max | Unit |
|---------------------------------|--------------------------|-------------------------|-----|-----------------|------|
| V _{CC} | Supply Voltage | | 4.5 | 5.5 | V |
| V _{IN} | Input Voltage | | 0 | V _{CC} | V |
| V _{OUT} | Output Voltage | | 0 | V _{CC} | V |
| T _A | Operating Temperature | | -40 | +85 | °C |
| t _r , t _f | Input Rise and Fall Time | V _{CC} = 5.0 V | 0 | 10 | ns/V |
| θ_{JA} | Thermal Resistance | SC-74A / SOT23-5 | - | 320 | °C/W |
| | | SC-88A | - | 377 | |
| | | MicroPak-6 | - | 154 | |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

DC ELECTICAL CHARACTERISTICS

| | | | | T _A = +25°C | | ; | T _A = -40 | to +85°C | |
|------------------|---------------------------|---------------------|--|------------------------|-------------|-------------|----------------------|-------------|------|
| Symbol | Parameter | V _{CC} (V) | Conditions | Min | Тур | Max | Min | Max | Unit |
| V _{IH} | HIGH Level Input Voltage | 4.5 – 5.5 | | 2.0 | - | - | 2.0 | - | V |
| V _{IL} | LOW Level Input Voltage | 4.5 – 5.5 | | - | _ | 0.8 | _ | 0.8 | V |
| V _{OH} | HIGH Level Output Voltage | 4.5 4.5 | $\begin{split} I_{OH} &= -20 \ \mu\text{A} \\ I_{OH} &= -2 \ \text{mA} \\ V_{IN} &= V_{IH} \ \text{or} \ V_{IL} \end{split}$ | 4.4 4.18 | 4.5 4.35 | - | 4.4 4.13 | - | V |
| V _{OL} | LOW Level Output Voltage | 4.5 4.5 | $\begin{split} I_{OL} &= 20 \; \mu\text{A} \\ I_{OL} &= 2 \; \text{mA} \\ V_{IN} &= V_{IH} \; \text{or} \; V_{IL} \end{split}$ | - | 0 0.10 | 0.1 0.26 | - | 0.1 0.33 | ٧ |
| I _{IN} | Input Leakage Current | 5.5 | $0 \leq V_{IN} \leq 5.5 \text{ V}$ | - | - | ±0.1 | _ | ±1.0 | μΑ |
| Icc | Quiescent Supply Current | 5.5 | V _{IN} = V _{CC} or GND | - | _ | 1.0 | _ | 10.0 | μΑ |
| I _{CCT} | I _{CC} per Input | 5.5 | One Input V_{IN} = 0.5 V or 2.4 V, Other Input V_{CC} or GND | . 1 | ı | 2.0 | - | 2.9 | mA |

AC ELECTRICAL CHARACTERISTICS


| | | | | | T _A = +25°(| | $T_A = -40$ | to +85°C | |
|-------------------------------------|--|------------------------|------------------------|------|------------------------|-----|-------------|----------|------|
| Symbol | Parameter | V _{CC} (V) | Conditions | Min | Тур | Max | Min | Max | Unit |
| t _{PLH} , t _{PHL} | Propagation Delay (Figure 4, 6) | 5.0 | C _L = 15 pF | _ | 3.4 | 12 | - | - | ns |
| | | | | _ | 6.3 | 17 | - | _ | |
| | 4.5 | C _L = 50 pF | - | 6.0 | 16 | - | 20 | | |
| | | | - | 11.5 | 27 | - | 31 | | |
| | | 5.5 | | - | 4.1 | 14 | - | 18 | |
| | | | | - | 11.2 | 26 | - | 30 | |
| t _{TLH} , t _{THL} | Output Transition Time | 5.0 | C _L = 15 pF | - | 4 | 10 | - | - | ns |
| | (Figure 4, 6) | 4.5 | C _L = 50 pF | _ | 11 | 25 | - | 31 | |
| | 5.5 | | - | 10 | 21 | - | 26 | | |
| C _{IN} | Input Capacitance | Open | | _ | 2 | 10 | - | - | pF |
| C_{PD} | Power Dissipation Capacitance (Figure 5) | 5.0 | (Note 2) | _ | 6 | _ | - | _ | pF |

^{2.} C_{PD} is defined as the value of the internal equivalent capacitance which is derived from dynamic operating current. Current consumption (I_{CCD}) at no output loading and operating at 50% duty cycle. (See Figure 5). C_{PD} is related to I_{CCD} dynamic operating current by the expression: I_{CCD} = (C_{PD}) (V_{CC}) (f_{IN}) + (I_{CCstatic}).

^{1.} Unused inputs must be held HIGH or LOW. They may not float.

NC7ST00

AC Loading and Waveforms



 C_L includes load and stray capacitance Input PRR = 1.0 MHz, $t_W = 500 \ \text{ns}$

Figure 4. AC Test Circuit





Figure 6. AC Waveforms



Input = AC Waveform;

PRR = Variable; Duty Cycle = 50%.

Figure 5. I_{CCD} Test Circuit

ORDERING INFORMATION


| Device | Top Mark | Packages | Shipping [†] |
|-------------------|----------|----------------|-----------------------|
| NC7ST00M5X | 8S00 | SC-74A | 3000 / Tape & Reel |
| NC7ST00M5X-L22090 | 8S00 | SOT23-5 | 3000 / Tape & Reel |
| NC7ST00P5X | T00 | SC-88A | 3000 / Tape & Reel |
| NC7ST00P5X-L22057 | T00 | SC-88A | 3000 / Tape & Reel |
| NC7ST00L6X | E3 | SIP6, MicroPak | 5000 / Tape & Reel |
| NC7ST00L6X-L22175 | E3 | SIP6, MicroPak | 5000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MicroPak is trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.



DATE 31 AUG 2016



NOTES:

- 1. CONFORMS TO JEDEC STANDARD MO-252 VARIATION UAAD
- 2. DIMENSIONS ARE IN MILLIMETERS
- 3. DRAWING CONFORMS TO ASME Y14.5M-2009
 4. PIN ONE IDENTIFIER IS 2X LENGTH OF ANY


 - OTHER LINE IN THE MARK CODE LAYOUT.


| DOCUMENT NUMBER: | 98AON13590G | Electronic versions are uncontrolled except when accessed directly from the Document Repos Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | | |
|------------------|---------------|---|-------------|--|
| DESCRIPTION: | SIP6 1.45X1.0 | | PAGE 1 OF 1 | |


ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.




DATE 18 JAN 2018







RECOMMENDED SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NOTES:

- DIMENSIONING AND TOLERANCING PER ASME
 Y14.5M, 1994.
 CONTROLLING DIMENSION: MILLIMETERS.
 MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH
 THICKNESS. MINIMUM LEAD THICKNESS IS THE
 MINIMUM THICKNESS OF BASE MATERIAL.
- DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE.

| | MILLIMETERS | | | |
|-----|-------------|------|--|--|
| DIM | MIN | MAX | | |
| Α | 0.90 | 1.10 | | |
| A1 | 0.01 | 0.10 | | |
| b | 0.25 | 0.50 | | |
| С | 0.10 | 0.26 | | |
| D | 2.85 | 3.15 | | |
| E | 2.50 | 3.00 | | |
| E1 | 1.35 | 1.65 | | |
| е | 0.95 BSC | | | |
| L | 0.20 | 0.60 | | |
| М | 0 ° | 10° | | |

GENERIC MARKING DIAGRAM*



XXX = Specific Device Code

Μ = Date Code = Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ", may or may not be present. Some products may not follow the Generic Marking.

| DOCUMENT NUMBER: | 98AON66279G | Electronic versions are uncontrolled except when accessed directly from the Document Rep Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | | | |
|------------------|-------------|---|-------------|--|--|
| DESCRIPTION: | SC-74A | | PAGE 1 OF 1 | | |

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



SC-88A (SC-70-5/SOT-353) CASE 419A-02 **ISSUE L**

DATE 17 JAN 2013



- TES:
 DIMENSIONING AND TOLERANCING
 PER ANSI Y14.5M, 1982.
 CONTROLLING DIMENSION: INCH.
 419A-01 OBSOLETE. NEW STANDARD 3.
- 419A-02.
 DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

| | INC | HES | MILLIN | IETERS |
|-----|-----------|-------|----------|--------|
| DIM | MIN | MAX | MIN | MAX |
| Α | 0.071 | 0.087 | 1.80 | 2.20 |
| В | 0.045 | 0.053 | 1.15 | 1.35 |
| С | 0.031 | 0.043 | 0.80 | 1.10 |
| D | 0.004 | 0.012 | 0.10 | 0.30 |
| G | 0.026 | BSC | 0.65 BSC | |
| Н | | 0.004 | | 0.10 |
| J | 0.004 | 0.010 | 0.10 | 0.25 |
| K | 0.004 | 0.012 | 0.10 | 0.30 |
| N | 0.008 REF | | 0.20 | REF |
| S | 0.079 | 0.087 | 2 00 | 2 20 |






XXX = Specific Device Code

= Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.



0.50 0.0197 0.65 0.025 0.65 0.025 0.40 0.0157 1.9 mm 0.0748 SCALE 20:1

SOLDER FOOTPRINT

| STYLE 1: PIN 1. BASE 2. EMITTER 3. BASE 4. COLLECTOR | STYLE 2: PIN 1. ANODE 2. EMITTER 3. BASE 4. COLLECTOR | STYLE 3: PIN 1. ANODE 1 2. N/C 3. ANODE 2 4. CATHODE 2 | STYLE 4: PIN 1. SOURCE 1 2. DRAIN 1/2 3. SOURCE 1 4. GATE 1 | STYLE 5: PIN 1. CATHODE 2. COMMON ANODE 3. CATHODE 2 4. CATHODE 3 |
|--|---|--|---|---|
| 5. COLLECTOR | 5. CATHODE | 5. CATHODE 1 | 5. GATE 2 | 5. CATHODE 4 |

| 5. COLLECTOR | 5. CATHODE | 5. CATHODE 1 | 4. GATE 1 5. GATE 2 | 5. CATHODE 3 |
|-----------------------|--------------|----------------|------------------------|---|
| STYLE 6: | STYLE 7: | STYLE 8: | STYLE 9: | Note: Please refer to datasheet for style callout. If style type is not called out in the datasheet refer to the device datasheet pinout or pin assignment. |
| PIN 1. EMITTER 2 | PIN 1. BASE | PIN 1. CATHODE | PIN 1. ANODE | |
| 2. BASE 2 | 2. EMITTER | 2. COLLECTOR | 2. CATHODE | |
| 3. EMITTER 1 | 3. BASE | 3. N/C | 3. ANODE | |
| 4. COLLECTOR | 4. COLLECTOR | 4. BASE | 4. ANODE | |
| 5. COLLECTOR 2/BASE 1 | 5. COLLECTOR | 5. EMITTER | 5. ANODE | |

| DOCUMENT NUMBER: | 98ASB42984B | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | | |
|------------------|--------------------------|---|-------------|--|
| DESCRIPTION: | SC-88A (SC-70-5/SOT-353) | | PAGE 1 OF 1 | |

ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

DATE 09 JUN 2021



REFERENCE







В

F1 F

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 19894
- CONTROLLING DIMENSION: MILLIMETERS
- MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE
- DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS, MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.25 PER SIDE. D AND E1 DIMENSIONS ARE DETERMINED AT DATUM D.
- DIMENSION 'b' DOES NOT INCLUDE DAMBAR PROTRUSION. DAMBAR PROTRUSION SHALL BE O. 08mm TOTAL IN EXCESS OF THE 'b' DIMENSION AT MAXIMUM MATERIAL CONDITION. MINIMUM SPACE BETWEEN PROTRUSION AND AN ADJACENT LEAD SHALL NOT BE LESS THAN 0.07mm.



TOP VIEW




GENERIC MARKING DIAGRAM*



XXX = Specific Device Code = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "=", may or may not be present. Some products may not follow the Generic Marking.

| | MILLIMETERS | | | | |
|-----|-------------|------|------|--|--|
| DIM | MIN. | N□M. | MAX. | | |
| Α | 0.90 | _ | 1.45 | | |
| A1 | 0.00 | _ | 0.15 | | |
| A2 | 0.90 | 1.15 | 1.30 | | |
| b | 0.30 | _ | 0.50 | | |
| С | 0.08 | _ | 0.22 | | |
| D | 2.90 BSC | | | | |
| Ε | 2.80 BSC | | | | |
| E1 | 1.60 BSC | | | | |
| e | 0.95 BSC | | | | |
| L | 0.30 | 0.45 | 0.60 | | |
| L1 | 0.60 REF | | | | |
| L2 | 0.25 REF | | | | |
| θ | 0° | 4° | 8* | | |
| θ1 | 0° | 10° | 15° | | |
| θ2 | 0° | 10° | 15° | | |



RECOMMENDED MOUNTING FOOTPRINT

For additional information on our Pb-Free strategy and soldering details, please download the $\square N$ Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

| DOCUMENT NUMBER: | 98AON34320E | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. | | |
|------------------|----------------|---|-------------|--|
| DESCRIPTION: | SOT-23, 5 LEAD | | PAGE 1 OF 1 | |

ON Semiconductor and unare trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the

onsemi, ONSEMi., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer p

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative