Schottky Barrier Rectifiers, Surface Mount, 3 A, 40 V-100 V

Features

- Low Power Loss, High Efficiency
- Guard Ring for Overvoltage Protection
- High Surge Current Capability
- UL Flammability 94V-0 Classification
- MSL 1 per J-STD-020
- NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- This Device is Pb-Free and RoHS Compliant

ABSOLUTE MAXIMUM RATINGS

(Values are at $T_A = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	SS34FA	SS36FA	S310FA	Unit
V _{RRM}	Repetitive Peak Reverse 40 60 100 Voltage		100	V	
V _{RMS}	RMS Reverse Voltage	28	42	70	V
V _R	DC Blocking Voltage	40 60 100		100	V
I _{F(AV)}	Average Forward Rectified Current	3		A	
I _{FSM}	Peak Forward Surge Current: 8.3 ms Single Half Sine–Wave Superimposed on Rated Load	80			A
TJ	Operating Junction Temperature Range	-55 to -55 to +150 +125		°C	
T _{STG}	Storage Temperature Range	-55 to +150		°C	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

(Values are at $T_A = 25^{\circ}C$ unless otherwise noted) (Note 1)

Symbol	Parameter	Value	Unit
ΨJL	Thermal Characteristics, Junction-to-Lead	16	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	152	°C/W

1. Per JESD51–3 Recommended Thermal Test Board. Device mounted on FR–4 PCB, board size = 76.2 mm \times 114.3 mm.




ON Semiconductor®


www.onsemi.com



SOD-123FL CASE 425AB



MARKING DIAGRAM



- &Y = Binary Calendar Year Coding Scheme
- &Z = Assembly Plant Code
 - = Specific Device Code
 - (34L, 36L or 30L)
- &G = Single Digit Weekly Datecode

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ELECTRICAL CHARACTERISTICS (Values are at $T_A = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter	Conditions	SS34FA	SS36FA	S310FA	Unit
V _F	Maximum Instantaneous Forward Voltage (Note 2)	I _F = 3 A	0.50	0.75	0.85	V
I _R	Maximum Reverse Current at Rated V _R	T _J = 25°C	0.5		0.1	mA
naleu v _R		$T_{\rm J} = 125^{\circ}{\rm C}$	60	10	5	
CJ	Typical Junction Capacitance	V _R = 4 V, f = 1 MHz	152	117	78	pF
T _{rr}	Typical Reverse Recovery Time	I _F = 0.5 A, I _R = 1 A, I _{RR} = 0.25 A	12	11	8	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 2. Pulse test with PW = $300 \ \mu s$, 1% duty cycle.

ORDERING INFORMATION

Part Number	Top Mark	Package	Shipping [†]
SS34FA, NRVBSS34FA*	34L	SOD-123FL (Pb-Free)	3,000 / Tape & Reel
SS36FA, NRVBSS36FA*	36L	SOD-123FL (Pb-Free)	3,000 / Tape & Reel
S310FA, NRVBS310FA*	30L	SOD-123FL (Pb-Free)	3,000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NRVB Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Forward Current Derating Curve



Figure 2. Maximum Non-Repetitive Forward Surge Current




Figure 3. Typical Forward Characteristics




Figure 5. Typical Forward Characteristics




Figure 4. Typical Forward Characteristics




Figure 6. Typical Reverse Characteristics

TYPICAL CHARACTERISTICS (Continued)




Figure 7. Typical Reverse Characteristics




Figure 8. Typical Reverse Characteristics







Figure 9. Typical Junction Capacitance

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS










FRONT VIEW





SOD-123FA CASE 425AB **ISSUE A**


DATE 11 AUG 2022

Onsemi

NDTES:

- NO INDUSTRY STANDARD APPLIES TO 1. THIS PACKAGE.
- 2.
- ALL DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND THE BAR PROTRUSIONS. З.

DIM	MILLIMETERS			
INI	MIN.	NDM.	MAX.	
A	1.23	1.33	1.43	
b	0,80	1.00	1,20	
C	0.16	0.23	0.30	
D	2.70	2,80	2.90	
D1	3.40	3,60	3.80	
E	1.70	1.80	1.90	
He	2.45		2.60	
L	0.35	0.60	0.85	



MOUNTING FOOTPRINT*

* For additional information on our Pb-Free strategy and soldering details, please download the DN Semiconductor Soldering and Mounting Techniques Reference Manual, SDLDERRM/D.

DOCUMENT NUMBER:	98AON13722G Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.					
DESCRIPTION: SOD-123FA PAGE 1 OF 1						
onsemi and ONSEMI. are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.						

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative