General Purpose Transistors

NPN Silicon

BCH817-16L/25L/40L, NSVBCH817-16L/25L/40L

Features

- 175°C T_{J(max)} Rated for High Temperature, Mission Critical Applications
- NSV Prefixes for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector – Emitter Voltage	V _{CEO}	45	V
Collector – Base Voltage	V _{CBO}	50	V
Emitter – Base Voltage	V _{EBO}	5.0	V
Collector Current – Continuous	Ι _C	500	mAdc
Collector Current – Peak	I _{CM}	1	А

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR- 5 Board, (Note 1) $T_A = 25^{\circ}C$ Derate above 25°C	P _D	225 1.3	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	400	°C/W
Total Device Dissipation Alumina Substrate, (Note 2) $T_A = 25^{\circ}C$ Derate above 25°C	P _D	300 1.8	mW mW/°C
Thermal Resistance, Junction-to-Ambient	R _{θJA}	330	°C/W
Junction and Storage Temperature	T _J , T _{stg}	-55 to +175	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


1. $FR-5 = 1.0 \times 0.75 \times 0.062$ in.


2. Alumina = 0.4 x 0.3 x 0.024 in 99.5% alumina.




ON Semiconductor®

www.onsemi.com







*Date Code orientation and/or overbar may vary depending upon manufacturing location.

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS					
Collector – Emitter Breakdown Voltage (I _C = 10 mA)	V _{(BR)CEO}	45	_	-	V
Collector – Emitter Breakdown Voltage (V_{EB} = 0, I _C = 10 μ A)	V _{(BR)CES}	50	-	-	V
Emitter – Base Breakdown Voltage (I _E = 1.0 μA)	V _{(BR)EBO}	5.0	-	-	V
Collector Cutoff Current $(V_{CB} = 20 \text{ V})$ $(V_{CB} = 20 \text{ V}, T_A = 150^{\circ}\text{C})$	I _{CBO}			100 5.0	nA μA
ON CHARACTERISTICS					
$ DC \mbox{ Current Gain} \\ (I_C = 100 \mbox{ mA}, \mbox{ V}_{CE} = 1.0 \mbox{ V}) \\ BCH817-16, \mbox{ NSVBCH817-16*} \\ BCH817-25, \mbox{ NSVBCH817-25*} \\ BCH817-40, \mbox{ NSVBCH817-40} \\ (I_C = 500 \mbox{ mA}, \mbox{ V}_{CE} = 1.0 \mbox{ V}) $	h _{FE}	100 160 250 40		250 400 600 -	_
Collector – Emitter Saturation Voltage (I _C = 500 mA, I _B = 50 mA)	V _{CE(sat)}	-	_	0.7	V
Base – Emitter On Voltage $(I_C = 500 \text{ mA}, V_{CE} = 1.0 \text{ V})$	V _{BE(on)}	-	_	1.2	V
SMALL-SIGNAL CHARACTERISTICS					
Current – Gain – Bandwidth Product ($I_C = 10 \text{ mA}, V_{CE} = 5.0 \text{ Vdc}, f = 100 \text{ MHz}$)	f _T	100	_	-	MHz
Output Capacitance (V _{CB} = 10 V, f = 1.0 MHz)	C _{obo}	-	10	-	pF

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

ORDERING INFORMATION


Device	Specific Marking	Package	Shipping [†]	
BCH817-16LT1G**	~~~~	XXX SOT-23 (Pb-Free)	3000 / Tape & Reel	
NSVBCH817-16LT1G**	^^^^			
BCH817-25LT1G**	xxx	SOT-23 (Pb-Free)		
NSVBCH817-25LT1G**			3000 / Tape & Reel	
BCH817-40LT1G	01	SOT-23		
NSVBCH817-40LT1G	- 6X	(Pb-Free)	3000 / Tape & Reel	

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

*NSV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable

**Device release available upon request – Please contact ON Semiconductor sales.

TYPICAL CHARACTERISTICS - BCH817-16L, NSVBCH817-16L



TYPICAL CHARACTERISTICS - BCH817-16L, NSVBCH817-16L




Figure 5. Saturation Region

Figure 6. Temperature Coefficients





Figure 7. Capacitances

TYPICAL CHARACTERISTICS - BCH817-25L, NSVBCH817-25L



TYPICAL CHARACTERISTICS - BCH817-25L, NSVBCH81725L




Figure 13. Saturation Region

Figure 14. Temperature Coefficients





Figure 15. Capacitances

TYPICAL CHARACTERISTICS - BCH817-40L, NSVBCH817-40L



TYPICAL CHARACTERISTICS - BCH817-40L, NSVBCH817-40L




Figure 21. Saturation Region

Figure 22. Temperature Coefficients




Figure 23. Capacitances

TYPICAL CHARACTERISTICS – BCH817–16L, NSVBCH817–16L, BCH817–25L, NSVBCH817–25L, BCH817–40L, NSVBCH817–40L




Figure 24. Safe Operating Area





© Semiconductor Components Industries, LLC, 2019

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative