ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor®

FDMC86102LZ

N-Channel Shielded Gate PowerTrench[®] MOSFET 100 V, 22 A, 24 m Ω

Features

- Shielded Gate MOSFET Technology
- Max $r_{DS(on)}$ = 24 m Ω at V_{GS} = 10 V, I_D = 6.5 A
- Max $r_{DS(on)} = 35 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, $I_D = 5.5 \text{ A}$
- HBM ESD protection level > 6 KV typical (Note 4)
- 100% UIL Tested
- RoHS Compliant



General Description


This N-Channel logic Level MOSFETs are produced using ON Semiconductor's advanced PowerTrench[®] process that incorporates Shielded Gate technology. This process has been optimized for the on-state resistance and yet maintain superior switching performance. G-S zener has been added to enhance ESD voltage level.


Application

■ DC - DC Switching

Top Bottom







MLP 3.3x3.3

MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted

Symbol	Parameter			Ratings	Units
V_{DS}	Drain to Source Voltage			100	V
V_{GS}	Gate to Source Voltage			±20	V
	Drain Current -Continuous	T _C = 25 °C		22	
I_D	-Continuous	T _A = 25 °C	(Note 1a)	7	Α
	-Pulsed			30	
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	84	mJ
D	Power Dissipation	T _C = 25 °C		41	W
P_{D}	Power Dissipation	T _A = 25 °C	(Note 1a)	2.3	VV
T _J , T _{STG}	Operating and Storage Junction Temperat	ture Range		-55 to +150	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	3	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	53	C/VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMC86102Z	FDMC86102LZ	Power 33	13 "	12 mm	3000 units

Electrical Characteristics T_J = 25 °C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Off Chara	cteristics					
BV_{DSS}	Drain to Source Breakdown Voltage	$I_D = 250 \mu A, V_{GS} = 0 V$	100			V
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25 °C		71		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 80 V, V _{GS} = 0 V			1	μΑ
I _{GSS}	Gate to Source Leakage Current	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$			±10	μΑ

On Characteristics

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_{D} = 250 \mu A$	1.0	1.6	2.2	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \mu A$, referenced to 25 °C		-6		mV/°C
r _{DS(on)}		$V_{GS} = 10 \text{ V}, I_D = 6.5 \text{ A}$		19	24	
	Static Drain to Source On Resistance	$V_{GS} = 4.5 \text{ V}, I_D = 5.5 \text{ A}$		25	35	$m\Omega$
		$V_{GS} = 10 \text{ V}, I_D = 6.5 \text{ A}, T_J = 125 \text{ °C}$		31	40	1
9 _{FS}	Forward Transconductance	V _{DS} = 5 V, I _D = 6.5 A		24		S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 50 V V 0 V	969	1290	pF
C _{oss}	Output Capacitance	$V_{DS} = 50 \text{ V}, V_{GS} = 0 \text{ V},$ f = 1 MHz	181	240	pF
C _{rss}	Reverse Transfer Capacitance	1 = 1 1011 12	9	15	pF
R_g	Gate Resistance		0.4		Ω

Switching Characteristics


t _{d(on)}	Turn-On Delay Time		7.1	15	ns
t _r	Rise Time	V _{DD} = 50 V, I _D = 6.5 A,	2.3	10	ns
t _{d(off)}	Turn-Off Delay Time	V_{GS} = 10 V, R_{GEN} = 6 Ω	19	35	ns
t _f	Fall Time		2.5	10	ns
$Q_{g(TOT)}$	Total Gate Charge	V _{GS} = 0 V to 10 V	15.3	22	nC
$Q_{g(TOT)}$	Total Gate Charge	$V_{GS} = 0 \text{ V to } 4.5 \text{ V}$ $V_{DD} = 50 \text{ V}$, $I_{D} = 6.5 \text{ A}$	7.6	11	nC
Q_{gs}	Total Gate Charge	I _D = 6.5 A	2.4		nC
Q_{gd}	Gate to Drain "Miller" Charge		2.5		nC

Drain-Source Diode Characteristics


V _{SD} Source to Drain Diode Forward Voltage	Source to Drain Diade Forward Voltage	$V_{GS} = 0 \text{ V}, I_S = 6.5 \text{ A}$ (Note 2)	0.80	1.3	\/
	Source to Drain blode Forward voltage	$V_{GS} = 0 \text{ V}, I_{S} = 2 \text{ A}$ (Note 2)	0.72	1.2	V
t _{rr}	Reverse Recovery Time	I _F = 6.5 A, di/dt = 100 A/μs	37	59	ns
Q _{rr}	Reverse Recovery Charge	TIF = 0.5 A, α//αι = 100 A/μs	27	43	nC

NOTES:

^{1.} R_{0JA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R_{0JC} is guaranteed by design while R_{0CA} is determined by the user's board design.



a. 53 °C/W when mounted on a 1 in² pad of 2 oz copper



b. 125 °C/W when mounted on a minimum pad of 2 oz copper

- 2. Pulse Test: Pulse Width < 300 $\mu\text{s},$ Duty cycle < 2.0%.
- 3. Starting T_J = 25 °C; N-ch: L = 1 mH, I_{AS} = 13 A, V_{DD} = 90 V, V_{GS} = 10 V.
- 4. The diode connected between gate and source serves only as protection against ESD. No gate overvoltage rating is implied.

Typical Characteristics T_J = 25 °C unless otherwise noted




Figure 1. On-Region Characteristics




Figure 3. Normalized On-Resistance vs. Junction Temperature




Figure 5. Transfer Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

Typical Characteristics T_J = 25 °C unless otherwise noted




Figure 7. Gate Charge Characteristics




Figure 9. Unclamped Inductive Switching Capability




Figure 11. Gate Leakage Current vs. Gate to Source Voltage




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 12. Forward Bias Safe Operating Area






Figure 13. Single Pulse Maximum Power Dissipation




Figure 14. Junction-to-Ambient Transient Thermal Response Curve

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative