# **Surface Mount Schottky Power Rectifier**

This device employs the Schottky Barrier principle in a large area metal-to-silicon power diode. State-of-the-art geometry features epitaxial construction with oxide passivation and metal overlay contact. Ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes in surface mount applications where compact size and weight are critical to the system.

#### **Features**

- Low Profile Package for Space Constrained Applications
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- 150°C Operating Junction Temperature
- Guard-Ring for Stress Protection
- NRV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These are Pb-Free and Halide-Free Devices

#### **Mechanical Charactersistics**

- Case: Epoxy, Molded, Epoxy Meets UL 94, V-0
- Weight: 95 mg (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Cathode Polarity Band
- Device Meets MSL 1 Requirements



## ON Semiconductor®

www.onsemi.com

# SCHOTTKY BARRIER **RECTIFIER** 4.0 AMPERE 40 VOLTS



CASE 403AA STYLE 6

### MARKING DIAGRAM



**RAF** = Specific Device Code Α = Assembly Location

= Year WW

= Work Week = Pb-Free Package

### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
MBRAF440T3G	SMA-FL (Pb-Free)	5000 / Tape & Reel
NRVBAF440T3G	SMA-FL (Pb-Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

### **MAXIMUM RATINGS**

Rating		Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage		V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	40	V
Average Rectified Forward Current (At Rated V <sub>R</sub> , T <sub>L</sub> = 107°C)		lo	4.0	А
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Halfwave, Single Phase, 60 Hz)		I <sub>FSM</sub>	100	А
Storage/Operating Case Temperature		T <sub>stg</sub> , T <sub>C</sub>	-55 to +150	°C
Operating Junction Temperature (Note 1)		TJ	-55 to +150	°C
Voltage Rate of Change (Rated V <sub>R</sub> , T <sub>J</sub> = 25°C)		dv/dt	10,000	V/μs
ESD Rating	Human Body Model Machine Model	ESD <sub>HBM</sub> ESD <sub>MM</sub>	3B M4	-

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction–to–Ambient:  $dP_D/dT_J < 1/R_{\theta JA}$ .

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Value	Unit
Thermal Resistance – Junction–to–Lead (Note 2) Thermal Resistance – Junction–to–Ambient (Note 2)	R <sub>θJL</sub> R <sub>θJA</sub>	25 90	°C/W

<sup>2. 1</sup> inch square pad size (1  $\times$  0.5 inch) for each lead on FR4 board.

## **ELECTRICAL CHARACTERISTICS**

Characteristic	Symbol	Va	lue	Unit
Maximum Instantaneous Forward Voltage (Note 3)	V <sub>F</sub>	T <sub>J</sub> = 25°C	T <sub>J</sub> = 100°C	V
$(I_F = 4.0 \text{ A})$		0.485	0.435	
Maximum Instantaneous Reverse Current	I <sub>R</sub>	T <sub>J</sub> = 25°C	T <sub>J</sub> = 100°C	mA
$(V_R = 40 \text{ V})$		0.3	15	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

<sup>3.</sup> Pulse Test: Pulse Width  $\leq$  250  $\mu$ s, Duty Cycle  $\leq$  2.0%.

### TYPICAL CHARACTERISTICS






Figure 1. Typical Forward Voltage

**Figure 4. Maximum Reverse Current** 



**Figure 3. Typical Reverse Current** 



**Figure 5. Forward Power Dissipation** 

P<sub>FO</sub>, AVERAGE POWER DISSIPATION (WATTS)

1.8

1.6

1.4

1.2 1.0 0.8

0.6

0.4

0.2

Figure 6. Capacitance

40




Figure 7. Current Derating





Figure 8. Typical Transient Thermal Response, Junction-to-Ambient







SMA-FL CASE 403AA-01 ISSUE O

**DATE 02 MAR 2011** 








**BOTTOM VIEW** 

## **RECOMMENDED SOLDER FOOTPRINT\***



**DIMENSIONS: MILLIMETERS** 

- AUTEUS.

  1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
  2. CONTROLLING DIMENSION: MILLIMETERS.

	MILLIMETERS		
DIM	MIN MAX		
Α	0.90	1.10	
ь	1.25	1.65	
U	0.15	0.30	
ם	2.40	2.80	
Е	4.80	5.40	
E1	4.00	4.60	
L	0.70	1.10	

DOCUMENT NUMBER:	98AON55210E	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	SMA-FL		PAGE 1 OF 1	

ON Semiconductor and at a trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

<sup>\*</sup>For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

#### **PUBLICATION ORDERING INFORMATION**

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative