



德力西电气有限公司

Product Specification

产品规格书

Model: DHBFG13532HA2SL

Factory Address: Delixi High Tech Park, LiuShi Town, Yueqing City,
Zhejiang Province

工厂地址：浙江省乐清市柳市镇德力西高科技工业园

Tel: +086-400-826-8008

电话：+086-400-826-8008

Website: www.delixi-electric.com

网址： www.delixi-electric.com



1. 外观尺寸 EXTERNAL DIMENSION	135*135*32
2. 订货编码	DHBFG13532HA2SL
3. 产品型号	G13532HA2SL
4. 重量 WEIGHT	595g
5. 轴承 BEARING	SLEEVE BEARING
6. 额定电压 RATED VOLTAGE	AC 220V
7. 额定电流 RATED CURRENT	0.14/0.12A±0.01MAXIMUM
8. 额定功率 RATED INPUT POWER	20/18W±2MAXIMUM
9. 转数 RATED SPEED	2500/2700 RPM±10%
10. 最大风量 MAXIMUM AIR FLOW	110/113CFM
11. 最大风压 MAXIMUM AIR PRESSURE	6.7/7.7mmH2O (AT ZERO AIR FLOW)
12. 启动电压 STARTING VOLTAGE	AC 110V MINIMUM
13. 存储温度 STORAGE HUMIDITY	-20℃~+80℃
14. 运转温度 OPERATING TEMPERATURE	-25℃~+65℃
15. 寿命 LIFE EXPECTANCE	30000HRS
16. 噪音分贝 SOUND LEVEL	44dBA/50dBA

SPECIFICATION 规格参数



