PNP Epitaxial Silicon Transistor

KSA916

Features

- Audio Power Amplifier
- Driver Stage Amplifier
- Complement to KSC2316

ABSOLUTE MAXIMUM RATINGS

(Values are at $T_A = 25^{\circ}C$ unless otherwise noted.)

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	-120	V
V _{CEO}	Collector-Emitter Voltage	-120	V
V _{EBO}	Emitter-Base Voltage	-5	V
I _C	Collector Current	-800	mA
T _J	Junction Temperature	150	°C
T _{STG}	Storage Temperature	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

(Values are at T_A = 25°C unless otherwise noted.) (Note 1)

Symbol	Parameter	Value	Unit	
P _D	Power Dissipation, by $R_{\theta JA}$	900	mW	
	Power Dissipation, by $R_{\theta JC}$	3	W	
	Derate Above 25°C, by R _{θJA}	7.2	mW/°C	
	Derate Above 25°C, by R _{θJC}	24	mW/°C	
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	130	°C/W	
$R_{ heta JC}$	Thermal Resistance, Junction-to-Case	41	°C/W	

^{1.} PCB size: FR-4, 76 mm \times 114 mm \times 1.57 mm (3.0 inch \times 4.5 inch \times 0.062 inch) with minimum land pattern size.




ON Semiconductor®

www.onsemi.com



TO-92 3 LF CASE 135AM

MARKING DIAGRAM



- 1: Emitter
- 2: Collector
- 3: Base

A = Assembly Code A916Y = Device Code YWW = Date Code

ORDERING INFORMATION

Device	Package	Shipping
KSA916YTA	TO-92 3 LF (Pb-Free)	2000 / Fan–Fold

KSA916

ELECTRICAL CHARACTERISTICS

(Values are at $T_A = 25^{\circ}C$ unless otherwise noted.)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV _{CBO}	Collector-Base Breakdown Voltage	$I_C = -1 \text{ mA}, I_E = 0$	-120	-	-	V
BV _{CEO}	Collector-Emitter Breakdown Voltage	$I_C = -10 \text{ mA}, I_B = 0$	-120	-	-	V
BV _{EBO}	Emitter-Base Breakdown Voltage	$I_E = -1 \text{ mA}, I_C = 0$	-5	ı	-	V
I _{CBO}	Collector Cut-Off Current	$V_{CB} = -120 \text{ V}, I_{E} = 0$	-	-	-0.1	μΑ
h _{FE1}	DC Current Gain	$V_{CE} = -5 \text{ V}, I_{C} = -10 \text{ mA}$	60	ı	ı	
h _{FE2}	DC Current Gain	$V_{CE} = -5 \text{ V}, I_{C} = -100 \text{ mA}$	80	-	240	
V _{CE} (sat)	Collector-Emitter Saturation Voltage	$I_C = -500 \text{ mA}, I_B = -50 \text{ mA}$	-	-	-1	V
f _T	Current Gain Bandwidth Product	$V_{CE} = -5 \text{ V}, I_{C} = -100 \text{ mA}$	-	120	-	MHz
C _{ob}	Output Capacitance	$V_{CB} = -10 \text{ V}, I_E = 0, f = 1 \text{ MHz}$	-	-	40	pF

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

$h_{\mbox{\scriptsize FE}}$ CLASSIFICATION

Classification	0	Y
h _{FE2}	80 ~ 160	120 ~ 240

KSA916

TYPICAL PERFORMANCE CHARACTERISTICS





Figure 1. Static Characteristic

Figure 2. DC Current Gain



Single Pulse

10 ms

1 ms

-100

Figure 3. Collector-Emitter Saturation Voltage

DC Operating $T_C = 25^{\circ}C$

100 ms

I_C, Collector Current (A)

-10




Figure 4. Base-Emitter On Voltage

V_{CE}, Collector-Emitter Voltage (V) Figure 5. Safe Operating Area

-10





Figure 6. Power Derating



CASE 135AM ISSUE B

DATE 14 JAN 2021



- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, GATE REMAINS AND TIE BAR PROTRUSIONS.
- 4. DIMENSION & AND &2 DOES NOT INCLUDE DAMBAR PROTRUSION.
 DIMENSION &2 LOCATED ABOVE THE DAMBAR PORTION OF MIDDLE LEAD.

	MILLIMETERS			
DIM	MIN.	N□M.	MAX.	
Α	3.70	3.90	4.10	
A1	1.25	1.45	1.65	
b	0.35	0.50	0.60	
b2	0.62		0.78	
С	0.35	0.45	0.55	
D	7.80	8.00	8.20	
Ε	4.70	4.90	5.10	
E2	3.70	3.90	4.10	
е	1.27 BSC			
e2	2.50 BSC			
F	2.45 REF			
L	13.00 REF			
L2	1.50		1.90	
L3	2.60		3,40	
L4	10.40 REF			

	► A	
	E-E	
	1 1	
_	D B	
L3 L2	h	
1	3	
L'4	e2	
<u>•</u>		7
T	ip view	_

	IUP VIEW	
	E2 	rA1
A	1 2 3	1
	F	

END VIEW

DOCUMENT NUMBER:	98AON14058G Electronic versions are uncontrolled except when accessed directly from the Dor Printed versions are uncontrolled except when stamped "CONTROLLED COPY"		
DESCRIPTION:	TO-92 3 8.0X4.9 (LEADFORMED)		PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT: Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative