




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2011.08.30	黃小燕
02	△	依業務要求，新增膠紙	2012.12.24	邱明周
03	△	依上級要求，更新CAP外觀	2014.07.09	郭國強
04	△	Correct annotation meaning	2021.11.25	郭康

Specifications
 Current Rating:2.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon HTN (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PFA101 - XX XX A 001 R 1 B X

No. of Pins per Row: 02~40
 Standard Plating: 02=Gold Flash
 Selective Plating: 01=Tin, 05=Gold Flash/Tin
 Color: 1=Black
 Standard Packing: A=box, C=Tube(03~40PIN), E=CAP+Tube(03~40PIN), F=CAP+Tape&Reel(02~40PIN)

Greenconn
 Website: www.greenconn.com
 E-mail: sales@greenconn.com

3RD.ANG PROJ.

 PAGE. 1/1

GENERAL TOLERANCE	
X'±3.0'	X.±0.25
.X'±2.0'	.X±0.20
.XX'±1.0'	.XX±0.13
.XXX'±0.5'	.XXX±0.08

DESIGNED: 郭康
 CHECKED:
 APPROVED:

DATE:2021.11.25
 DATE:
 DATE:

DWG. NO. GPFA101-CA1RB
 PART NO. GPFA101-XXXX A001R1BX

TITLE. 2.00 PIN HEADER SINGLE ROW DIP TYPE BASE 2.00H