





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2011.08.30	黃小燕
02	△	依業務要求，新增膠紙	2012.12.24	邱明周
03	△	依上級要求，更新CAP外觀	2014.07.09	郭國強
04	△	Correct annotation meaning	2021.11.25	郭康



Specifications  
 Current Rating:2.0Amp  
 Insulation Resistance:1000MΩMin.  
 Dielectric Withstanding Voltage:500VAC  
 Contact Resistance:20mΩMax.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material:Brass  
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon HTN (Halogen Free) or the equivalent material  
 All materials must meet Greenconn hazardous substances control standards.

Recommended P.C.Board Layout  
 (Tolerance:±0.05)




### Ordering Information

G PFA101 - XX XX A 001 R 1 B X

No. of Pins per Row 02~40  
 Standard Plating 02=Gold Flash  
 Selective Plating 01=Tin 05=Gold Flash/Tin  
 Color 1=Black  
 Standard Packing A=box  
 Selective Packing C=Tube(03~40PIN)  
 E=CAP+Tube(03~40PIN)  
 F=CAP+Tape&Reel(02~40PIN)

**Greenconn**  
 Website:www.greenconn.com  
 E-mail:sales@greenconn.com

3RD.ANG PROJ.  
  
 PAGE. 1/1

GENERAL TOLERANCE	
X'±3.0'	X.±0.25
.X'±2.0'	.X±0.20
.XX'±1.0'	.XX±0.13
.XXX'±0.5'	.XXX±0.08

DESIGNED: 郭康  
 CHECKED:  
 APPROVED:

DATE:2021.11.25  
 DATE:  
 DATE:

DWG. NO. GPFA101-CA1RB  
 PART NO. GPFA101-XXXX A001R1BX

TITLE. 2.00 PIN HEADER SINGLE ROW DIP TYPE BASE 2.00H