





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2014.03.25	邱明周



Specifications
 Current Rating:2.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PFC101 - XX XX A 074 R 1 B X

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
C=Tube
Selective Packing
A=Box
E=Cap+Tube
F=Cap+Tape&Reel

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.±5.0°	X.±0.30
.X.±3.0°	.X.±0.25
.XX.±2.0°	.XX.±0.15
.XXX.±1.0°	.XXX.±0.10

DESIGNED: 邱明周	DATE: 2014.03.25
CHECKED: 曹熙	DATE: 2014.03.25
CO SIGNED: 黃龍福	DATE: 2014.03.25
APPROVED: 李輝	DATE: 2014.03.25

DWG. NO.	GPFC101-CA74RB
PART NO.	GPFC101-XXXX A074R1BX

TITLE.
 2.00 PIN HEADER
 SINGLE ROW SMT TYPE
 CONNECTOR

REV.	UNIT.	SCALE.	PAGE.	Symbol
01	mm	5:1	1/1	