

EA8107

High Efficiency 1.5MHz 1.2A Synchronous Step Down Converter

Description

The EA8107 is a high efficiency, high frequency synchronous DC -DC step -down pulse width modulated (PWM) converter. The 100% duty cycle feature provides low dropout operation, extending battery life in portable systems.


The internal synchronous switch increases efficiency and eliminates the need for external Schottky diode. At shutdown mode, the input supply current is less than 1μ A.

TheEA 8107 fault protection includes over current protection , short circuit protection , UVLO and thermal shutdown. The Internal soft-start function prevents inrush current at turn-on.

The EA8107 is offered in SOT-23-5 and SOT-23-6 Packages.

Pin Assignments

E5 Package (SOT-23-5)



E6 Package (SOT-23-6)

_	FB	PG		_
	6	5	4	1
IJ	1	2	3	Į
Ľ	EN	GND	LX	Ľ

Figure 1. Pin Assignment of EA8107

Features

- 2.5V~6V Input Voltage Range
- 0.6V Reference Voltage
- 1.2A Output Current
- Low $R_{DS(ON)}$ for Internal Switch (Top/Bottom): 340/210m Ω
- 1.5MHz Switching Frequency
- Internal 1ms Soft-Start Time
- Internal Compensation Function
- 100% Dropout Operation
- Power Good Indicator Output (SOT-23-6 Only)
- Input Over Voltage Protection
- Over Current Protection
- Hiccup Short Circuit Protection
- Over Temperature Protection with Auto Recovery
- RoHS Compliant and Halogen Free

Applications

- Set Top Box
- LCD TV & Tablet
- AP Router & WiFi Dongle
- 3.5G & 4G Dongle
- USB3.0 & SSD storage

Ordering Information

Package Type E5: SOT-23-5 E6: SOT-23-6

SOT-23-5 Marking

Part Number	Product Code
EA8107E5	FW4

SOT-23-6 Marking

Part Number	Product Code
EA8107E6	FW5



EA8107

Typical Application Circuit




Figure 2. Schematic Diagram

VIN=5V, the recommended BOM list is as below.

V _{OUT}	C1	C4	R1	R2	L1	C2
3.3V	4.7µF MLCC	0.1µF MLCC	453kΩ	100kΩ	2.2µH	10µF MLCC
2.5V	4.7µF MLCC	0.1µF MLCC	316kΩ	100kΩ	2.2µH	10µF MLCC
1.8V	4.7µF MLCC	0.1µF MLCC	200kΩ	100kΩ	2.2µH	10µF MLCC
1.5V	4.7µF MLCC	0.1µF MLCC	150kΩ	100kΩ	1.8µH	10µF MLCC
1.2V	4.7µF MLCC	0.1µF MLCC	100kΩ	100kΩ	1.8µH	10µF MLCC
1.05V	4.7µF MLCC	0.1µF MLCC	75kΩ	100kΩ	1.5µH	10µF MLCC

Table 1. Recommended Component Values





Functional Pin Description

Pin Name	Pin No. (SOT-23-6)	Pin No. (SOT-23-5)	Pin Function
EN	1	1	Enable control pin. Pull high to turn the IC on, and pull low to disable the IC. Don't leave this pin floating.
GND	2	2	Ground pin.
LX	3	3	Power switching node. Connect an external inductor to this switching node.
VIN	4	4	Power supply input pin. Placed input capacitors as close as possible from VIN to GND to avoid noise influence.
PG	5		Open drain power good output pin.
FB	6	5	Voltage feedback input pin. Connect FB and V_{OUT} with a resistive voltage divider. This IC senses feedback voltage via FB and regulates it at 0.6V.

Block Diagram




Figure 3. Block Diagram of EA8107





Absolute Maximum Ratings (Note 1)

• VIN to GND0.3V to +6.5V
• LX to GND
• Dynamic LX Voltage in 20ns Duration
\bullet EN, FB, PG to GND0.3V to V_{IN}
 Package Thermal Resistance, (θ_{JA}) ^(Note 2)
SOT-23-5 250°C/W
SOT-23-6 250°C/W
 Package Thermal Resistance, (θ_{JC})
SOT-23-5 130°C/W
SOT-23-6 110°C/W
 Maximum Junction Temperature (T_J)
 Lead Temperature (Soldering, 10sec.)+++
• Storage Temperature (T _s)65°C to +150°C

Note 1: Stresses beyond this listed under "Absolute Maximum Ratings" may cause permanent damage to the device. Note 2: θ_{JA} is measured at 25°C ambient with the component mounted on a high effective thermal conductivity 4-layer board of JEDEC-51-7. The thermal resistance greatly varies with layout, copper thickness, number of layers and PCB size.

Recommended Operating Conditions

• Supply Voltage (V _{IN})	- +2.5V to +6V
• Operation Temperature Range (T _{OPR})	40°C to +85°C





Electrical Characteristics

(V_{IN}=5V, V_{OUT}=2.5V, T_A=25°C, unless otherwise specified.)

Parameter	Symbol	Conditions	Min	Тур	Мах	Unit
Input Supply Voltage	V _{IN}		2.5		6.0	V
Input Over Voltage Protection	V _{IN OVP}			6.3		V
Shutdown Current	I _{SHDN}	EN=0V		0.1	1	μA
Quiescent Current	lq	V _{FB} =0.65V, I _{OUT} =0A		200		μA
Reference Voltage	V _{REF}		0.588	0.6	0.612	V
FB Input Leakage Current	I _{FB}	V _{FB} =V _{IN}		0.01	1	μA
P-Channel MOSFET On-Resistance (Note 3)	R _{DS(ON)}			330		mΩ
N-Channel MOSFET On-Resistance (Note 3)	R _{DS(ON)}			200		mΩ
P-Channel Current Limit (Note 3)	I _{LIM}			1.5		Α
EN High-Level Input Voltage	V _{EN(H)}		1.5			V
EN Low-Level Input Voltage	V _{EN(L)}				0.4	V
EN Input Current	I _{EN}			2.5		μA
Under Voltage Lockout Voltage	UVLO			2.4		V
UVLO Hysteresis	V _{HYS}			0.3		V
Oscillation Frequency	Fosc		1.2	1.5	1.8	MHz
Minimum On Time				50		ns
Maximum Duty Cycle			100			%
Internal Soft Start Time	T _{SS}			1		ms
PG Rising Threshold	V _{PG (H)}	V _{FB} Rising		90		%
PG Low Threshold	V _{PG (L)}	V _{FB} falling		85		%
PG Sink Current	I _{PG}	V _{PG} =0.1V		1		mA
LX Discharge Resistance				100		Ω
Thermal Shutdown Temperature (Note 3)	T _{SD}			150		°C

Note 3: Guarantee by design.







Typical Performance Curves

 V_{IN} =5V, V_{OUT} =3.3V, C1=4.7 μ F//0.1 μ F, C2=10 μ F, L1=2.2 μ H, TA=+25°C, unless otherwise noted.

VOUT=3.3V








Figure 6. Steady State Waveform





Figure 8. Power On through VIN Waveform

Figure 5. Efficiency vs. Load Current



1µs/div

Figure 7. Steady State Waveform




Figure 9. Power On through VIN Waveform


V_{IN} =5V, V_{OUT} =3.3V, C1=4.7µF//0.1µF, C2 VOUT=1.2V





Typical Performance Curves (Continued)

V_{IN}=5V, V_{OUT}=3.3V, C1=4.7µF//0.1µF, C2=10µF, L1=2.2µH, TA=+25°C, unless otherwise noted.



100ms/div.

Figure 10. Power Off through VIN Waveform

I_{OUT}=0A




Figure 12. Power On through EN Waveform








Figure 14. Power Off through EN Waveform



I_{OUT}=1.2A



I_{OUT}=1.2A






Figure 13. Power On through EN Waveform









Typical Performance Curves (Continued)

 V_{IN} =5V, V_{OUT} =3.3V, C1=4.7 μ F//0.1 μ F, C2=10 μ F, L1=2.2 μ H, TA=+25°C, unless otherwise noted.




Figure 16. Load Transient Waveform





Function Description

The EA 8107 is a high efficiency , internal compensation and constant frequency current mode step-down synchronous DC/DC converter. It has integrated high-side (330m Ω , typ.) and low-side (200m Ω , typ.) power switches , and provides 1.2A continuous load current. It regulates input voltage from 2.5V to 6V, and down to an output voltage as low as 0.6V.

Enable

The EA8107 EN pin provides digital control to turn on/off the regulator. When the voltage of EN exceeds the threshold voltage, the regulator will start the soft start function. If the EN pin voltage is below the shutdown threshold voltage, the regulator will turn into the shutdown mode and the shutdown current will be smaller than 1 μ A. For auto start-up operation, connect EN to VIN.

Soft Start

The EA8107 employs internal soft start function to reduce input inrush current during start up. The internal soft start time will be 1ms.

Under Voltage Lockout

When the EA8107 is power on, the internal circuits will be held inactive until V_{IN} voltage exceeds the UVLO threshold voltage. And the regulator will be disabled when V_{IN} is below the UVLO threshold voltage. The hysteretic of the UVLO comparator is 200mV (typ).

PG Signal Output

PG pin is an open-drain output and requires a pull up resistor. PG is actively held low in soft-start, standby and shutdown. It is released when the output voltage rises above 90% of nominal regulation point.

Over Current Protection

The EA8107 over current protection function is implemented by using cycle-by-cycle current limit architecture. The inductor current is monitored by measuring the high-side MOSFET series sense resistor voltage. When the load current increases, the inductor current will also increase. When the peak inductor current reaches the current limit threshold, the output voltage will start to drop. When the over current condition is removed, the output voltage will return to the regulated value.

Short Circuit Protection

The EA8107 provides short circuit protection function to prevent the device damaged from short condition. When the short condition occurs and the feedback voltage drops lower than 40% of the regulation level, the oscillator frequency will be reduced and hiccup mode will be triggered to prevent the EA8107 from overheating during the extended short condition. Once the short condition is removed, the frequency and current limit will return to normal.

Over Temperature Protection

The EA8107 incorporates an over temperature protection circuit to protect itself from overheating. When the junction temperature exceeds the thermal shutdown threshold temperature, the regulator will be shutdown. And the hysteretic of the over temperature protection is $30^{\circ}C(typ)$.

Input Over Voltage Protection

The EA8107 supports input over voltage protection. When input voltage exceeds the input over Voltage threshold, the regulator will be shutdown unless the input over voltage is removed.





Application Information

Output Voltage Setting

The output voltage V_{OUT} is set by using a resistive divider from the output to FB. The FB pin regulated voltage is 0.6V. Thus the output voltage is:

$$V_{OUT}=0.6V \times \left(1+\frac{R1}{R2}\right)$$

Table 2 lists recommended values of R1 and R2 for most used output voltage.

Table 2	Recommended Resistance Values	5

V _{OUT}	R1	R2
3.3V	453kΩ	100kΩ
2.5V	316kΩ	100kΩ
1.8V	200kΩ	100kΩ
1.5V	150kΩ	100kΩ
1.2V	100kΩ	100kΩ

Place resistors R1 and R2 close to FB pin to prevent stray pickup.


Input Capacitor Selection

The use of the input capacitor is filtering the input voltage ripple and the MOSFETS switching spike voltage. Because the input current to the step-down converter is discontinuous, the input capacitor is required to supply the current to the converter to keep the DC input voltage. The capacitor voltage rating should be 1.25 to 1.5 times greater than the maximum input voltage. The input capacitor ripple current RMS value is calculated as:

$$I_{CIN(RMS)} = I_{OUT} \times \sqrt{D \times (1-D)}$$
$$D = \frac{V_{OUT}}{V_{IN}}$$

Where D is the duty cycle of the power MOSFET.

This function reaches the maximum value at D=0.5 and the equivalent RMS current is equal to $I_{OUT}/2$. The following diagram is the graphical representation of above equation.



A low ESR capacitor is required to keep the noise minimum. Ceramic capacitors are better, but tantalum or low ESR electrolytic capacitors may also suffice.


Output Capacitor Selection

The output capacitor is used to keep the DC output voltage and supply the load transient current. When operating in constant current mode, the output ripple is determined by four components:

$$V_{RIPPLE}(t) = V_{RIPPLE(C)}(t) + V_{RIPPLE(ESR)}(t) + V_{RIPPLE(ESL)}(t) + V_{NOISE}(t)$$

The following figures show the form of the ripple contributions.

V_{RIPPLE(ESR)}(t)





EA8107


Application Information (Continued)

$$V_{\text{RIPPLE(ESR)}} = \frac{V_{\text{OUT}}}{F_{\text{OSC}} \times L} \times \left(1 - \frac{V_{\text{OUT}}}{V_{\text{IN}}}\right) \times \text{ESR}$$
$$V_{\text{RIPPLE(ESL)}} = \frac{\text{ESL}}{L} \times V_{\text{IN}}$$
$$V_{\text{RIPPLE(C)}} = \frac{V_{\text{OUT}}}{8 \times F_{\text{OSC}^2} \times L \times C_{\text{OUT}}} \times \left(1 - \frac{V_{\text{OUT}}}{V_{\text{IN}}}\right)$$

Where F_{OSC} is the switching frequency, L is the inductance value, V_{IN} is the input voltage, ESR is the equivalent series resistance value of the output capacitor, ESL is the equivalent series inductance value of the output capacitor and the C_{OUT} is the output capacitor.

Low ESR capacitors are preferred to use. Ceramic, tantalum or low ESR electrolytic capacitors can be used depending on the output ripple requirements. When using the ceramic capacitors, the ESL component is usually negligible.

It is important to use the proper method to eliminate high frequency noise when measuring the output ripple. The figure shows how to locate the probe across the capacitor when measuring output ripple. Remove the scope probe plastic jacket in order to expose the ground at the tip of the probe. It gives a very short connection from the probe ground to the capacitor and eliminates noise.




Ceramic Capacitor

Inductor Selection

The output inductor is used for storing energy and filtering output ripple current. But the trade-off condition often happens between maximum energy storage and the physical size of the inductor. The first consideration for selecting the output inductor is to make sure that the inductance is large enough to keep the converter in the continuous current mode. That will lower ripple current and result in lower output ripple voltage. The ΔI_{L} is inductor peak-to-peak ripple current:

$$\Delta I_{L} = \frac{V_{OUT}}{F_{OSC} \times L} \times \left(1 - \frac{V_{OUT}}{V_{IN}}\right)$$

The following diagram is an example to graphically represent ΔI_L equation.




A good compromise value between size and efficiency is to set the peak-to-peak inductor ripple current ΔI_{L} equal to 30% of the maximum load current. But setting the peak-to-peak inductor ripple current ΔI_{L} between 20%~50% of the maximum load current is also acceptable. Then the inductance can be calculated with the following equation:

$$\Delta I_L = 0.3 \times I_{OUT(MAX)}$$

$$L = \frac{(V_{IN} - V_{OUT}) \times V_{OUT}}{V_{IN} \times F_{OSC} \times \Delta I_{L}}$$

To guarantee sufficient output current, peak inductor current must be lower than the EA8107 high-side MOSFET current limit. The peak inductor current is shown as below:








Application Information (Continued)

Feedforward Capacitor Selection

Internal compensation function allows users saving time in design and saving cost by reducing the number of external components. The use of a feedforward capacitor C6 in the feedback network is recommended to improve transient response or higher phase margin.



For optimizing the feedforward capacitor, knowing the cross frequency is the first thing. The cross frequency (or the converter bandwidth) can be determined by using a network analyzer. When getting the cross frequency with no feedforward capacitor identified, the value of feedforward capacitor C6 can be calculated with the following equation:

$$C3 = \frac{1}{2\pi \times F_{CROSS}} \times \sqrt{\frac{1}{R1} \times \left(\frac{1}{R1} + \frac{1}{R2}\right)}$$

Where F_{CROSS} is the cross frequency.

To reduce transient ripple, the feedforward capacitor value can be increased to push the cross frequency to higher region. Although this can improve transient response, it also decreases phase margin and causes more ringing. In the other hand, if more phase margin is desired, the feedforward capacitor value can be decreased to push the cross frequency to lower region. In general, the feedforward capacitor range is between 10pF to 100pF.

PCB Layout Recommendation

The device's performance and stability are dramatically affected by PCB layout. It is recommended to follow these general guidelines shown as below:

- 1. Place the input capacitors and output capacitors as close to the device as possible. The traces which connect to these capacitors should be as short and wide as possible to minimize parasitic inductance and resistance.
- 2. Place feedback resistors close to the FB pin.
- 3. Keep the sensitive signal (FB) away from the switching signal (LX).
- 4. Multi-layer PCB design is recommended.






Figure 17. Recommended Layout Diagram





Outline Information







SOT-23-5 Package (Unit: mm)

SYMBOLS	DIMENSION IN MILLIMETER			
UNIT	MIN	MAX		
А	0.90	1.45		
A1	0.00	0.15		
A2	0.90	1.30		
В	0.30	0.50		
D	2.80	3.00		
E	2.60	3.00		
E1	1.50	1.70		
е	0.90	1.00		
e1	1.80	2.00		
L	0.30	0.60		

Note: Followed From JEDEC MO-178-C.

Carrier Dimensions







Tape Size	Pocket Pitch	Reel Size (A)		Reel Width	Empty Cavity	Units per Reel
(W1) mm	(P)mm	in	mm	(W2) mm	Length mm	
8	4	7	180	8.4	300~1000	3,000





Outline Information (Continued)







SOT-23-6 Package (Unit: mm)

SYMBOLS	DIMENSION IN MILLIMETER			
UNIT	MIN	MAX		
A	0.90	1.45		
A1	0.00	0.15		
A2	0.90	1.30		
В	0.30	0.50		
D	2.80	3.00		
E	2.60	3.00		
E1	1.50	1.70		
е	0.90	1.00		
e1	1.80	2.00		
L	0.30	0.60		

Note: Followed From JEDEC MO-178-C.

Carrier Dimensions





Tape Size	Pocket Pitch	Reel Size (A)		Reel Width	Empty Cavity	Units per Reel
(W1) mm	(P) mm	in	mm	(W2) mm	Length mm	
8	4	7	180	8.4	300~1000	3,000