





A B C D E F



N=PIN数

Material 材料  
 Insulator 塑胶: PBT PA9T (UL 94V-0)  
 Contact 端子: Brass 黄铜  
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金  
 Electrical Characteristics 电气特性  
 Current rating 额定电流: 2.5Amps  
 Dielectric Withstanding Voltage 耐压:  
     AC 500V for 1 Minute.  
 Insulator Resistance 绝缘电阻: 1000MΩ Min.  
 Contact Resistance 接触电阻: 20mΩ Max.  
 Operating Temperature 工作温度: -40°C ~ +105°C  
 Max. Processing Temp 瞬时温度:  
     PBT 240° C for 6 seconds  
     PA9T (260° C for 10 seconds)



P.C.B LAYOUT

未注尺寸公差			PZ2.54-1*N-WZ		上海洲日电子有限公司			
尺寸	公差				版本编号		Shanghai Zhouri Electronics CO.,LTD	
	长度	角度	20171018 A/1				上海康司玛电子设备进出口有限公司	
X.	±0.3	±5°			图纸编号		Shanghai KangSiMa Eletronic Equipment	
X.X	±0.2	±3°	ZR20171018-258				import and export Co.,LTD	
X.XX	±0.15				物料编号		TEL:86-21-34975176/51571121	
制图	周元金	201171018	第三视角				1:1	
审核	张海娜	201171018			⊕		: 1	
核准	章妹	201171018						

A B C D E F