





REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2017.10.20	馮國東



Specifications
 Current Rating: 1.0Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 300VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Brass
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 Nylon (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.

Recommended P.C.Board Layout
 (Tolerance: ±0.05)



Ordering Information

G PEC132 - XX XX A 025 R 1 Z X

No. of Pins per Row
01~33

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
C=Tube(05~33PIN)
Selective Packing
A=Box
E=CAP+Tube(05~33PIN)
F=CAP+Tape&Reel

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X. ±5.0°	X. ±0.30
.X ±3.0°	.X ±0.25
.XX ±2.0°	.XX ±0.15
.XXX ±1.0°	.XXX ±0.10

DESIGNED: 馮國東	DATE: 2017.10.20
CHECKED: 曹熙	DATE: 2017.10.20
CO SIGNED: 蘭文禮	DATE: 2017.10.20
APPROVED: 李輝	DATE: 2017.10.20

DWG. NO.	GPEC132-CA25RZ
PART NO.	GPEC132-XXXX A025R1ZX

TITLE:
 1.27 PIN HEADER
 SINGLE ROW SMT TYPE
 CONNECTOR

REV.	UNIT.	SCALE.	PAGE.
01	mm	4:1	1/1