


# MSKSEMI

SEMICONDUCTOR




ESD




TVS



TSS



MOV




GDT



PLED

Product data sheet



SOT-363

**MMDT3052DW ( NPN+NPN)**  
**Silicon Epitaxial Planar Transistor**

**Features**

- Each transistor elements are independent

**Applications**

- For low frequency amplify application

**MARKING: 5G**

**Absolute Maximum Ratings (T<sub>a</sub> = 25°C)**

Parameter	Symbol	Value	Unit
Collector Base Voltage	V <sub>CBO</sub>	50	V
Collector Emitter Voltage	V <sub>CEO</sub>	50	V
Emitter Base Voltage	V <sub>EBO</sub>	6	V
Collector Current	I <sub>C</sub>	200	mA
Power Dissipation	P <sub>tot</sub>	150	mW
Junction Temperature	T <sub>j</sub>	125	°C
Storage Temperature Range	T <sub>stg</sub>	- 55 to + 125	°C

**Characteristics at T<sub>a</sub> = 25 °C**

Parameter	Symbol	Min.	Typ.	Max.	Unit
DC Current Gain at V <sub>CE</sub> = 6 V, I <sub>C</sub> = 0.1 mA at V <sub>CE</sub> = 6 V, I <sub>C</sub> = 1 mA	E	90	-	-	-
	F	120	-	240	-
	F	200	-	400	-
	G	350	-	700	-
Collector Base Cutoff Current at V <sub>CB</sub> = 50 V	I <sub>CBO</sub>	-	-	100	nA
Emitter Base Cutoff Current at V <sub>EB</sub> = 6 V	I <sub>EBO</sub>	-	-	100	nA
Collector Emitter Breakdown Voltage at I <sub>C</sub> = 100 μA	V <sub>(BR)CEO</sub>	50	-	-	V
Collector Emitter Saturation Voltage at I <sub>C</sub> = 100 mA, I <sub>B</sub> = 10 mA	V <sub>CE(sat)</sub>	-	-	0.3	V
Transition Frequency at V <sub>CE</sub> = 6 V, -I <sub>E</sub> = 10 mA	f <sub>T</sub>	-	200	-	MHz
Collector Output Capacitance at V <sub>CB</sub> = 6 V, f = 1 MHz	C <sub>ob</sub>	-	2.5	-	pF

## Electrical Characteristics Curves

Fig 1. Transition Frequency vs Emitter Current




Fig 2. Common Emitter Transfer




Fig 3. Common Emitter Output




Fig 4. DC Current Gain vs Collector Current








Fig 5. Collector Output Capacitance vs Collector Base Voltage




**SOT-363 Package Outline Dimensions**



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
c	0.100	0.150	0.004	0.006
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.400	0.085	0.094
e	0.650 TYP		0.026 TYP	
e1	1.200	1.400	0.047	0.055
L	0.525 REF		0.021 REF	
L1	0.260	0.460	0.010	0.018
theta	0°	8°	0°	8°

**SOT-363 Suggested Pad Layout**



**Note:**

1. Controlling dimension: in millimeters.
2. General tolerance: ± 0.05mm.
3. The pad layout is for reference purposes only.

**REEL SPECIFICATION**

P/N	PKG	QTY
MMDT3052DW	SOT-363	3000

## Attention

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringement of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.