



DGD21844M

HALF-BRIDGE GATE DRIVER IN SO-14

Description

The DGD21844M is a high voltage and high speed gate driver capable of driving N-Channel MOSFETs and IGBTs in a half-bridge configuration. High voltage processing techniques enable the DGD21844M's high-side to switch to 600V in a bootstrap operation.

The DGD21844M logic inputs are compatible with standard TTL and CMOS levels (down to 3.3V) for easy interfacing with controlling devices. The driver outputs feature high-pulse current buffers designed for minimum driver cross conduction. Programmable deadtime by an external resistor provides more system level flexibility.

The DGD21844M is offered in the SO-14 package and the device's operating temperature extends from -40°C to +125°C.

Applications

- DC-DC converters
- DC-AC inverters
- AC-DC power supplies
- Motor controls
- Class-D power amplifiers

V_{CC} V_{CC} V_B TO LOAD SD* DGD21844M DT COM V_{SS} LO

Typical Configuration

Features

- Floating High-Side Driver in Bootstrap Operation to 600V
- Drives Two N-Channel MOSFETs or IGBTs in Half Bridge Configuration
- 1.9A Source / 2.3A Sink Output Current Capability
- Outputs Tolerant to Negative Transients
- Programmable Deadtime to Protect MOSFETs
- Wide Low-Side Gate Driver and Logic Supply: 10V to 20V
- Wide Logic Supply Voltage Offset Voltage: -5V to 5V
- Logic Input (IN and SD*) 3.3V Capability
- Schmitt Triggered Logic Inputs with Internal Pull Down
- Undervoltage Lockout for High- and Low-Side Drivers
- Extended Temperature Range: -40°C to +125°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: SO-14 (Type TH)
- Package Material: Molded Plastic. "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 ³
- Weight: 0.142 grams (Approximate)



Top View


Ordering Information (Note 4)

| Ì | Part Number | Marking | Reel Size (inches) | Tape Width (mm) | Quantity Per Reel |
|---|-----------------|-----------|--------------------|-----------------|-------------------|
| | DGD21844MS14-13 | DGD21844M | 13 | 16 | 2,500 |

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.


Marking Information



);; = Manufacturer's Marking DGD21844M = Product Type Marking Code YY = Year (ex: 22 = 2022) WW = Week (01 to 53)



Pin Diagrams




Top View SO-14

Pin Descriptions

| Pin Number | Pin Name | Function |
|--------------|-----------------|---------------------------------------------------------------------------------------------------------------------------|
| 1 | IN | Logic input for high-side and low-side gate driver outputs (HO and LO), in phase with HO (referenced to V _{SS}) |
| 2 | SD* | Logic input for shutdown (referenced to V _{SS}), enabled low |
| 3 | V_{SS} | Logic ground |
| 4 | DT | Programmable Deadtime lead, referenced to V _{SS} |
| 5 | COM | Low-side return |
| 6 | LO | Low-side gate drive output |
| 7 | V _{CC} | Low-side and logic fixed supply |
| 8, 9, 10, 14 | NC | No connection (no internal connection) |
| 11 | Vs | High-side floating supply return |
| 12 | НО | High-side gate drive output |
| 13 | V_{B} | High-side floating supply |

Functional Block Diagram





Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

| Characteristic | Symbol | Value | Unit |
|------------------------------------------|----------------------|----------------------------------------------|------|
| High-Side Floating Supply Voltage | V_{B} | -0.3 to +624 | V |
| High-Side Floating Supply Offset Voltage | Vs | V _B -24 to V _B +0.3 | V |
| High-Side Floating Output Voltage | V _{HO} | V _S -0.3 to V _B +0.3 | V |
| Offset Supply Voltage Transient | dV _S / dt | 50 | V/ns |
| Programmable Dead Time Pin Voltage | V_{DT} | V _{SS} -0.3 to V _{CC} +0.3 | V |
| Logic and Low-Side Fixed Supply Voltage | V _{CC} | -0.3 to +24 | V |
| Low-Side Output Voltage | V_{LO} | -0.3 to V _{CC} +0.3 | V |
| Logic Supply Offset Voltage | V _{SS} | V _{CC} -24 to V _{CC} +0.3 | V |
| Logic Input Voltage (IN and SD*) | V _{IN} | V _{SS} -0.3 to V _{CC} +0.3 | V |

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

| Characteristic | Symbol | Value | Unit |
|---------------------------------------------------|------------------|-------------|------|
| Power Dissipation Linear Derating Factor (Note 5) | P_{D} | 1.0 | W |
| Thermal Resistance, Junction to Ambient (Note 5) | $R_{	heta JA}$ | 120 | °C/W |
| Operating Temperature | TJ | +150 | |
| Lead Temperature (Soldering, 10s) | T_L | +300 | °C |
| Storage Temperature Range | T _{STG} | -55 to +150 | |

Note:

5. When mounted on a standard JEDEC 2-layer FR-4 board.

Recommended Operating Conditions

| Parameter | Symbol | Min | Max | Unit |
|--------------------------------------------|-----------------|---------------------|---------------------|------|
| High Side Floating Supply Absolute Voltage | V _B | V _S + 10 | V _S + 20 | V |
| High Side Floating Supply Offset Voltage | Vs | (Note 6) | 600 | V |
| High Side Floating Output Voltage | V _{HO} | Vs | V _B | V |
| Logic and Low Side Fixed Supply Voltage | Vcc | 10 | 20 | V |
| Low Side Output Voltage | V_{LO} | 0 | V_{CC} | V |
| Logic Input Voltage (IN and SD*) | V_{IN} | V_{SS} | 5 | V |
| Programmable Dead Time Pin Voltage | V_{DT} | Vss | Vcc | V |
| Logic Ground | V_{SS} | -5 | 5 | V |
| Ambient Temperature | T _A | -40 | +125 | °C |

Note:

6. Logic operation for $V_S = -5V$ to +600V.



$\hline \textbf{DC Electrical Characteristics} \ (V_{BIAS} \ (V_{CC}, \ V_{BS}) = 15 \text{V}, \ V_{SS} = \text{COM}, \ @T_{A} = +25 ^{\circ}\text{C}, \ \text{unless otherwise specified.}) \ (\text{Note 7})$

| Parameter | Symbol | Min | Тур | Max | Unit | Conditions |
|---------------------------------------------------------------|---------------------|-----|-----|-----|------|---------------------------------|
| Logic "1" Input Voltage for HO & Logic "0" for LO | V_{IH} | 2.5 | _ | _ | V | $V_{CC} = 10V \text{ to } 20V$ |
| Logic "0" Input Voltage for HO & Logic "1" for LO | V_{IL} | _ | _ | 0.8 | V | $V_{CC} = 10V$ to $20V$ |
| SD* Input Positive Going Threshold | V_{SDTH+} | 2.5 | _ | _ | V | $V_{CC} = 10V$ to $20V$ |
| SD* Input Negative Going Threshold | V _{SDTH} - | _ | | 0.8 | V | $V_{CC} = 10V$ to $20V$ |
| High Level Output Voltage, V _{BIAS} - V _O | V_{OH} | _ | | 1.4 | V | $I_O = 0mA$ |
| Low Level Output Voltage, Vo | V_{OL} | _ | | 0.2 | V | $I_O = 20mA$ |
| Offset Supply Leakage Current | I_{LK} | _ | | 50 | μA | $V_{B} = V_{S} = 600V$ |
| Quiescent V _{BS} Supply Current | I _{BSQ} | 20 | 60 | 150 | μA | $V_{IN} = 0V \text{ or } 5V$ |
| Quiescent V _{CC} Supply Current | I _{CCQ} | 0.4 | 1.0 | 1.8 | mA | $V_{IN} = 0V \text{ or } 5V$ |
| Logic "1" Input Bias Current | I _{IN+} | _ | 25 | 60 | μA | IN = 5V, SD* = 0V |
| Logic "0" Input Bias Current | I _{IN-} | _ | | 1.0 | μA | IN = 0V, SD* = 5V |
| V _{BS} Supply Undervoltage Positive Going Threshold | V_{BSUV+} | 8.0 | 8.9 | 9.8 | V | |
| V _{BS} Supply Undervoltage Negative Going Threshold | V_{BSUV} | 7.4 | 8.2 | 9.0 | V | |
| V _{CC} Supply Undervoltage Positive Going Threshold | V _{CCUV+} | 8.0 | 8.9 | 9.8 | V | |
| V _{CC} Supply Undervoltage Negative Going Threshold | V _{CCUV} - | 7.4 | 8.2 | 9.0 | V | |
| Output-High Short-Circuit Pulsed Current | I _{O+} | 1.4 | 1.9 | _ | Α | V _O = 0V, PW ≤ 10μs |
| Output-Low Short-Circuit Pulsed Current | I _{O-} | 1.7 | 2.3 | _ | Α | V _O = 15V, PW ≤ 10μs |


Note: 7. The V_{IN} and I_{IN} parameters are referenced to V_{SS} and are applicable to the two logic input pins: IN and SD*. The V_O and I_O parameters are referenced to COM and are applicable to the respective output pins: HO and LO.

AC Electrical Characteristics (V_{BIAS} (V_{CC} , V_{BS}) = 15V, V_{SS} = COM, C_L = 1000pF, @ T_A = +25°C, unless otherwise specified.)

| Parameter | Symbol | Min | Тур | Max | Unit | Conditions |
|-----------------------------------------------------------------|--------------------|-----|-----|-----|------|-----------------------------|
| Turn-On Propagation Delay | toN | _ | 680 | 900 | ns | $V_S = 0V$ |
| Turn-Off Propagation Delay | toff | _ | 270 | 400 | ns | V _S = 0V or 600V |
| Shut-Down Propagation Delay | t _{SD} | _ | 180 | 270 | ns | _ |
| Delay Matching, HO & LO Turn-On | t _{DMON} | _ | _ | 90 | ns | _ |
| Delay Matching, HO & LO Turn-Off | t _{DMOFF} | _ | _ | 40 | ns | _ |
| Turn-On Rise Time | t _R | _ | 40 | 60 | ns | $V_S = 0V$ |
| Turn-Off Fall Time | t _F | _ | 20 | 35 | ns | $V_S = 0V$ |
| | t _{DT} | 280 | 400 | 520 | ns | $R_{DT} = 0\Omega$ |
| Deadtime: t _{DT} LO-HO & t _{DT} HO-LO | | 4 | 5 | 6 | μs | $R_{DT} = 200k\Omega$ |
| Destine Matchine | tмот | _ | 0 | 50 | ns | $R_{DT} = 0\Omega$ |
| eatime Matching = t _{DT LO-HO} - t _{DT HO-LO} | | _ | 0 | 600 | ns | $R_{DT} = 200k\Omega$ |



Timing Waveforms







Figure 1. Input / Output Timing Diagram

Figure 2. Shutdown Waveform Definitions



 $\begin{array}{c} \text{Deadtime } t_{\text{DT LO-HO}} = t_{\text{ON HO}} \cdot t_{\text{OFF LO}} \\ t_{\text{DT HO-LO}} = t_{\text{ON LO}} \cdot t_{\text{OFF HO}} \\ \text{Deadtime matching} \\ t_{\text{MDT}} = t_{\text{DT LO-HO}} \cdot t_{\text{DT HO-LO}} \end{array}$

Delay matching $t_{DM \, OFF} = t_{OFF \, LO} - t_{OFFT \, HO}$

Figure 3. Switching Time Waveform Definitions



Typical Performance Characteristics (V_{CC} = 15V, @T_A = +25°C, unless otherwise specified.)




Figure 4. Turn-on Propagation Delay vs. Supply Voltage




Figure 5. Turn-on Propagation Delay vs. Temperature




Figure 6. Turn-off Propagation Delay vs. Supply Voltage




Figure 7. Turn-off Propagation Delay vs. Temperature




Figure 8. SD Propagation Delay vs. Temperature




Figure 9. SD Propagation Delay vs. Supply Voltage






Figure 10. Rise Time vs. Supply Voltage




Figure 12. Fall Time vs. Supply Voltage




Figure 14. Quiescent Current vs. Supply Voltage




Figure 11. Rise Time vs. Temperature




Figure 13. Fall Time vs. Temperature




Figure 15. Quiescent Current vs. Temperature






Figure 16. Delay Matching vs. Supply Voltage




Figure 18. Output Source Current vs. Supply Voltage




Figure 20. Output Sink Current vs. Supply Voltage




Figure 17. Delay Matching vs. Temperature




Figure 19. Output Source Current vs. Temperature




Figure 21. Output Sink Current vs. Temperature






Figure 22. Logic 1 Input Voltage vs. Supply Voltage




Figure 24. Logic 0 Input Voltage vs. Supply Voltage




Figure 26. Deadtime vs. Supply Voltage




Figure 23. Logic 1 Input Voltage vs. Temperature




Figure 25. Logic 0 Input Voltage vs. Temperature




Figure 27. Deadtime vs. Temperature






Figure 28. Deadtime vs. RDT




Figure 29. VCC UVLO vs. Temperature




Figure 30. VBS UVLO vs. Temperature





Figure 31. Offset Supply Leakage Current vs. Temperature



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-14 (Type TH)




| SO-14 (Type TH) | | | | | | | | |
|-----------------|----------------------|-------|------|--|--|--|--|--|
| Dim | Min | Max | Тур | | | | | |
| Α | 1.55 | 1.73 | | | | | | |
| A1 | 0.10 | 0.25 | | | | | | |
| b | 0.35 | 0.51 | | | | | | |
| С | 0.190 | 0.248 | | | | | | |
| D | 8.56 | 8.74 | 8.61 | | | | | |
| Е | 5.84 | 6.20 | 6.00 | | | | | |
| E1 | 3.81 | 3.99 | 3.94 | | | | | |
| е | | | 1.27 | | | | | |
| h | | | 0.33 | | | | | |
| L | 0.41 | 0.89 | | | | | | |
| Ø | 0° | 8° | | | | | | |
| AII [| All Dimensions in mm | | | | | | | |

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-14 (Type TH)



| Dimensions | Value (in mm) |
|------------|---------------|
| С | 1.27 |
| C1 | 5.20 |
| Х | 0.60 |
| V | 2.20 |



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and
- Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- products provided subject to Diodes' Standard Terms and Conditions Sale Diodes are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing. Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com

12 of 12 February 2022 www.diodes.com Document number: DS41250 Rev. 3 - 2 © Diodes Incorporated