



AH3377

HIGH VOLTAGE LOW SENSITIVITY HALL EFFECT UNIPOLAR SWITCH

Description

The AH3377 is a high voltage high sensitivity Hall Effect Unipolar switch IC designed for proximity, position and level sensing in industrial and consumer home appliances and personal care applications. To support wide range of demanding applications, the design has been optimized to operate over the supply range of 3.0V to 28V. With chopper stabilized architecture and an internal bandgap regulator to provide temperature compensated supply for internal circuits, the AH3377 provides a reliable solution over the whole operating range. For robustness and protection, the device has a reverse blocking diode with a Zener clamp on the supply. The output has an over current limit and a Zener clamp.


The single open drain output can be switched on with South pole of sufficient strength. When the magnetic flux density (\mathbf{B}) perpendicular to the package is larger than the operate point (\mathbf{B}_{OP}) the output is switched on (pulled low) and is held on until magnetic flux density B is lower than the release point (\mathbf{B}_{RP}). The output remains switched off for North pole fields to or no magnetic fields.


The magnetic operating and release polarity is opposite for SOT23 and SC59 packages. SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) packages will require south pole to the part marking side to operate while SC59 will require south pole to the non-part marking side.

Features

- Unipolar Operation
- Low Sensitivity: B_{OP} and B_{RP} of +115G and +90G Typical
- Single Open Drain Output with Over Current Limit
- 3.0V to 28V Operating Voltage Range
- Chopper Stabilized Design Provides
 - o Superior Temperature Stability
 - o Minimal Switch Point Drift
 - Enhanced Immunity to Stress
- Good RF Noise Immunity
- · Reverse Blocking Diode
- Zener Clamp on Supply and Output Pins
- -40°C to +125°C Operating Temperature
- ESD: HBM > 6kV
- Industry Standard SC59, SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack) Packages
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Pin Assignments





Applications

Position and Proximity Sensing in Consumer Home Appliances,
 Building Automation, Office Equipments and Industrial Applications

May 2018

© Diodes Incorporated


- · Open and Close Detect
- Position Detect
- · Level Detect
- Flow Meters
- Contact-less switches

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Applications Circuit



Note:


4. C_{IN} is for power stabilization and to strengthen the noise immunity, the recommended capacitance is 10nF ~ 100nF. R_L is the pull-up resistor.

Pin Descriptions

Package: SC59, SOT23 and SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

Pin Number	Pin Name	Function
1	V_{DD}	Power Supply Input
2	GND	Ground
3	OUTPUT	Output Pin

Functional Block Diagram





Absolute Maximum Ratings (Notes 5 & 6) (@T_A = +25°C, unless otherwise specified.)

Symbol	Characteristic		Value	Unit	
V_{DD}	Supply Voltage (Note 6)		32	V	
V_{DDR}	Reverse Supply Voltage (Note 6)		-32	V	
V _{OUT_MAX}	Output Off Voltage (Note 6)		32	V	
I _{OUT}	Continuous Output Current		60	mA	
I _{OUT_R}	Reverse Output Current	-50	mA		
В	Magnetic Flux Density		Unlimited		
P _D	Package Power Dissipation	SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)	550	mW	
_	,	SC59 and SOT23	230		
Ts	Storage Temperature Range		-65 to +165	°C	
TJ	Maximum Junction Temperature		+150	°C	
ESD HBM	Electros Static Discharge Withstand - Human Body Model (HBN	1)	6	kV	

Notes:

- 5. Stresses greater than the 'Absolute Maximum Ratings' specified above may cause permanent damage to the device. These are stress ratings only; functional operation of the device at these or any other conditions exceeding those indicated in this specification is not implied. Device reliability may be affected by exposure to absolute maximum rating conditions for extended periods of time.
- The absolute maximum V_{DD} of 32V is a transient stress rating and is not meant as a functional operating condition. It is not recommended to
 operate the device at the absolute maximum rated conditions for any period of time.

Recommended Operating Conditions (@T_A = -40°C to +125°C, unless otherwise specified.)

Symbol	Parameter	Condition	Rating	Unit
V_{DD}	Supply Voltage	Operating	3.0 to 28	V
T _A	Operating Temperature Range	Operating	-40 to +125	°C

Electrical Characteristics (Notes 7 & 8) (@T_A = -40°C to +125°C, V_{DD} = 3V to 28V, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Тур	Max	Unit
V _{OUT_ON}	Output ON Voltage	$I_{OUT} = 20$ mA, B > B _{OP}	-	0.2	0.4	V
I _{LKG}	Output Leakage Current (When output is off)	V _{OUT} = 28V, B < B _{RP} , Output off	-	<0.1	10	μΑ
I_{DD}	Supply Current	Output open, T _A = +25°C	-	3	3.5	mA
		Output open, T _A = -40°C to +125°C	-	1	4	mA
I _{DD R}	Reverse Supply Current	$V_{DD} = -18V$, $T_A = -40^{\circ}C$ to $+125^{\circ}C$	-	-0.01	1	mA
א_טטי_ג	Reverse Supply Current	$V_{DD} = -28V$, $T_A = -40$ °C to $+125$ °C	-	-0.01	1.5	mA
t _{P_ON}	Device Power-On Time (Start-up Time)	$V_{DD} >= 3V, B > B_{OP} $ (Note 7)	-	10	-	μs
f _C	Chopping Frequency	-	-	800	-	kHz
t _D	Response Time Delay (Time from magnetic threshold reached to the start of the output rise or fall)	(Note 9)	-	3.75	-	μs
t _R	Output Rising Time (External pull-up resistor R∟ and load capacitance dependent)	$R_L = 1k\Omega$, $C_L = 20pF$	-	0.2	1	μs
t _F	Output Falling Time (Internal switch resistance and load capacitance dependent)	$R_L = 1k\Omega$, $C_L = 20pF$	-	0.1	1	μs
I _{OCL}	Output Current Limit	B > B _{OP} (Note 10)	30	-	55	mA
Vz	Zener Clamp Voltage	$I_{DD} = 5mA$	28	-	-	V

Notes:

- 7. When power is initially turned on, V_{DD} must be within its correct operating range (3.0V to 28V) to guarantee the output sampling. The output state is valid after the start-up time of 10μs typical from the operating voltage reaching 3V.
- 8. Typical values are defined at T_A = +25°C, V_{DD} = 12V. Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization.
- 9. Guaranteed by design, process control and characterization, Not tested in production.
- 10. The device will limit the output current I_{OUT} to current limit of I_{OCL}




Magnetic Characteristics (Note 11 &12) (T_A = -40°C to +125°C, V_{DD} = 3.0V to 28V, unless otherwise specified.)

(1mT=10 Gauss)


					(11111=10 Gadoo)	
Symbol	Parameter	Conditions	Min	Тур	Max	Unit
B _{OPS} (South pole to part marking side for SOT23 and SIP-3 (Ammo Pack), SIP-3		V _{DD} = 12V, T _A = +25°C	-	115	-	
(Bulk Pack) packages; South pole to the non-part marking side for SC59 package. See diagram below)	Operation Point	T _A = -40°C to +125°C	95	115	140	
B _{RPS} (South pole to part marking side for SOT23 and SIP-3 (Ammo Pack), SIP-3		V _{DD} = 12V, T _A = +25°C	-	90	-	Gauss
(Bulk Pack) packages; South pole to the non-part marking side for SC59 package. See diagram below)	Release Point	$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$	70	90	120	
D (ID ID)	Hysteresis (Note 13)	V _{DD} = 12V, T _A = +25°C	-	25	-	
B _{HY} (B _{OPX} - B _{RPX})	Trysteresis (Note 13)	$T_A = -40^{\circ}C \text{ to } +125^{\circ}C$	18	25	36	

Notes:

- 11. When power is initially turned on, VDD must be within its correct operating range (3.0V to 28V) to guarantee the output sampling. The output state is valid
- 11. When power is littled bit, V_{DD} must be within its correct operating range (5.00 to 280) to guarantee the output sampling. The output state is valid after the start-up time of 10us typical from the operating voltage reaching 3V.
 12. Typical values are defined at T_A = +25°C, V_{DD} = 12V. Maximum and minimum values over the operating temperature range is not tested in production but guaranteed by design, process control and characterization.
 13. Maximum and minimum hysteresis is guaranteed by design, process control and characterization.




(Magnetic Flux Density B)






Typical Operating Characteristics


Output Switch Operate and Release Points (Magnetic Thresholds) -Bops and BRPS




Switch Points \mathbf{B}_{OPS} and \mathbf{B}_{RPS} vs Supply Voltage



Switch Points $\mathbf{B}_{\mathsf{OPS}}$ and $\mathbf{B}_{\mathsf{RPS}}$ vs Temperature




Switch Points $\mathbf{B}_{\mathsf{OPS}}$ and $\mathbf{B}_{\mathsf{RPS}}$ vs Temperature




Switch Points \mathbf{B}_{OPS} and \mathbf{B}_{RPS} vs Temperature

Supply Current



Supply Current vs Supply Voltage




Supply Current vs Temperature




Typical Operating Characteristics (Cont.)

Supply Reverse Current




Reverse Supply Current vs Supply Voltage




Reverse Supply Current vs Temperature

Output Switch On Voltage




Output ON Voltage vs Supply Voltage




Output ON Voltage vs Temperature

Output Switch Leakage Current



Output Leakage Current vs Supply Voltage




Output Leakage Current vs Temperature




Typical Operating Characteristics (Cont.)

Output Current Limit



Output Current Limit vs Supply Voltage




Output CurrentLimit vs Temperature



Thermal Performance Characteristics

(1) Package Type: SC59 and SOT23

T _A (°C)	25	50	60	70	80	85	90	100	105	110	120	125	130	140	150
P _D (mW)	230	184	166	147	129	120	110	92	83	74	55	46	37	18	0




(2) Package Type: SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)

T _A (°C)	25	50	60	70	80	85	90	100	105	110	120	125	130	140	150
P _D (mW)	550	440	396	362	308	286	264	220	198	176	132	110	88	44	0




Power Dissipation Curve





Ordering Information




Dockers			Bulk		7" Tape an	d Reel	Ammo Box		
Part Number	Package Code	Packaging	Quantity	Part Number Quantity		Part Number Suffix	Quantity	Part Number Suffix	
AH3377-P-A	Р	SIP-3 (Ammo Pack)	NA	NA	NA	NA	4000/Box	-A	
AH3377-P-B	Р	SIP-3 (Bulk Pack)	1000	-B	NA	NA	NA	NA	
AH3377-SA-7	SA	SOT23	NA	NA	3000/Tape & Reel	-7	NA	NA	
AH3377-W-7	W	SC59	NA	NA	3000/Tape & Reel	-7	NA	NA	

Notes: 14. Ammo Box is for SIP-3 (Ammo Pack) Spread Lead.

15. Bulk is for SIP-3 (Bulk Pack) Straight Lead.


Marking Information

(1) Package Type: SC59 and SOT23



Part Number	Package	Identification Code
AH3377	SC59	DD
AH3377	SOT23	ZT

(2) Package Type: SIP-3 (Ammo Pack), SIP-3 (Bulk Pack)




Part Number	Package	Identification Code		
AH3377	SIP-3 (Ammo Pack)	3377		
AH3377	SIP-3 (Bulk Pack)	3377		



Package Outline Dimensions (All dimensions in mm.)


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SC59



	SC	59		
Dim	Min	Max	Тур	
Α	0.35	0.50	0.38	
В	1.50	1.70	1.60	
С	2.70	3.00	2.80	
D	-	-	0.95	
G	-	-	1.90	
Н	2.90	3.10	3.00	
J	0.013	0.10	0.05	
K	1.00	1.30	1.10	
L	0.35	0.55	0.40	
М	0.10	0.20	0.15	
N	0.70	0.80	0.75	
α	0°	8°	-	
All	Dimens	ions in	mm	






Sensor Location



Package Outline Dimensions (Cont.) (All dimensions in mm.)


Please see http://www.diodes.com/package-outlines.html for the latest version.

(2) Package Type: SOT23



	SO	Г23	
Dim	Min	Max	Тур
Α	0.37	0.51	0.40
В	1.20	1.40	1.30
C	2.30	2.50	2.40
D	0.89	1.03	0.915
F	0.45	0.60	0.535
G	1.78	2.05	1.83
Н	2.80	3.00	2.90
J	0.013	0.10	0.05
K	0.890	1.00	0.975
K1	0.903	1.10	1.025
L	0.45	0.61	0.55
L1	0.25	0.55	0.40
M	0.085	0.150	0.110
а	0°	8°	
All [Dimensi	ions in i	mm

Min/Max




Sensor Location




Package Outline Dimensions (Cont.) (All dimensions in mm.)


Please see http://www.diodes.com/package-outlines.html for the latest version.

(3) Package Type: SIP-3 (Bulk Pack)





S	SIP-3 (Bulk Pack)				
Dim	Min	Max	Тур		
Α	1.40	1.60	1.50		
b	0.33	0.43	0.38		
b2	0.40	0.508	0.46		
С	0.35	0.41	0.38		
D	3.90	4.30	4.10		
Е	2.80	3.20	3.00		
e1	1.24	1.30	1.27		
F	0.00	0.20			
J	2.62 REF				
L	14.00	15.00	14.50		
L1	1.55	1.75	1.65		
S	0.63	0.84	0.74		
a1			5°		
a2			5°		
a3			45°		
a4			3°		
All Dimensions in mm					




Sensor Location




Please see http://www.diodes.com/package-outlines.html for the latest version.

(4) Package Type: SIP-3 (Ammo Pack)



SIP-3					
(Ammo Pack)					
Dim	Min	Max	Тур		
Α	1.40	1.60	1.50		
b	0.33	0.43	0.38		
b2a	0.40	0.52	0.46		
С	0.35	0.41	0.38		
D	3.90	4.30	4.10		
Е	2.80	3.20	3.00		
e1	1.24	1.30	1.27		
e2	2.40	2.90	2.65		
F	0.00	0.20			
J	2.62 REF				
L	14.00	15.00	14.50		
La	12.90	14.90	13.90		
L1	1.55	1.75	1.65		
L3	2.00	3.00	2.50		
S	0.63	0.84	0.74		
a1			5°		
a2			5°		
а3			45°		
a4			3°		
All Dimensions in mm					




Sensor Location



Suggested Pad Layout


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SC59



Dimensions	Value (in mm)	
Z	3.4	
Х	0.8	
Y	1.0	
С	2.4	
E	1.35	

(2) Package Type: SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	29



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com