

General Description

The WSF12N10G use advanced SGT MOSFET technology to provide low RDS(ON), low gate charge, fast switching and excellent avalanche characteristics. his device is specially designed to get better ruggedness and suitable to use in.

Features

Low RDS(on) & FOM

Extremely low switching loss

Excellent stability and uniformity or Invertors

Product Summery

BVDSS	RDSON	ID
100V	125mΩ	12A

Applications


Consumer electronic power supply

Motor control

Synchronous-rectification

Isolated DC

TO-252 Pin Configuration





Absolute Maximum Ratings at Tj=25°C unless otherwise noted

Symbol	Parameter	Value	Unit	
VDS	Drain source voltage		100	V
VGS	Gate source voltage		±20	V
ID	Continuous drain current1)	TC=25 ℃	12	А
ID, pulse	Pulsed drain current2)	TC=25 ℃	24	А
PD	Power dissipation3)	TC=25 ℃	16.9	W
EAS	Single pulsed avalanche energy	Note5)	1.2	mJ
Tstg,Tj	Operation and storage temperature		-55 to 150	$^{\circ}$
RθJC	Thermal resistance, junction-case		7.4	℃ /W
RθJA	Thermal resistance, junction-ambient Note4)		62	℃ /W



Electrical Characteristics at Tj=25 °C unless otherwise specified

Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
BVDSS	Drain-source breakdown voltage	Vgs=0 V, In=250 μA	100	111	-	V
VGS(th)	Gate threshold voltage	VDS=VGS, ID=250 μA	1.2	2.0	2.5	V
RDS(ON)	Drain-source on-state resistance	Vgs=10 V, ID=5 A	-	105	125	mΩ
RDS(ON)	Drain-source on-state resistance	Vgs=4.5 V, ID=3 A	-	115	145	mΩ
lgss	Gate-source leakage current	V _{GS} =20 V	-	-	100	- nA
		Vgs=-20 V	-	-	-100	
Ipss	Drain-source leakage current	VDS=100 V, VGS=0 V	-	-	1	uA
Ciss	Input capacitance		-	206.1	-	pF
Coss	Output capacitance	Vgs=0 V, Vps=50 V, f=100 kHz	-	28.9	-	pF
Crss	Reverse transfer capacitance		-	1.4	-	pF
td(on)	Turn-on delay time		-	14.7	-	ns
tr	Rise time	Vgs=10 V, Vps=50 V,	-	3.5	-	ns
td(off)	Turn-off delay time	R _G =2 Ω, I _D =5 A	-	20.9	-	ns
t f	Fall time	15-07	-	2.7	-	ns
Qg	Total gate charge		-	4.3	-	nC
Qgs	Gate-source charge	I _D =5 A, V _D s=50 V,	-	1.5	-	nC
Qgd	Gate-drain charge	V _{DS} =50 V, V _{GS} =10 V	-	1.1	-	nC
Vplateau	Gate plateau voltage		-	5.0	-	V
ls	Diode forward current		-	-	7	А
Isp	Pulsed source current	Vgs <vth< td=""><td>-</td><td>-</td><td>21</td></vth<>	-	-	21	
Vsp	Diode forward voltage	Is=7 A, Vgs=0 V	-	-	1.0	V
t rr	Reverse recovery time		-	32.1	-	ns
Qrr	Reverse recovery charge	Is=5 A, di/dt=100 A/µs	-	39.4	-	nC
Irrm	Peak reverse recovery current		-	2.1	-	Α
	•	· · · · · · · · · · · · · · · · · · ·	-	-	•	•

Note:


- 1) Calculated continuous current based on maximum allowable junction temperature.
- 2) Repetitive rating; pulse width limited by max. junction temperature.
- 3) Pd is based on max. junction temperature, using junction-case thermal resistance.
- 4) The value of Reja is measured with the device mounted on 1 in 2 FR-4 board with 2oz. Copper,

in a still air environment with Ta=25 °C.

5) V_{DD}=50 V, R_G=50 Ω , L=0.3 mH, starting T_j=25 °C.



Electrical Characteristics Diagrams






Figure 1, Typ. output characteristics




Figure 2, Typ. transfer characteristics




Figure 3, Typ. capacitances




Figure 4, Typ. gate charge





Figure 5, Drain-source breakdown voltage

Figure 6, Drain-source on-state resistance








Figure 7, Forward characteristic of body diode




Figure 9, Drain current





Fig.11 Switching Time Waveform






Figure 10, Safe operation area T_C=25 °C




Fig.12 Unclamped Inductive Switching Waveform



Attention

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5,In the event that any or all Winsok power products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you Intend to use.
- 9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.