

RoHS



MATERIAL LIST

TEL: 0769-82001899



VER	DESCRIBE	NATE	DRAWN
A0	新图框编制	2020/08/29	姜光鸿

NO.	PART	MATERIAL	COATING/COLOR	QTY
1	HOUSING	LCP UL94V-0	BLACK	1
2	TERMINALS	PHOSPHOR BRONZE	PLATING TIN	N
3	SOLDER TAB	PHOSPHOR BRONZE	PLATING TIN	2

NOTE:
 1 TECHNICAL PARAMETER:
 1.1 RATINGS: 1A/50V (DC AC)
 1.2 CONTACT RESISTANCE: 20MΩ MAX.
 1.3 INSULATION RESISTANCE: 100MΩ MIN
 1.4 WITHSTAND VOLTAGE: 500V AC/MINUTE
 1.5 WORKING TEMPERATURE: -25°C TO +85°C
 MATES WITH :P1010L SERIES HOUSING
 POLES:02-20P
 PART NO: M1010RSF-xxP



PIN位数



P.C.B LAYOUT

PIN	A	B	C
2	1.00	4.00	3.20
3	2.00	5.00	4.20
4	3.00	6.00	5.20
5	4.00	7.00	6.20
6	5.00	8.00	7.20
7	6.00	9.00	8.20
8	7.00	10.00	9.20
9	8.00	11.00	10.20
10	9.00	12.00	11.20
11	10.00	13.00	12.20
12	11.00	14.00	13.20
13	12.00	15.00	14.20
14	13.00	16.00	15.20
15	14.00	17.00	16.20
16	15.00	18.00	17.20
17	16.00	19.00	18.20
18	17.00	20.00	19.20
19	18.00	21.00	20.20
20	19.00	22.00	21.20

TOLERANCE UNLESS OTHERWISE		UNIT	mm	XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO., LTD.	DRAWN	姜光鸿
X. ±0.30	X° ±5°	VIEW			CHKD	
.X ±0.20	.X° ±2°	SCALE	1:1	TYPE	1.00mm Crimp Style Connectors	
.XX ±0.08	.XX° ±1°	NUMBER	XF-M011	PART.NO.	M1010RS-xxP	
.XXX ±0.03	.XXX° ±0.5°				DATE	2020/08/29