

RoHS

MATERIAL LIST

TEL: 0769-82001899



VER	DESCRIBE	NATE	DRAWN
A0	新图框编制	2020/08/29	姜光鸿

NO.	PART	MATERIAL	COATING/COLOR	QTY
1	HOUSING	PA6T UL94V-0	BLACK	1
2	TERMINALS	BRASS	PLATING GOLD	N

NOTE:
 1 TECHNICAL PARAMETER:
 1.1 RATINGS: 3A/250V (DC AC)
 1.2 CONTACT RESISTANCE: 20MΩ MAX.
 1.3 INSULATION RESISTANCE: 1000MΩ MIN
 1.4 WITHSTAND VOLTAGE: 600V AC/MINUTE
 1.5 WORKING TEMPERATURE: -40°C TO +105°C
 1.6 MAX.PROCESSING TEMP:240°C~260°C FOR 30-60SECONDS
 (260°C FOR 10SECONDS)

Ordering Information: PM254VS-12-XX-H85-X-X-X-X-X

1.Part No. 2.Size(H): 3.Material: 4.Finish:
 Optional:H355=3.55mm(W:5.10mm) H50=5.00mm(W:5.10mm) H57=5.70mm(W:5.10mm) H71=7.10mm(W:5.10mm) H80=8.00mm(W:5.10mm) H85=8.50mm(W:5.10mm) H100=10.00mm(W:5.10mm)
 Optional:6=PA6T P=PBT 9=PA9T L=LCP
 Optional:0=G/F 2=Au2U* 3=Au3U* 5=Au5U



Poles	Dimensions(mm)	
	A	B
02	2.54	5.58
03	5.08	8.12
04	7.62	10.66
05	10.16	13.20
06	12.70	15.74
07	15.24	18.28
08	17.78	20.82
09	20.32	23.36
10	22.86	25.90
11	25.40	28.44
12	27.94	30.98
13	30.48	33.52
14	33.02	36.06
15	35.56	38.60
16	38.10	41.14
17	40.64	43.68
18	43.18	46.22
19	45.72	48.76
20	48.26	51.30
~	~	~
40	99.06	102.10

TOLERANCE UNLESS OTHERWISE		UNIT	mm
X. ±0.30	X° ±5°	VIEW	
.X ±0.20	.X° ±2°	SCALE	1:1
.XX ±0.08	.XX° ±1°	NUMBER	XF-PM004
.XXX ±0.03	.XXX° ±0.5°		

XFCN 兴飞连接器有限公司
 XFCN CONNECTORS CO., LTD.

TYPE	2.54mm Female Header Connectors	DRAWN	姜光鸿
PART.NO.	PM254VS-12-XX-H85	CHKD	
		APPD	
		DATE	2020/08/29