

1

2

3

4

5


6

7

8

9

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2014.02.10	邱明周



Specifications

Current Rating: 2.0Amp

Insulation Resistance:1000MΩMin.

Dielectric Withstanding Voltage:500VAC

Contact Resistance:20mΩMax.

Operating Temperature:-40°C to +105°C

Materials

Contact Material:Phosphor Bronze


Insulator Material:High Temperature

Thermoplastic, UL 94V-0 Nylon 6T


(Halogen Free) or the equivalent material

All materials must meet Greenconn

requirement for environment protection.



Recommended P.C.Board
Layout
(Tolerance:±0.05)



Ordering Information

C SFB102 - XX XX A 001 R 1 A X

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
A=Box
Selective Packing
C=Tube

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGN: 邱明周

CHECKED: 劉北平

AUDITED: 曹熙

APPROVED: 曹熙代

DATE: 2014.02.10

DATE: 2014.02.10

DATE: 2014.02.10

DATE: 2014.02.10

DWG. NO.
CSFB102-CA1RA

PART NO.
CSFB102-XXXX A001R1AX

TITLE.
2.00 FEMALE HEADER
SINGLE ROW
RIHGT ANGLE SERIES

REV.	UNIT.	SCALE.	PAGE.	
01	mm	5:1	1/1	

1

2

3

4

5

6

7

8

9