

F

E


D

C

B

A

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2010.05.21	謝金發
02	△	依上級要求變更圖號	2012.04.06	李芳忠
03	△	依業務要求新增白色塑膠配方	2013.03.12	邱明周
04	△	將塑膠顏色白色變更為米色	2013.12.06	邱明周
05	△	依業務要求增加車載料號	2017.12.19	馮國東



Specifications
 Current Rating: 2.0Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials

Contact Material: Phosphor Bronze
 Insulator Material: High Temperature Thermoplastic, UL 94V-0 LCP or the equivalent material

☆ All materials must meet Greenconn hazardous substances control standards.

"★": Critical Characteristics.
 符號"★"表示(與安全或法規無關)客戶特殊要求,與產品組裝、功能等相關的產品或過程特殊特性。


"☆": Safety Features
 符號"☆"表示(與安全或法規有關)那些與政府法規符合性或車輛/產品功能安全性相關的產品或過程特殊特性。

Greenconn P/N	Customer	Remarks
CSFD103-0301A002C1AD	G005	Automotive Connector

Ordering Information



Recommended P.C.Board Layout
 (Tolerance: ±0.05)



格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGNED: 馮國東	DATE: 2017.12.19	DWG. NO.
X.*±5.0°	X.±0.30	CHECKED: 曹熙	DATE: 2017.12.19	CSFD103-CA2CA
.X*±3.0°	.X±0.25	CO SIGNED: 劉北平	DATE: 2017.12.19	PART NO.
.XX*±2.0°	.XX±0.15	APPROVED: 李輝	DATE: 2017.12.19	CSFD103-XXXX A002CXAX
.XXX*±1.0°	.XXX±0.10			

TITLE.
2.00 FEMALE HEADER SINGLE ROW SMT TYPE BASE 6.35H

REV.	UNIT.	SCALE.	PAGE.
05	mm	3:1	1/1