






REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2014.05.27	邱國強
02	△	平面度依客戶要求修改標準	2019.08.14	馮國東
03	△	依業務要求增加膠紙選項和修改平面度	2020.08.21	何東華

Specifications
 Current Rating:2.0Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T (Halogen Free) or the equivalent material
 All materials must meet Greenconn hazardous substances control standards.



Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PFD101 - XX XX A 003 R 1

No. of Pins per Row
02~40

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color
1=Black

Standard Packing
C=Tube
Selective Packing
A=box
E=CAP+Tube
F=CAP+Tape&Reel
G=Acetate Tape+Tube
H=Acetate Tape+Tape&Reel

Dim.C	NOTE
0.10	02~08PIN
0.12	09~10PIN
0.15	11~40PIN

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE

X'±5.0'	X.±0.30
.X'±3.0'	.X±0.25
.XX'±2.0'	.XX±0.15
.XXX'±1.0'	.XXX±0.10

DESIGNED: 何東華

DATE: 2020.08.21

CHECKED:

DATE:

CO SIGNED: 廖世龍

DATE: 2020.08.21

APPROVED:

DATE:

DWG. NO.

GPFD101-CA3RB

PART NO.

GPFD101-XXXX A003R1BX

TITLE.

2.00 PIN HEADER
 SINGLE ROW DIP TYPE
 CONNECTOR

REV.	UNIT.	SCALE.	PAGE.
03	mm	5:1	1/1