






REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	2014.02.12	邱明周



Specifications
 Current Rating:2Amp
 Insulation Resistance:1000MΩMin.
 Dielectric Withstanding Voltage:500VAC
 Contact Resistance:20mΩMax.
 Operating Temperature:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:High Temperature Thermoplastic, UL 94V-0 Nylon 6T (Halogen Free) or the equivalent material
 All materials must meet Greenconn requirement for environment protection.



Recommended P.C.Board Layout
 (Tolerance:±0.05)



Ordering Information

G PFD201 - XX XX A 009 R 1 B X

No. of Pins per Row 02~40
 Standard Plating 02=Gold Flash
 Selective Plating 01=Tin 05=Gold Flash/Tin
 Color 1=Black
 Standard Packing C=Tube
 Selective Packing A=Box E=CAP+Tube F=CAP+Tape&Reel

格菱股份有限公司
Greenconn Corporation

GENERAL TOLERANCE		DESIGN: 邱明周	DATE: 2014.02.12	DWG. NO.	TITLE. 2.00 PIN HEADER DUAL ROWS SMT TYPE BASE 2.00H
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2014.02.12	GPFD201-CA9RB	
.X*±3.0°	.X±0.25	AUDITED: 曹熙	DATE: 2014.02.12	PART NO.	
.XX*±2.0°	.XX±0.15	APPROVED: 李輝	DATE: 2014.02.12	GPFD201-XXXX A009R1BX	
.XXX*±1.0°	.XXX±0.10				

REV.	UNIT.	SCALE.	PAGE.
01	mm	3:1	1/1