TAP650 Series



High-power, low profile design

FEATURES

- For variable speed drives, power supplies, control devices, robotics, motor control and other power designs.
- High-purity ceramic metalized with film on bottom for better heat transfer and optimum discharge.
- Encapsulation: Special resin-filled epoxy casing. High insulation resistance (CTI 600), high dielectric strength and partial discharge capability.
- Resistance Element: Special design for low inductance and capacitance values. The element demonstrates stability while covering high wattage and pulse loading.



Resistance values 0.25Ω to $1M\Omega$ (others upon request).

max lead length.

voltage not exceeding max. power

Short time overload 1,000 W at 70°C for 10sec., delta-R = 0.4% max.

Temperature coefficient ±150 ppm/°C (others upon request)

Resistance tolerance $\pm 5\%$ to $\pm 10\%$

Maximum working


Values below 1 ohm are measured at

5,000VDC, higher voltage upon request,

CHARACTERISTICS

Power650W at 85°C bottom case temp. (Please ask for detailed
mounting procedure! This value is only applicable if using
thermal conduction to the heat sink Rth-cs<0.117°K/W.
This value can be obtained by using a thermal transfer
compound with a heat conductivity of 8.55 W/mK. The
flatness of the cooling plate must be better than 0.05mm
overall. Surface roughness should not exceed 6.4µm.





	0.4% max.		
Power rating	650W at 85°C bottom case temperature (others upon request) up to 1,500A depending on pulse length and frequency. Please ask for details!		
Peak current			
Electric strength voltage	6kVrms, 50 Hz,up to 12 kVrms upon special request.		
Single shot voltage	up to 12kV norm wave (1.5/50 µsec)		
Partial discharge	4KVrms, <10 pC, up to 7kV upon spe- cial request		
Insulation resistance	10 GΩ min. at 500V		
Inductance	80nH (typical)		
Capacity/mass	110 pF		
Capacity/parallel	40 pF		
Operating temperature	res. body: -55°C to +150°C; std. cables: -40°C to +120°C (other cables upon request)		
Mounting max. torque	1.8 Nm, M4 screws		
Housing material	According to UL94-V0		
Standard storage condi- tions	0° to 85°C at 80% RH max. for min. 12 months. For different conditions please contact factory		
Derating (thermal resist.)	8.55W/°K (0.117°K/W)		


Test	Method	Typical results
Short time overload	1,000W/10sec	0.4%
Humidity steady state	56 days/40°C/95%	0.25%
Temp. cycling	-55°/+125°/5 cycles	0.20%
Shock	40g/4,000 times	0.25%
Vibrations	2-500Hz/10g	0.25%
Load life	3,000cyl; Pn 30 min. on / 30 min off	0.40%

(continued)

TAP650 Series

High-power, low profile design

DIMENSIONS



ORDERING INFORMATION

	IS compliant	Standard part numbers	
TAP Style	Compliant version vailable I Resistance 1 Ohm = 1R0 10 Ohm = 10R 1000 Ohm = 1K0	TAP650JR25E TAP650JR50E TAP650JR70E TAP650J4R7E TAP650J40RE TAP650J27RE TAP650J36RE TAP650J50RE TAP650J50RE	TAP650J100E TAP650J270E TAP650J500E TAP650J1K0E TAP650J2K5E TAP650J5K0E TAP650J7K5E TAP650J10KE

THIS PRODUCT IS DESIGNED FOR USE WITH PROPER HEATSINKING.

Maximum base plate temperature of the resistor must be monitored and kept within specified limits to establish the power rating. Best technique is to attach a thermocouple to the side of the base plate of the resistor. Temperature of plastic housing or heat sink cannot be used to establish rating of the resistor. The Ohmite CP4 (https://www.ohmite.com/cp4-series-chillplate/) is an example of properly designed heat sink.



139

rev 6/20-1